

SCREW TOGETHER HOODS, TOP ENTRY


DTPPK SERIES

TECHNICAL SPECIFICATIONS

Material: UL 94 V-0 Plastic Material
 Operating Temperature: -55°C to +110°C
 Cable Entry: Top
 Thumbscrews: UNC 4-40 (standard)
 M2.5, M2.6 or M3.0 on request
 Cable Diameter: Up to 13 mm
 Colour: Black

FEATURES

- Available in sizes 9-15-25-37
- Suitable for any common Sub-D connector
- Re-openable
- Strain relief inserts ensure a secure termination
- Also available in Metalized version



Size	Product Code
9-way	DTPPK9-K
15-way	DTPPK15-K
25-way	DTPPK25-K
37-way	DTPPK37-K

Size	Dim A	Dim B	Dim C
9-way	31,2	39,9	15,0
15-way	39,5	41,5	15,0
25-way	53,4	48,6	15,0
37-way	69,7	53,6	15,0

SCREW TOGETHER HOODS, 45° ENTRY


D45PPK SERIES

TECHNICAL SPECIFICATIONS

Material: UL 94 V-0 Plastic Material
 Operating Temperature: -55°C to +110°C
 Cable Entry: Side
 Thumbscrews: UNC 4-40 (standard)
 M2.5, M2.6 or M3.0 on request
 Cable Diameter: Up to 13 mm
 Colour: Black

FEATURES

- Available in sizes 9-15-25-37
- Suitable for any common Sub-D connector
- Re-openable
- Strain relief inserts ensure a secure termination
- Also available in Metalized version



Size	Product Code
9-way	D45PPK9-K
15-way	D45PPK15-K
25-way	D45PPK25-K
37-way	D45PPK37-K

Size	Dim A	Dim B	Dim C
9-way	31,0	36,3	15,0
15-way	39,5	40,3	15,0
25-way	53,2	40,3	15,0
37-way	69,7	40,3	15,0