

[Home](#) > [5530199F](#)

Search For Part Number

Part Number: **5530199F**

General Description

Series	553
Description	3 mm White/White Bi -Level CBI
Package Options	Bulk Packaging
Sizes	3mm
Lamp Type	Bi-Level Housing
Viewing	Right Angle
Polarity	Cathode Right
Lens Style	Untinted, Non -Diffused
Viewing Angle	45
LED Centerline	5.0mm

Absolute Maximum Ratings (Ta = 25Å °)

Derating	0.42 (mA/degC)
Reverse Voltage	5
Solder Temperature	260 for 5 secs
Operating Temperature	-40 to +85
Storage Temperature	-40 to +100

Operating Characteristics

Color	White
LED Type	High Efficiency
LED Position	1,2
Luminous Intensity Min	950
Forward Voltage Typical	3.2
Forward Voltage Max	3.7
Test Current mA	20mA



5530199F

[check stock](#)



[This is a
RoHS Compliant Product.
To learn more click here.](#)

[Site Map](#) [Contact Us](#) [BLP Components](#) [Privacy Policy](#) [Careers](#)

Copyright© 2008, Dialight. All Rights Reserved.