



ENGLISH

## Datasheet

Stock No: 1718311

### RS Pro Top Plate Swivel Braked Castor, 125mm Dia., 230kg



#### Technical Data

Wheel diameter	125 mm
Width of Tread	36 mm
Size of Plate	105 x 85 mm
Plate hole centres	80 x 60 mm
Plate hole	9 mm
Offset	40 mm
Overall height	155 mm
Temperature	- 20 / + 60 °C
Swivel Radius	116 mm
Hardness of tread	Shore A 75
Load capacity	230 kg

## Product Details

Swivel castor with total lock, tail end of castor  
Wheel centre made of Polyamide, Tread:  
elastic-tyre, non-marking, roller bearing

Roll performance	+	+	+	+	+
Movement noise	+	+	+	+	+
Attrition	+	+	+	+	+
Corrosion resistance	+	+	+	+	+