



DC axial fans

Series 3250 JU 92 x 92 x 38 mm



Highlights:

- Motor protection against reverse polarity and locking.
- Air exhaust over struts
- Connection via 310 mm strands AWG 24, TR 64, bared and tin-plated
- Ingress protection rating of IP68

Material: Housing: Fiberglass-reinforced PBT composite
Impeller: Fiberglass-reinforced PA composite

Direction of rotation: Clockwise, seen on rotor

Nominal Data

Type	Air flow CFM	Nominal voltage VDC	Voltage range VDC	Sound pressure level dB(A)	Sound power level Bel(A)	Ball bearings	Power input Watts	Speed RPM	Temperature range °C	Mass g	Ingress Protection Rating	UL Approval	Curves
3258 J/2HHPU	138.3	48	36...56	59	7.2	Yes	24.3	6650	-20...70	240	IP68	Yes	1
3258 J/2H3PU	158.9	48	36...56	64	8.0	Yes	33.6	7450	-20...70	240	IP68	Yes	2

Curves

