

Power cable Model: AK-PC-12A





Product code	AK-PC-12A
Product type	Power cable
Series	Pro
Output voltage	250 V
Output amperage	10 A
Ground wire	Yes
Cable length	3 m
The cable plug #1	Hybrid standard C/E/F (CEE 7/7)
The cable plug #2	IEC C13 90°
Material	CCA
Wire construction	PVC
Cable diameter	7 mm
Product color	Black
Product size (L \times W \times H)	250 x 87 x 63 mm
Package size (L x W x H)	251 x 88 x 64 mm
Net weight	246,9 g
Gross weight	247,9 g
CE compatibility	Yes
FCC compatibility	No
RoHS compatibility	Yes
REACH compatibility	Yes
EAN code	5901720136015













Description

Akyga® AK-PC-12A is a power cable with **IEC C13** and **CEE 7/7** plugs. It allows you to connect devices such as a **computer**, **TV** set or **monitor** to the power supply. Thanks to the right-angled plug, it will save space between the powered device and the wall or shelf. In contrast, the black universal cable color will perfectly match any interior. The cable allows you to power the device with a current of **10 A** and a voltage of **250 V**. Its length is **3 m**.