



5

4

3


2

1






1,27
1,27x7= 8,89



PCB layout, component side
PCB thickness up to 2,4mm



A-A



Material: Shielding: brass plating nickel alloy
Insert: Thermoplastic, UL-94-V0, black
Contact: -Phosphor Bronze, selective gold plating
15u" over nickel in contact area
-Tin plating over nickel in solder area

			Dat.	Name	 All Dim. in mm Orig. Size DIN A 4	HARTING RJ Industrial® 2-ports modular RJ 45 Jack with 2x8 signal solder pins and 3 grounding solder pins	Maßstab/ Scale	
			Detail.	09/DEC/11			BH	1,5:1
			Insp.	09/DEC/11			JB	
			Stand.					
36299	20/04/12	SD	HARTING EURL F-95972 Paris			 TB 09 45 551 1122	Blatt/ Page	
EC03766							1 / 1	
Mod.	Dat.	Name				Sub.		