




SPECIFICATION CONTROL DRAWING Crystal Resonator

FREQUENCY
24.000000MHz



Holder Style	3X25X06 4-Pad
Mode	Fundamental
Adjustment Tolerance	± 10 PPM at 25°C
Temperature Stability	± 25 PPM
Operating Temp. Range	-40°C to +85°C
Load Capacitance	10 pF
ESR	60 Ohm
Static Capacitance (C0)	Unspecified pF
Ageing	3.0ppm / Yr Max
Marking	AEL24.00 WWYY

Amdt Date	Change Note	AEL Code		
6 OCT 10	Supply on 12mm width tape only	X24M000000S050		
	Datecode added	<table border="1" style="width: 100%; border-collapse: collapse;"> <tr> <th style="width: 60%;">Issue Ref</th> <td style="text-align: center;">C</td> </tr> </table>	Issue Ref	C
Issue Ref	C			