



Conductor: {26AWG(0.16x7)BC}x6C  
 Insulation:(PP6331 TD:0.95±0.03)x6C  
 Jacket: PVC NOUL 65P



P1	P2
1 White	6
2 Black	5
3 Red	4
4 Green	3
5 Yellow	2
6 Blue	1

**Note for plug:**  
 Material:  
 Housing-Polycarbonate,clear.  
 Terminal-0.36[.014] thick phosphor bronze.  
 Thick gold in localized gold plate.  
 Area,Gold flash over the remainder.  
 Over 2.54mm[.000100] thick nickel underplate

**Order code: AT-S-26-6/6/X-XX**

Order color:  
 B: Black  
 W: White  
 S: Silver

Length Code	Length (mm)
5	1525±20(5FT)
7	2135±30(7FT)
10	3050±60(10FT)
12	3660±60(12FT)
14	4270±60(14FT)
25	7625±100(25FT)
50	15250±150(50FT)

**RoHS compliant**  
 Unit: mm

Scale	Free	Date		Name	
TOLERANCE		Drawn	18.12.2017	Amy	
.X	±0.50	Approved	18.12.2017	Amy	
.XX	±0.20				
DIM	TOL				
Angle	±2°				



Customer-No.	
ASSMANN WSW-No.	AT-S-26-6/6/X-XX
Drawing-No.	ASS 8168 CA
Replace	rev00

1	2	3	4	5	6	7
H	G	F	E	D	C	B