

**Professionally approved products.
Datasheet**

Male Crimp D-Sub Connector Coaxial Contact

RS Stock number 251-835




Specifications:

- Impedance: 50Ω
- Working frequency: 1GHz max
- Dielectric with standing voltage: 600V
- Insulation resistance 5000: 14 Ω
- Contact resistance $\leq 5 \text{ m}\Omega$
- Insertion loss: $\leq 0.2 \text{ dB}$
- Mating force per set of contact 0.4 N to 9 N
- Mating endurance 500
- Temperature -55° to $+125^\circ \text{ C}$

Professionally approved products. Datasheet

Dimensions – mm:



DM537403NCLF	Ct coax male sortie droite	2.75	4.00	4.40	5.45	RG 180 BU
DM53740NCLF	Ct coax male sortie droite	1.00	1.75	2.32	3.20	RG 178 BU
DM537401NCLF	Ct coax male sortie droite	1.70	2.46	3.13	3.84	RG 179 BU
Ref contact	Designation	$\phi A^{+0.10}_0$	$\phi B^{\pm 0.05}$	$\phi C^{+0.10}_0$	$\phi D^{\pm 0.10}$	Ref cable