



Standard and Ground Terminal Blocks

Compression clamp

MA 2,5/5 Spacing 5mm



M 4/6 Spacing 6mm



Characteristics		IEC NFC VDE	UL	CSA
Wire size mm ² / AWG	Solid Wire	0.2 - 4	22-12AWG	22-12AWG
	Stranded Wire	0.22 - 2.5		
Rated voltage	V	800	600	600
Rated current	A	24	20	25
Rated wire size	mm ² / AWG	2.5mm ²	12AWG	12AWG
Wire stripping length	mm / inches	10mm/ .39"		
Recommended torque	Nm / lb.in	0.4-0.6 Nm / 3.5-5.3 lb-in		

Selection

Body Colour	Type	Order Code	Pack
● Grey	MA 2,5/5	0115 486.03	50
● Blue	MA 2,5/5.N	0125 486.05	50
● Beige VO	MA 2,5/5.VO	0195 486.04	50
● Green+yellow (with contact rail)	MA 2,5/5.P	0165 488.27	50
● Green+yellow VO (with contact rail)	MA 2,5/5.PVO	0195 488.16	50
● Yellow+green (without contact rail)	MA 2,5/5.PI	0165 677.03	50

Characteristics		IEC NFC VDE	UL	CSA
Wire size mm ² / AWG	Solid Wire	0.2 - 4	22-10AWG	22-10AWG
	Stranded Wire	0.22 - 4		
Rated voltage	V	800	600	600
Rated current	A	32	30	25
Rated wire size	mm ² / AWG	4mm ²	10AWG	10AWG
Wire stripping length	mm / inches	9.5mm/ .37"		
Recommended torque	Nm / lb.in	0.5-0.8 Nm / 4.4-7.1 lb-in		

Selection


Body Colour	Type	Order Code	Pack
● Grey	M 4/6	0115 116.07	50
● Blue	M 4/6.N	0125 116.01	50
● Yellow	M 4/6	0105 116.16	50
● Orange	M 4/6	0105 002.20	50
● Red	M 4/6	0105 032.15	50
● Black	M 4/6	0105 031.14	50
● Beige VO	M 4/6.VO	0195 116.00	50
● Green+yellow (with contact rail)	M 4/6.P	0165 113.16	50
● Green+yellow VO (with contact rail)	M 4/6.PVO	0195 113.05	50
● Yellow+green (without contact rail)	M 4/6.PI	0165 275.00	50

[Return to main index](#)

Standard and Ground Terminal Blocks

Compression clamp

M 6/8 Spacing 8mm




Characteristics		IEC NFC VDE	UL	CSA
Wire size mm ² / AWG	Solid Wire	0.5 - 10	22-8AWG	22-8AWG
	Stranded Wire	0.5 - 6		
Rated voltage	V	800	600	600
Rated current	A	41	50	55
Rated wire size	mm ² / AWG	6mm ²	8AWG	8AWG
Wire stripping length	mm / inches	12mm/ .47"		
Recommended torque	Nm / lb.in	0.8-1 Nm / 7.1-8.9 lb-in		

Selection

Body Colour	Type	Order Code	Pack
● Grey	M 6/8	0115 118.11	50
● Blue	M 6/8.N	0125 118.13	50
● Yellow	M 6/8	0105 118.20	50
● Orange	M 6/8	0105 004.22	50
● Beige VO	M 6/8.VO	0195 118.12	50
● Green+yellow (with contact rail)	M 6/8.P	0165 114.17	50
● Green+yellow VO (with contact rail)	M 6/8.PVO	0195 114.06	50
● Yellow+green (without contact rail)	M 6/8.PI	0165 451.21	50

M 10/10 Spacing 10mm



Characteristics		IEC NFC VDE	UL	CSA
Wire size mm ² / AWG	Solid Wire	0.5 - 10	22-8AWG	22-8AWG
	Stranded Wire	0.5 - 6		
Rated voltage	V	800	600	600
Rated current	A	41	50	55
Rated wire size	mm ² / AWG	10mm ²	6AWG	6AWG
Wire stripping length	mm / inches	12mm/ .47"		
Recommended torque	Nm / lb.in	1.2-1.4 Nm / 10.6-12.3 lb-in		

Selection


Body Colour	Type	Order Code	Pack
● Grey	M 10/10	0115 120.17	50
● Blue	M 10/10	0125120.11	50
● Orange	M 10/10	0105 120.26	50
● Beige VO	M 10/10.VO	0195 120.10	50
● Green+yellow (with contact rail)	M 10/10.P	0165 115.10	50
● Green+yellow VO (with contact rail)	M 10/10.PVO	0195 115.07	50
● Yellow+green (without contact rail)	M 10/10.PI	0165 452.22	50

[Return to main index](#)

Standard and Ground Terminal Blocks

Compression clamp

M 16/12 Spacing 12mm




Characteristics		IEC NFC VDE	UL	CSA
Wire size mm ² / AWG	Solid Wire	0.5 - 25*	14-4AWG	14-4AWG
	Stranded Wire	0.5 - 16*		
Rated voltage	V	800	600	600
Rated current	A	85	85	100
Rated wire size	mm ² / AWG	16mm ²	4AWG	4AWG
Wire stripping length	mm / inches	14mm / .55"		
Recommended torque	Nm / lb.in	1.2-1.4 Nm / 10.6-12.3 lb-n		

Selection

Body Colour	Type	Order Code	Pack
● Grey	M 16/12	0115 129.14	20
● Blue	M 16/12.N	0125 129.16	20
● Yellow	M 16/12	0105 129.23	20
● Beige VO	M 16/12 VO	0195 129.15	20
● Green+yellow (with contact rail)	M 16/12.P	0165 130.23	20
● Green+yellow VO (with contact rail)	M 16/12.P VO	0195 130.12	20
● Yellow+green (without contact rail)	M 16/12.PI	0165 453.23	20

M 35/16 Spacing 16mm



Characteristics		IEC NFC VDE	UL	CSA
Wire size mm ² / AWG	Solid Wire	1 - 50	16-0AWG	16-0AWG
	Stranded Wire	1 - 35		
Rated voltage	V	800	600	600
Rated current	A	125	150	140
Rated wire size	mm ² / AWG	35mm ²	0AWG	0AWG
Wire stripping length	mm / inches	17mm / .67"		
Recommended torque	Nm / lb.in	2.8-3 Nm / 24.3-26.1 lb-in		

Selection

Body Colour	Type	Order Code	Pack
● Grey	M 35/16	0115 124.07	20
● Blue	M 35/16.N	0125 124.01	20
● Yellow	M 35/16	0105 124.16	20
● Beige VO	M 35/16 VO	0195 124.00	20
● Green+yellow (with contact rail)	M 35/16.P	0165 111.14	20
● Green+yellow VO (with contact rail)	M 35/16.P VO	0195 111.03	20
● Yellow+green (without contact rail)	M 35/16.PI	0165 454.24	20

*Note	M16/12.P	M35/16.P
Solid Wire	4-25 mm ² 14-4 AWG	4-50mm ² 12-0 AWG
Stranded Wire	4-16mm ²	4-35mm ² 12-2 AWG

Return to main index