



P/N LEGEND


A12514	WR	S	XP	N	L	X	T1	T	00	R
①	②	③	④	⑤	⑥	⑦	⑧	⑨	⑩	⑪

① Series No.  
 ② Connector type: WR=Right angle  
 ③ Mounting type: S=SMT TYPE  
 ④ No. of circuits  
 ⑤ N=Halogen Free  
 ⑥ Material: L=LCP ;  
 ⑦ Color: N=Natural ; B=Black  
 ⑧ Plating code for contacts:  
 T1=Matte Tin-plated;  
 ⑨ Plating code for solder tabs:  
 T=Matte Tin-plated;  
 ⑩ Option code: 00=Standard  
 ⑪ Packing code: R=Tape & Reel



SPECIFICATIONS

Current Rating: 1A AC,DC  
 Voltage Rating: 50V AC,DC  
 Temperature Range: -25°C ~ +85°C  
 Contact Resistance: 30mΩ Max.  
 Insulation Resistance: 100MΩ Min.  
 Withstanding Voltage: 500V AC/minute  
 Pin Material: Phosphor Bronze  
 Solder Tabs: Brass




Circuit No.	Dimensions			Circuit No.	Dimensions		
	A	B	C		A	B	C
02P	1.25	5.75	3.80	09P	10.00	14.50	12.55
03P	2.50	7.00	5.05	10P	11.25	15.75	13.80
04P	3.75	8.25	6.30	11P	12.50	17.00	15.05
05P	5.00	9.50	7.55	12P	13.75	18.25	16.30
06P	6.25	10.75	8.80	13P	15.00	19.50	17.55
07P	7.50	12.00	10.05	14P	16.25	20.75	18.80
08P	8.75	13.25	11.30	15P	17.50	22.00	20.05

				燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.					
		UNIT	SCALE	SHEET	TITLE:				
		mm	1 : 1	1 of 3	1.25mm PITCH 90° WAFER-SMT TYPE				
A5	EN202206071082	2022.06.08	徐貴湖	DRAWN BY				APPROVED BY	
A4	EN202204201026	2022.04.14	徐貴湖	徐富永				徐富永	
A3	EN20220331988	2022.02.18	徐貴湖	2020.06.17				2020.06.17	
A2	EN20210312583	2021.04.22	鄭小嬌	GENERAL TOLERANCE					
A1	EN20210113550	2021.03.23	鄭小嬌	X. X±0.25	ANGLE±				
A0	NEW RELEASE	2020.06.17	鄭小嬌	X. XX±0.15					
REV.	DESCRIPTION	DATE	NAME	X. XXX±0.05			DRAW NO. :	REV. A5	


DRAW NO. : A12514WR-S-XPXXXXXXXXX




# 塑膠各PIN外觀差異




02P




03P




04~05P




06P




07P




08P




09P




10P




11P




12P



13P



14P



15P



燦達電子工業股份有限公司  
JOINT TECH ELECTRONIC IND. CO., LTD.

UNIT	SCALE	SHEET
mm	1 : 1	2 of 3





TITLE:

1.25mm PITCH  
90° WAFER-SMT TYPE

A5	EN202206071082	2022.06.08	徐貴湖
A4	EN202204201026	2022.04.14	徐貴湖
A3	EN20220331988	2022.02.18	徐貴湖
A2	EN20210312583	2021.04.22	鄭小嬌
A1	EN20210113550	2021.03.23	鄭小嬌
A0	NEW RELEASE	2020.06.17	鄭小嬌
REV.	DESCRIPTION	DATE	NAME

DRAWN BY	APPROVED BY
徐富永	徐富永
2020.06.17	2020.06.17
GENERAL TOLERANCE	
X. X±0.25	ANGLE±
X. XX±0.15	
X. XXX±0.05	

DRAW NO. :	REV. A5
A12514WR-S-XPXXXXXXXR	



Number of Contacts	W±0.3	F±0.1	S±0.1	Q'ty/Reel
02P	16.00	7.50	/	1,000
03P				
04P				
05P				
06P				
07P	24.00	11.50		
08P				
09P				
10P	32.00	14.20	28.40	
11P				
12P				
13P				
14P				
15P	44.00	20.20	40.40	

				燦達電子工業股份有限公司 JOINT TECH ELECTRONIC IND. CO., LTD.			
				UNIT	SCALE	SHEET	TITLE:
				mm	1 : 1	3 of 3	
A5	EN202206071082	2022.06.08	徐貴湖	DRAWN BY 徐富永	APPROVED BY 徐富永	1.25mm PITCH 90° WAFER-SMT TYPE TAPING SPEC.	
A4	EN202204201026	2022.04.14	徐貴湖				
A3	EN20220331988	2022.02.18	徐貴湖	2020.06.17 2020.06.17		DRAW NO. : A12514WR-S-XPXXXXXXXR	
A2	EN20210312583	2021.04.22	鄭小嬌	GENERAL TOLERANCE			
A1	EN20210113550	2021.03.23	鄭小嬌	X. X±0.25	ANGLE±		
A0	NEW RELEASE	2020.06.17	鄭小嬌	X. XX±0.15			
REV.	DESCRIPTION	DATE	NAME	X. XXX±0.05			