

CAT. N° 0 371 20



TERMINAL BLOCK VIKING 3 - SCREW - 1 CONNECT - 1 ENTRY/1 OUTLET - PITCH 5 -ORANGE

Pack (number of units)	60
Volume (dm ³)	1,256
Weight (g)	418,00

Product characteristics

Connecting

- Grey for standard circuit, blue for neutral conductor, orange for circuit not broken by the master isolating device, red for special circuits (safety, protected, etc), green for protection conductor class II equivalent assemblies

1 connection - 1 entry/1 outlet

- Colour : Orange
- Nominal cross-section : 2.5 mm²
- Capacity – Rigid wire : 0.25 to 4 mm²
- Capacity – Flexible wire with or without ferrules : 0.25 to 2.5 mm²
- Pitch : 5 mm

General characteristics

Viking™ 3 terminal blocks with screw connection - for copper cables

- Used to make the electrical connection between 2 flexible copper wires with or without ferrules or 2 rigid copper wires
- 2 areas for automatic insertion bridging combs up to 8 pitch (upper level only for multi-level blocks)
- For rails depth 15 mm, EN 60715 depth 7.5 mm and 15 mm

Documentation

Catalogue pages & additional information

- [Selection chart \(p.324-325\)](#)
- [Description page \(p.328\)](#)
- [Technical page \(p.335\)](#)
- [Viking™ 3 terminal blocks with screw connection](#)

Agreements & certificates of conformity

- [VERITAS \(BV\)-23393/C0 BV](#)
- [IMQ-CA02](#)
- [NF App Industri-NF208_1010](#)
- [UL recogn-20101029-E60900](#)
- [ATEX-LCIE 16 ATEX 3049U - 02](#)
- [Ex-002/H](#)

Installation & technical data

- [F00671EN-02](#)
- [F00902EN-03](#)