


### Features

- I stepper motor : 12Vdc / 32mA
- I applications :
  - n office machines
  - n automatic machines
  - n split air conditioners

### Specifications

- I rated voltage : 12Vdc
- I current : 60mA
- I impedance : 200ohm
- I phase : 4
- I step angle / step : 7.5° / 85
- I reduction ratio : 1/85
- I detent torque : 350gfcM
- I pull-in torque : 600gfcM
- I max. starting pulse rate : 500pps
- I max. slewing pulse rate : 800pps
- I temperature range : 45°C
- I noise : 25dB
- I colours
  - n B1 : pink
  - n A1 : orange
  - n A2 : yellow
  - n B2 : blue
  - n GND : red
  - n GND2 (for MOTS2) : brown



6	+	X	X	X
7	+	X	X	+
8	X	X	X	+

