

S201S05V

S26MD01

Тип	Макс. ток, А	Напряжение вых., В	Ток сраб., мА	Напр. изол., В	Соответствие стандартам	Корпус	Рис.
S201S05V	3	600	15	3000		SIP4	1
S202T01	2	600	8	3000		SIP4	2
S201S06V	3	600	15	3000		SIP4	3
S202T02	2	600	8	3000		SIP4	4
S202S01	8	600	8	4000	UL, CSA	SIP4	5
S202S02	8	600	8	4000	UL, CSA	SIP4	6
S202SE1	8	600	8	3000	TUV, UL, CSA	SIP4	5
S202SE2	8	600	8	3000	TUV, UL, CSA	SIP4	7
S202S11	8	600	8	4000	UL, CSA	SIP4	8
S202S12	8	600	8	4000	UL, CSA	SIP4	9
S216S02	16	600	50	4000	UL, CSA	SIP4	7
S216SE2	16	600	50	3000	TUV, UL, CSA	SIP4	7
S26MD01	0,6	600	10	4000	UL, CSA	DIP8	10
S26MD02	0,6	600	10	4000	UL, CSA	DIP8	11




Рис. 1




Рис. 2




Рис. 7




Рис. 8




Рис. 3




Рис. 4




Рис. 9




Рис. 10




Рис. 5




Рис. 6