

TE CONNECTIVITY (TE)
6WWV-16-008=#6 TRIBARRIER

Buchanan

2-796608-4
 TE Internal Number: 2-796608-4
 Alias ID: 6WWV-16-008

[EU RoHS Compliant](#)
[EU ELV Compliant](#)

Barrier Style **Tri-Barrier**

Bottom Termination Style **Solderless Wire Wrap**

Current Rating (A) **25**

Number of Positions **16**

Centerline (Pitch) **9.53 mm [.375 in]**
[See All Features](#)

✓ Active

[PRODUCT DRAWING](#)
 English

[3D PDF](#)

[See All Documentation](#)

North America ▼

Contact us to request pricing, availability and customization options.

[REQUEST ADDITIONAL INFORMATION](#) >

GET SAMPLE	
SAVE TO LIST ▼	
FIND SIMILAR PRODUCTS	

DOCUMENTATION

FEATURES

PRODUCT COMPLIANCE

Product Drawings

[6WWV-XX-008 ASSEMBLY](#)

PDF **(TIFF AVAILABLE)**
English

CAD Files

[3D PDF](#)

PDF
3D

[Customer View Model](#)

2D_DXF.ZIP
English

[Customer View Model](#)

3D_IGS.ZIP
English

[Customer View Model](#)

3D_STP.ZIP
English

1-1773458-2_BARRIER_STRIPS_QUICK_REFERENCE_GUIDE

Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.

Product Type Features	Connector & Contact Terminates To	Printed Circuit Board
	Block Style	Open Bottom with Standoffs
	Product Type	Barrier Strip

Configuration Features	Number of Positions	16
	Number of Rows	1
	Number of Levels	1

Electrical Characteristics	Current Rating (Max) (A)	25
	Current Rating (A)	25
	Voltage (V)	300

Body Features	Barrier Style	Tri-Barrier
	Color	Black

Contact Features	Terminal Plating Finish	Bright
	Terminal Material	Copper Alloy
	Terminal Plating Material	Tin

Termination Features	Bottom Termination Style	Solderless Wire Wrap
----------------------	--------------------------	-----------------------------

Mechanical Attachment	Screw Size	6-32
	Mounting Ears	Without
	Mounting Options	None
	Screw Material	Steel
	Screw Plating Material	Zinc Chromate
	Mounting Insert	Without







	Mounting Angle	Vertical
Housing Features	Centerline (Pitch)	9.53 mm [.375 in]
	Housing Material	Thermoplastic
Dimensions	Wire Range	22 – 12AWG [.3 – 3 mm²]
	Length	153.95 mm [6.061 in]
Industry Standards	UL Flammability Rating	UL 94V-0
Packaging Features	Packaging Method	Package
	Packaging Quantity	40
Other	Comment	Do not order screw and captive clamp in combination with other top hardware., Other options available upon request, consult our Product Information Center.
Statement of Compliance	Statement of Compliance PDF	

Compatible Products

[> Contact Product Support](#)

Customers Also Bought

BARRIER STRIPS	BARRIER STRIPS	TERMINAL BLOCK HEADERS & RECEPTACLES	TERMINAL BLOCK HEADERS & RECEPTACLES
			
<p>6WWV-10-008=#6 TRIBARRIER TERM 6WWV-10-008</p>	<p>6WWV-08-008=#6 TRIBARRIER TERM 6WWV-08-008</p>	<p>12 POS 5.08MM R/A PLUG, TRM BLK 1-796635-2</p>	<p>13 POS 5.08MM R/A PLUG, TRM BLK 1-796635-3</p>

[Our Company](#)

[Events](#)

[TE News Center](#)

[Careers](#)

[Investors](#)


[Corporate Responsibility](#)

[Terms and Conditions of Sale](#)

[Distributors](#)

[Suppliers](#)

 [Email or Call Us](#)

 [Find Authorized Distributors](#)

 [What's New on TE.com](#)

 [Product FAQs](#)

Select Country & Language

[United States \(EN\)](#)

[Germany \(DE\)](#)

[China \(中文\)](#)

[Japan \(日本語\)](#)

[Afghanistan \(EN\)](#) ▼

[Find Your Country](#) ▼

[Terms of Use](#) | [Privacy](#) | [Cookie Policy](#) | [Accessibility](#) | [Site Map](#)



© 2017 TE Connectivity Corporation. All Rights Reserved