



COB connector Ø 50 mm for LED array 15.85 x 15.85 mm 47.319.2360.50



0,25 - 0,5 mm²



0,5 mm²

COB connector Ø 50 mm for LED array 15.85 x 15.85 mm 47.319.2360.50



DESCRIPTION

With integrated reflector interface
Screw mounting: for screws M3 and locking washer
Max. torque for screw fixing 0.5 Nm*
Strip length: 7-1 mm
Polarity of LED must be observed
Specifications of LED manufacturer must be observed
cURus: For limited applications
VDE-Reg. No. E289
*Please note the max torque of the COB manufacturer

Product name:	COB connector Ø 50 mm for LED array 15.85 x 15.85 mm
Mounting method 1:	Screw mount
Mounting method 2:	P2F fixing with 28.902.-102
Prefixation of COB:	No
Material:	Housing: PBT Contacts: CuSn
LED manufacturer:	Bridgelux, LUMILEDS
LED Typ:	Vesta (LES 9 mm), LUXEON Fusion Spot CSP Array
Conductor cross-section:	0.5 mm ²
Approval:	cURus
cULus file no.:	E-345385
Rating:	3A / 150 VDC
Pkg.:	504

Suitable for the following LED models:

LED Manufacturer	LED Type	More Information
Bridgelux	Vesta (LES 9 mm)	http://www.bridgelux.com
LUMILEDS	LUXEON Fusion Spot CSP Array	http://www.philipslumileds.com