



PRODUCT-DETAILS

# TY300-40-100

## CABLE TIE 40LB 11IN NATURAL NYL

---

### General Information

Extended Product Type	TY300-40-100
Product ID	7TCG054360R0241
EAN	5414363063841
Catalog Description	CABLE TIE 40LB 11IN NATURAL NYL
Long Description	Cable Tie, Natural Polyamide (Nylon 6.6) for Temperatures up to 85 Degrees Celsius (185 F) for Indoor Applications, UL/EN/CSA62275 Type 2/21 Rated for AH-2 Plenum, Length of 289.56mm (11.4 Inches), Width of 3.556mm (0.140 Inches), Thickness of 1.17mm (0.046 Inches), Tensile Strength Rating of 180 Newtons (40 Pounds), 100 Pack

---

### Ordering

EAN	5414363063841
Customs Tariff Number	3926909990

---

### Dimensions

Product Net Weight	.003 lb 1.361 g
--------------------	--------------------

---

### Container Information

Package Level 1 Units	100 piece
Package Level 1 Width	5 in 127 mm

Package Level 1 Height	1.7 in 43 mm
Package Level 1 Depth / Length	15 in 381 mm
Package Level 2 Units	1000 piece
Package Level 2 Width	7 in 178 mm
Package Level 2 Height	5 in 127 mm
Package Level 2 Depth / Length	16.7 in 424 mm

## Additional Information

Brand / Label	Ty-Fast
Bundle Diameter	3 in 76.2 mm
Color	Natural
Lock Type	Plastic Pawl
Material	Nylon/Polyamide 6.6
Number of Batteries	0
Product Name	PLASTIC CABLE TIE
Product Type	General Purpose
Standards	UL E49405
Tensile Strength	40 lb 180 N
Thickness	0.046 in 1.17 mm
UPC	786210918129

## Certificates and Declarations (Document Number)

Data Sheet, Technical Information	TY300-40-100
Declaration of Conformity - CE	9AKK107492A9843
Instructions and Manuals	TY300-40-100

## Classifications

ETIM 6	EC000046 - Cable tie
ETIM 7	EC000046 - Cable tie
UNSPSC	39121703
WEEE Category	Product Not in WEEE Scope
IDEA Granular Category Code (IGCC)	5034 >> Cable ties

## Categories

Low Voltage Products and Systems → Installation Products → Wire Management and Connectivity → Cable Ties