


5

4


3

2



1



Max wire  $\phi$  1,05 mm



A

							Dot.	Name	 All Dim. in mm Orig. Size DIN A 4	D-Sub, 25 poles, male, straight, turned solder buckets, holes	Maßstab/ Scale  1.5:1
						Detail.	18/07/01	AF			
						Insp.					
						Stand.					
09 67 025 5615 050	3.1 <sup>+0,1</sup>	S4									
09 67 025 5615	3.1 <sup>+0,1</sup>	PL2									
09 67 025 5604	3.1 <sup>+0,1</sup>	PL3	36189	08/11/10	SC						
			29700	18/07/01	AF						
Part number	$\phi$ hole	Performance level	Mod.	Dot.	Name	HARTING EURL F-95972 Paris			TB 09 67 025 56xx		Blatt/ Page 1 / 2
									Sub.		