

## Coaxial Cable Connector 11\_QMA-50-2-3/133\_N

### Description

Straight cable plug

Interface standards  
QMA QLF compliant



### Technical Data

#### Electrical Data

|                          |             |
|--------------------------|-------------|
| Impedance                | 50 $\Omega$ |
| Interface frequency max. | 18 GHz      |

#### Mechanical Data

|                |           |
|----------------|-----------|
| Centre contact | plugged   |
| Outer contact  | soldered  |
| Weight         | 0.0044 kg |

#### Environmental Data

|  |                 |
|--|-----------------|
| Operating temperature                                | -40 °C to 85 °C |
| 2011/65/EU (RoHS - including 2015/863 and 2017/2102) | compliant       |

#### Material Data

| Piece Parts    | Material                  | Surface Plating       |
|----------------|---------------------------|-----------------------|
| Centre contact | Copper Beryllium / Bronze | SUCOPRO Plating       |
| Outer contact  | Bronze                    | SUCOPLATE (R) Plating |
| Body           | Brass                     | SUCOPRO Plating       |
| Insulator      | PFA / PTFE                |                       |

### Related Documents

|                      |                |
|----------------------|----------------|
| Outline drawing      | DOU-00007073   |
| Catalogue drawing    | DCA-00007075   |
| Assembly instruction | DOC-0000179521 |

### Ordering Information

|                      |                      |
|----------------------|----------------------|
| Single package       | 11_QMA-50-2-3/133_NE |
| Bulk 100 pcs package | 11_QMA-50-2-3/133_NH |

### Additional Information

|                 |   |
|-----------------|---|
| Suitable cables | SUCOFORM_86, EZ_86_TP_M17, MULTIFLEX_86 |
|-----------------|---|

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[11\\_QMA-50-2-3/133\\_NH](#)