


PRST 4-PRKWT/LED P 4-07/XX

MICRO (M12) Double-Ended Cordset
4 Pole, 0.25mm², Male to Female Right Angle, LED P, PVC
Cable with Stainless Steel Coupling Nut



Technical Data

Material

Molded Body	PVC, Orange (male) PVC, Transparent (female)
Coupling Nut	Stainless Steel
Contacts	Brass, gold over nickel plated
Insert	PVC, Orange
O-Ring	EPDM (female)

Electrical

Current Rating	4A
Voltage Rating	10 - 30 VDC

Mechanical

Temperature	-25°C to +70°C
Protection	IP 69 K



Cable Specifications

Cable Jacket	PVC, Orange
Overall Diameter	5.0mm
Conductor	0.25mm ² , stranded

Features & Benefits

- 316LV4A stainless steel coupling nut
- PVC inserts, molded body and cable jacket
- EPDM O-ring for female connector
- IP 69 K rated
- PNP LED yellow/yellow/green

Pin Assignments



Part Number

PRST 4-PRKWT/LED P 4-07/2M
PRST 4-PRKWT/LED P 4-07/5M

Poles

4