

## Data sheet

Commercial Art.No.: 70.352.1635.0

Hood BAS GOT GC 16 M25 A0

revos BASIC size 16 hood with cable gland M25, top cable entry, double locking lever

1011011010001010010101101  
0100110110010110100101010  
101001101100111001010010  
101001101100111001010010  
101001101100111001010010  
1101010011011001011010010  
10101010010101101010011  
10101010010101101010011

**DIGITALIZATION  
IN PROGRESS**

Commercial Art.No.	70.352.1635.0
EAN	4015573617834
Order Unit	1

Certificates / Approvals



## Technical data

### General

Housing material	Aluminium
Color	Grey
Surface	With powder coating
Degree of protection (IP)	IP54
UV resistant	Yes
Inflammability class of insulation material acc. with UL94	Other
Operating temperature range min.	-40 °C
Operating temperature range max.	120 °C

### Model

Construction	16
Model	male
Locking mechanism	Double locking levers
Cable entry	Above
Type of cable	Gland nut
With cable screw gland	Yes
Thread size M	25
Thread size PG	
Hinged lid	No
EMC-version	No
Length	94 mm
Width	56 mm
Height	60 mm

### Classification

ECLASS 8.1	27440202
ETIM 7.0	EC000437
ETIM 6.0	EC000437

ETIM 5.0	EC000437
ETIM 4.0	EC000437
ETIM 3.0	EC000437