




### 3311 - FEMALE MANIFOLD BSP PARALLEL AND METRIC



**maximum working pressure** 20 bar  
2 MPa  
290 psi

**working temperature** -10 to 80 °C  
14 to 176 °F  
263 to 353 °K

**body** TREATED ALUMINIUM

Part Nb	C1	C2	H (mm)	H1 (mm)	H2 (mm)	K (mm)	L (mm)	L1 (mm)	N (mm)	ØT (mm)	 (kg)
3311 10 13 02	G1/4	G1/8	4.5	30	15	20	61	50	30	5	.075
3311 10 13 03	G1/4	G1/8	4.5	30	15	20	91	30	30	5	.112
3311 10 13 04	G1/4	G1/8	4.5	30	15	20	121	60	30	5	.165
3311 10 13 05	G1/4	G1/8	4.5	30	15	20	151	90	30	5	.209
3311 10 13 06	G1/4	G1/8	4.5	30	15	20	181	120	30	5	.244
3311 13 17 02	G3/8	G1/4	5.5	30	11	20	74	61	36	6.5	.076
3311 13 17 03	G3/8	G1/4	6	30	11	20	110	36	36	6.5	.121
3311 13 17 04	G3/8	G1/4	6	30	11	20	146	72	36	6.5	.147
3311 13 17 05	G3/8	G1/4	6	30	11	20	182	108	36	6.5	.212
3311 13 17 06	G3/8	G1/4	6	30	11	20	218	144	36	6.5	.22
3311 19 10 07	G1/8	M5x0,8	3.5	20	8.5	15	95	80	11	4.4	.057