

## Coaxial PCB Connector 92\_SMA-50-0-10/111\_N

### Description

Straight PCB jack

Interface Standards

IEC 60169-15\_MIL-STD-348A/310\_CECC 22110



### Technical Data

#### Electrical Data

Impedance 50 Ω  
Interface frequency max. 18 GHz

#### Mechanical Data

Board mounting type edge mount  
Weight 0.0044 kg

#### Environmental Data

Operating temperature -65 °C to 165 °C  
2011/65/EU (RoHS - including  
2015/863 and 2017/2102) compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	SUCOPRO Plating
Outer contact	Brass	SUCOPRO Plating
Body	Brass	SUCOPRO Plating
Insulator	PTFE (Polytetrafluoroethylene)	

### Related Documents

Outline drawing DOU-00088078  
Catalogue drawing DCA-00181402

### Ordering Information

Single package 92\_SMA-50-0-10/111\_NE

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[HUBER+SUHNER:](#)

[92\\_SMA-50-0-10/111\\_NE](#)