



DWD024K

701W 13MM PERCUSSION DRILL

Features and Benefits

- Low weight ensures the drill is easy to use and it reduces user fatigue
- Compact design enables comfortable use and allows access to tight spaces
- An excellent power to size ratio results in a powerful, durable drill in a compact size
- Trigger sensitive variable speed switch allows a user to drill slowly for precision accuracy when starting to drill a hole
- Rubber back handle increase comfort to the user in drilling and hammer drilling applications
- "Lock on" button gives the user the option to keep the machine continually running when doing repetitive operations

Standard Equipment

- Chuck key
- Multi-position side handle
- Heavy duty carrying case
- Depth stop

Specifications	
Power Input	701 Watts
Power Output	302 Watt
No Load Speed	0-2800 rpm
Blows per Minute	0-47600 bpm
Max Torque	8.6 Nm
Chuck Capacity	1.5-13 mm
Max. Drilling Capacity [Wood]	25 mm
Spindle Thread	1/2" x 20 U.N.F