

Model	DMDDY222
Product name	Car Battery Tester
Type	Digital
Current measurement range	100-2000CCA
Current measurement accuracy	±20CCA
Voltage measurement range	9-36V
Internal resistance measurement range	0-99.99 (mΩ)
Internal resistance measurement accuracy	±3%
Power supply voltage	12-24V (V)
Power	3AH - 200Ah
LCD screen size	3.2 inch
Voltage measure range	9-36V
Work temperature	zero 20~50°C