

Item no.: 260-106  
 Product description: 2-CONDUCTOR TERMINAL STRIP; LATERAL MARKING; 6 POLE; WITH FIXING FLANGE; WITH MOUNTING FEET 209-123 FOR TS 35; SIDE-ENTRY



Packing unit 50 pieces

Product group	9 (Std Chassis Mt Blocks)
pole count	6
Cross section from [mm <sup>2</sup> ]	0,08 mm <sup>2</sup>
Cross section to [mm <sup>2</sup> ]	1,5 mm <sup>2</sup>
Cross section from [AWG]	28 AWG
Cross section to [AWG]	16 AWG
Connection method	CAGE CLAMP®CONNECTION
Number of strands	5
Measured voltage EN	400 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	18 A
Weight	10,65 g
Color	grey
Wiring type	Side-entry
No. of connection Points	12
No. of potentials	6
Height	17 mm
Height	0,669 in
Width	44,5 mm
Width	1,752 in
Depth	25 mm



Strip length from	8 mm
Strip length to	9 mm
Strip length	0,33 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
260-106	ABS	04-HG476174-PDA	400	17,5	1,5
260-106	BBJ	B/12/696/03	400	17,5	1,5
260-106	BV	07436/C0	400	17,5	0,08-1,5
260-106	CCA	NL5800	400		1,5
260-106	CSA	18677-45	300	15	24-16
260-106	DEMKO	120039	400	17,5	1,5
260-106	Dep.MaE	CS4590N	300	20	
260-106	DNV	E7569	400	18	1,5
260-106	GL	17295-00HH	400	17,5	1,5
260-106	KEMA	2079569.01	400		1,5
260-106	KR	HMB05880-EL002	400	17,5	1,5
260-106	LR	92/20242(E4)	400	17,5	1,5
260-106	PRS	TE/1718/880590/08	400		1,5
260-106	RMR	11130002	400	17,5	1,5
260-106	SABS	751/82640			1,5
260-106	SEMKO	9408057	500		1,5
260-106	UL	E45172	300	10	28-16
260-106	UR	E45172	300	10	28-16

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected