

PIEZO BUZZER SPECIFICATIONS

- MODEL AW4B12TSP-453Z
- WITH “RoHS”
- ELECTRICAL SPECIFICATIONS:

| | | |
|---------------------------|-------|-----------------|
| Rated voltage | (VDC) | 12 |
| Operating Voltage | (VDC) | 3-18 |
| Max. consumption | (mA) | 10.0/12VDC |
| Min. sound pressure level | (dB) | 85dB/12VDC/10cm |
| Resonant frequency | (KHz) | 4.5 ± 1kHz |
| Operating temperature | (°C) | -20 - +70 |
| Storage temperature | (°C) | -30 - +80 |
| Weight | (g) | 1.0 |
| Case material and color | | PBT/BLACK |
| Dimension | (mm) | See drawing |

- APPEARANCE AND DIMENSIONS:

