


coupling socket KD4-1/4-A-R

Part number: 531694

FESTO

Self-closing with non-return valve



Data sheet

Feature	Value
Nominal size	8 mm
Operating pressure complete temperature range	-0.95 ... 12 bar
Standard nominal flow rate	765 l/min
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation possible
Corrosion resistance classification CRC	1 - Low corrosion stress
Ambient temperature	-10 ... 80 °C
Nominal tightening torque	9.5 Nm
Tolerance for nominal tightening torque	± 15 %
Product weight	58 g
Pneumatic connection, port 1	Male thread G1/4
Materials note	Conforms to RoHS