

PICCOLO PC F 85 G



Sample photo

Order symbol: PC F 85 G
Product nbr: 8724312
Description: Enclosure, PC
Remarks: Grey cover

EAN: 6418074002211
EI. number:
 Finland: 3423415
 Electric No. 8212001637
 Denmark:
 Electric No. Italy: 7201045
 Electric No. Sweden: 2536823

Including: Base with screws for mounting plate, cover with PUR gasket and polyamide cover screws.

| Dimensions: | Length | Width | Height | Accessories: |
|-------------|--------|-------|--------|--|
| mm: | 230 | 80 | 85 | FM-3 DIN-35 Mounting rail |
| inch: | 9.1 | 3.1 | 3.3 | FP 22040 Wall fastening lug (2 pcs) |

| Materials: | Rating: |
|---|--|
| Material: Polycarbonate | Ingress Protection (EN 60529): IP66/IP67 |
| Base colour: RAL 7035 -light grey | Impact Resistance (EN 62262): IK08 |
| Cover screws material: Polyamide | Electrical insulation: Totally insulated |
| Cover colour: RAL 7035 -light grey | Halogen free (DIN/VDE 0472, Part 815): 1 |
| Cover screws colour: Grey | UV resistance: UL 508 |
| Gasket material: Polyurethane | Flammability Rating: UL 746C 5" |
| | Glow Wire Test (IEC 695-2-1) °C: 960 |
| | NEMA Class: NEMA 1, 4X, 6, 12, 13 |

| Temperatures: | Certificates: |
|--|---------------|
| Temperature °C (short term): -40 ... 120 °C | SGS Fimko |
| Temperature °C (continuous): -40 ... 80 °C | |
| Temperature °F (short term): -40 ... 250 °F | |
| Temperature °F (continuous): -40 ... 175 °F | |

| Accessories: |
|--|
| F-MP Mounting plate |

