



Cable Ties Polyamide 6.6 standard T30R



T-Series in PA66 black, Article number: 111-03012

- Available in a wide range of material and sizes
- Made from 100% high quality plastic, allows for good recycling
- Inside serration for a strong hold onto bundles
- Easy application either manually or with a processing tool
- Simply to insert due to bent tail

These cable ties are used for routing, bundling and securing of cables, pipes and hoses.



Base Data

| | |
|-------------------------------|-----------------------------------|
| Application Tool | MK3SP, MK3PNSP2, MK7P, MK7, MK20 |
| Colour | Black (BK) |
| Fixation Method (FF) | None |
| Identification Plate Position | none |
| Product Family | T-Series in PA66 black |
| Product Group | Cable Ties Polyamide 6.6 standard |
| Releasable Closure (Yes/No) | No |
| Tie Closure | plastic pawl |

Product Dimensions

| | |
|-----------------------------|---------|
| Bundle Ø max. | 35.0 mm |
| Bundle Ø max. (imperial) | 1.38 " |
| Bundle Ø min. | 1.5 mm |
| Bundle Ø min. (imperial) | 0.06 " |
| Length (L) | 150 mm |
| Length (L) (imperial) | 5.9 " |
| Min. Tensile Strength (lbs) | 30 lbs |
| Min.Tensile Strength (N) | 135 N |
| Width (W) | 3.5 mm |
| Width (W) (imperial) | 0.14 " |

Logistic and Packaging

| | |
|--------------|---------------|
| EAN code | 5022660018787 |
| Pack Cont. | 500 |
| Quantity per | Bag |

Material and Specifications

| | |
|-----------------------|------------------------------------|
| Flammability | UL94 V2 |
| Material | PA66 |
| Material | Polyamide 6.6 (PA66) |
| Operating Temperature | -40 °C to +85 °C, (+105 °C, 500 h) |