



RECOMMENDED PCB LAYOUT  
TOLERANCE: ±0.05

REMARKS:

附注:

1. MATERIAL:

材料:

1.1 HOUSING: THERMOPLASTIC

本体: 热塑性塑胶料

COLOR: WHITE

颜色: 白色

1.2 COVER: THERMOPLASTIC

盖子: 热塑性塑胶料

COLOR: WHITE

颜色: 白色

1.2 CONTACT: COPPER ALLOY

接触件: 铜合金

2. PLATING:

表面处理:

2.1 CONTACT:

PLATED GOLD OVER NICKEL AND 50u" MIN.

接触件: 镀镍底50u" 以上, 在镍表面镀金

Technical Speciality

技术特性

Rated Voltage: 50V AC/DC Max

额定电压: 50V AC/DC Max

Current Rating: 1.0A Max

额定电流: 1.0A Max

Insulation Resistance: 1000MΩ Min

绝缘电阻: 1000MΩ Min

Contact Resistance: 100mΩ Max

接触电阻: 100mΩ Max

Withstand Voltage:

耐压: 500V AC/minute

Operating Temperature: -25°C ~ +85°C

工作温度: -40°C ~ +85°C



深圳市华宇创精密电子有限公司

TOLERANCE: X.X ±0.30 X.XX ±0.25 X.XXX ±0.15 X' ±2' X.X' ±0.5'	DRAWN BY : 陈一鸣	DATE : 2014-02-23	PART NAME: SIM 6P 全塑掀盖 无柱
	CHECKED BY: 马跃	DATE : 2014-02-23	PART NO. : HYC268-SIM06-280B
UNIT: mm [inch] SCALE: 1:1 SIZE: A4	APPROVED BY: 邱敏	DATE : 2014-02-23	DRAW NO. : HYC-SIM2011041520
			SHEET NO. : 1 OF 1