

Wiha SoftFinish®.


The specialist for dry and general applications.



The right tool at a glance,
thanks to the printed screw symbol
on the handle end.

The Wiha SoftFinish® zone features a solid moulded core with soft outer grip. This requires less force, yet achieves 40% more torque than conventional handles. The handle is shaped to fit comfortably in the hand, providing maximum torque forces in dry and general working conditions.

If a stuck screw has to be loosened, a precise hammer blow can be applied to the solid steel cap. Due to the hex blade extending through the handle to the steel cap, there is no loss of impact energy.



The solid steel cap at the end of the SoftFinish® handle enables controlled hammer blows, for example, when loosening a tight screw.

Due to the solid steel cap and hex blade extending through the handle, there is no loss of impact energy when a precise hammer blow is applied.



Thermoplastic elastomer tolerates high loads and feels soft and pleasant to the touch.

Blade with hex bolster for wrenches to use on particularly tight screws.



Wiha SoftFinish®.

- Multi-component SoftFinish® handle provides maximum user comfort
- Ergonomically perfect handle design
- Printed screw symbol on handle end for fast identification
- Available in versions with round blade, hex blade or hex blade with solid steel cap
- Blade made of high quality CVM-steel, through-hardened and chrome plated
- Wiha ChromTop®-finish on tip for a perfect fit every time

For slotted screws.



302 SoftFinish® slotted cabinet screwdriver.

Round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN 5265, DIN ISO 2380.

Application: Especially for dry and general applications.

Order-No.	⌀	→	⊖	●	→	→	→
00684 6	2.0•	65	0.4	2.0	169	23	10
00685 3	2.5	75	0.4	2.5	179	23	10
00686 0	3.0•	80	0.5	3.0	184	23	10
00687 7	3.0	100	0.5	3.0	204	23	10
00689 1	3.0•	150	0.5	3.0	254	23	10
00690 7	3.0•	200	0.5	3.0	304	23	10
32383 7	3.0	300	0.5	3.0	404	23	5
00691 4	3.5	100	0.6	3.5	204	23	10
26931 9	3.5•	200	0.5	3.5	304	23	10
00692 1	4.0	100	0.8	4.0	211	30	10
00694 5	4.0•	150	0.8	4.0	261	30	10
00695 2	4.0•	200	0.8	4.0	311	30	10
00696 9	4.0•	300	0.8	4.0	411	30	5
27753 6	4.5•	80	0.8	4.5	191	30	10
00697 6	4.5•	125	0.8	4.5	236	30	10
00698 3	5.5	125	1.0	5.5	236	30	10
00700 3	5.5	150	1.0	5.5	261	30	10
00701 0	5.5•	200	1.0	5.5	311	30	10
00702 7	5.5•	300	1.0	5.5	411	30	5
32384 4	6.0	300	1.0	6.0	418	36	5

• Additional dimension. Non-DIN size.



302 SoftFinish® slotted workshop screwdriver.

Round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN 5265, DIN ISO 2380.

Application: Especially for dry and general applications.

Order-No.	⌀	→	⊖	●	→	→	→
27754 3	6.0	100	1.0	5.5	218	36	10
27755 0	6.0	150	1.0	5.5	268	36	10
00704 1	6.5	100	1.2	6.0	218	36	10
00703 4	6.5	150	1.2	6.0	268	36	10
00706 5	6.5•	200	1.2	6.0	318	36	5
00708 9	8.0	150	1.2	7.0	274	41	10
00707 2	8.0	175	1.2	7.0	299	41	5
00709 6	8.0	175	1.6	7.0	299	41	5
32399 8	8.0	300	1.2	7.0	424	41	5
00711 9	10.0	200	1.6	8.0	324	41	5
32400 1	10.0	300	1.6	8.0	424	41	5
00712 6	12.0	250	2.0	8.0	374	41	5
00713 3	14.0	250	2.5	11.0	374	41	5

• Additional dimension. Non-DIN size.

For slotted screws.



308 SoftFinish® slotted screwdriver.

Hex blade with hex bolster.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN 5265, DIN ISO 2380.

Application: Especially for dry and general applications.

Order-No.	⌀	→	⊖	●	⊖	→	→	→
00731 7	3.5	75	0.6	4.0	-	186	30	10
00732 4	4.5•	90	0.8	4.0	-	201	30	10
00733 1	5.5	100	1.0	5.0	8	213	36	10
00734 8	6.5	125	1.2	6.0	10	238	36	10
00735 5	7.0•	125	1.1	6.0	10	238	36	10
00736 2	8.0	150	1.2	8.0	13	268	41	10
00737 9	9.0•	150	1.4	8.0	13	268	41	10
00738 6	10.0	175	1.6	8.0	13	293	41	5
00739 3	12.0	200	2.0	10.0	16	318	41	5
00740 9	14.0	250	2.5	10.0	16	368	41	5

• Additional dimension. Non-DIN size.



530 SoftFinish® slotted screwdriver.

Hex blade with hex bolster, solid steel cap.

Order-No.	⌀	→	⊖	●	⊖	→	→	→
03223 4	3.5	75	0.6	4.0	-	186	30	10
03224 1	4.5•	90	0.8	4.0	-	201	30	10
03225 8	5.5	100	1.0	5.0	8	213	36	10
03226 5	6.5	125	1.2	6.0	10	238	36	10
03228 9	8.0	150	1.2	8.0	13	271	41	5
03230 2	10.0	175	1.6	8.0	13	296	41	5
03231 9	12.0	200	2.0	10.0	16	321	41	5
03232 6	14.0	250	2.5	10.0	16	371	41	5

• Additional dimension. Non-DIN size.



398 SoftFinish® slotted screw-holding screwdriver.

Clamping sleeve holds the screw.

Blade: Chrome-vanadium steel, through hardened, black-finish.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: For setting and turning screws in difficult to access areas.

Order-No.	⌀	→	⊖	→	→	→
32867 2	2.5	75	0.4	186	30	5
32868 9	3.0	100	0.5	211	30	5
32869 6	4.0	125	0.8	243	36	5
32870 2	5.0	150	1.0	268	36	5
32871 9	6.0	175	1.2	293	36	5



Wiha SoftFinish®.

The specialist for dry and general applications.

For Phillips screws.



311 SoftFinish® Phillips screwdriver.
Round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: ISO 8764.

Application: Especially for dry and general applications.

Order-No.	⊕	→	●	○	←	→	→
00754 6	PH0	60	3.0	164	23		10
27756 7	PH0	100	3.0	204	23		10
00756 0	PH1	80	4.5	191	30		10
27757 4	PH1	100	4.5	211	30		10
00757 7	PH1•	200	4.5	311	30		10
03738 3	PH1•	300	4.5	411	30		5
00759 1	PH2	100	6.0	218	36		10
27758 1	PH2	150	6.0	268	36		10
00760 7	PH2•	200	6.0	318	36		5
03739 0	PH2•	300	6.0	418	36		5
00762 1	PH3	150	8.0	274	41		10
00763 8	PH4	200	10.0	324	41		5

• Additional dimension. Non-DIN size.



312 SoftFinish® Phillips screwdriver.
Hex blade with hex bolster.

Order-No.	⊕	→	●	○	←	→	→
00764 5	PH1	80	5.0	8	186	30	10
00765 2	PH2	100	6.0	10	213	36	10
00766 9	PH3	150	8.0	13	268	41	10
00767 6	PH4	200	10.0	16	318	41	5



531 SoftFinish® Phillips screwdriver.
Hex blade with hex bolster, solid steel cap.

Order-No.	⊕	→	●	○	←	→	→
03237 1	PH1	80	5.0	8	186	30	10
03238 8	PH2	100	6.0	10	213	36	10
03239 5	PH3	150	8.0	13	268	41	10



397 SoftFinish® Phillips screw-holding screwdriver.
Clamping sleeve holds the screw.

Blade: Chrome-vanadium steel, through hardened, black-finish.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: For setting and turning screws in difficult to access areas.

Order-No.	⊕	→	→	→	→
32406 3	PH0	100	211	30	5
32404 9	PH1	125	236	36	5
32405 6	PH2	175	286	36	5

For Pozidriv screws.



313 SoftFinish® Pozidriv screwdriver.
Round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: ISO 8764.

Application: Especially for dry and general applications.

Order-No.	⊕	→	●	→	→	→
00768 3	PZ0	60	3.0	164	23	10
00770 6	PZ1	80	4.5	191	30	10
26454 3	PZ1	300	4.5	411	30	5
00772 0	PZ2	100	6.0	218	36	10
26455 0	PZ2	300	6.0	418	36	5
00774 4	PZ3	150	8.0	274	41	10



314 SoftFinish® Pozidriv screwdriver.
Hex blade with hex bolster.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: ISO 8764.

Application: Especially for dry and general applications.

Order-No.	⊕	→	●	○	←	→	→
00776 8	PZ1	80	5.0	8	186	30	10
00777 5	PZ2	100	6.0	10	213	36	10
00778 2	PZ3	150	8.0	13	268	41	10
00779 9	PZ4	200	10.0	16	318	41	5



532 SoftFinish® Pozidriv screwdriver.
Hex blade with hex bolster, solid steel cap.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: ISO 8764.

Application: Especially for dry and general applications.

Order-No.	⊕	→	●	○	←	→	→
03245 6	PZ1	80	5.0	8	186	30	10
03246 3	PZ2	100	6.0	10	213	36	10
03247 0	PZ3	150	8.0	13	271	41	10

Stubby-screwdriver.



302 SoftFinish® slotted screwdriver.
Short round blade.


Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha Stubby SoftFinish® handle, multi-component with roll-off protection.

Standards: DIN 5265, DIN ISO 2380, handle acc. to DIN 5268 - style K.

Application: For working in confined spaces.

Order-No.	①	→	→	●	→	→	→
26964 7	4.0	25	0.8	4.0	81	34	10
26965 4	5.5	25	1.0	5.5	81	34	10
26966 1	6.5	25	1.2	6.5	81	34	10
26967 8	8.0	25	1.2	8.0	81	34	10



311 SoftFinish® Phillips screwdriver.
Short round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha Stubby SoftFinish® handle, multi-component with roll-off protection.

Standards: ISO 8764, handle acc. to DIN 5268 - style K.

Application: For working in confined spaces.

Order-No.	⊕	→	●	→	→	→
26968 5	PH1	25	4.5	81	34	10
26969 2	PH2	25	6.0	81	34	10
26970 8	PH3	25	8.0	81	34	10



313 SoftFinish® Pozidriv screwdriver.
Short round blade.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha Stubby SoftFinish® handle, multi-component with roll-off protection.

Standards: ISO 8764, handle acc. to DIN 5268 - style K.

Application: For working in confined spaces.

Order-No.	⊕	→	●	→	→	→
26971 5	PZ1	25	4.5	81	34	10
26972 2	PZ2	25	6.0	81	34	10
26973 9	PZ3	25	8.0	81	34	10

Screwdriver with mm scale.



NEW
3021 SoftFinish® slotted screwdriver.
Round blade with lasered millimetre scale from 30 to 110 mm.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN 7437, DIN 5264, DIN ISO 2380.

Application: Especially for dry and general applications.

Extra: High-contrast millimetre scale permanently lasered on to the blade for depth, inner, outer and step measurements between 30 to 110 mm.

Order-No.	①	→	→	●	→	→	→
35397 1	5.5	125	1.0	5.5	236	30	10



NEW
3111 SoftFinish® Phillips screwdriver.
Round blade with lasered millimetre scale from 20 to 90 mm.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN 7437, DIN 5264, DIN ISO 2380.

Application: Especially for dry and general applications.

Extra: High-contrast millimetre scale permanently lasered on to the blade for depth, inner, outer and step measurements between 20 to 90 mm.

Order-No.	⊕	→	●	→	→	→
35398 8	PH2	100	6.0	218	36	10



NEW
3131 SoftFinish® Pozidriv screwdriver.
Round blade with lasered millimetre scale from 20 to 90 mm.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Standards: DIN 7437, DIN 5264, DIN ISO 2380.

Application: Especially for dry and general applications.

Extra: High-contrast millimetre scale permanently lasered on to the blade for depth, inner, outer and step measurements between 20 to 90 mm.

Order-No.	⊕	→	●	→	→	→
35399 5	PZ2	100	6.0	218	36	10



► See VDE tools, page 228 – 237

Wiha SoftFinish®.

The specialist for dry and general applications.

For TORX® screws.



362 SoftFinish® TORX® screwdriver.
Round blade.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: Especially for dry and general applications.

Order-No.	Blade	Length	Width	Tip	Tip	Tip
26259 4	T3	60	2.5	164	23	10
26260 0	T4	60	2.5	164	23	10
01285 4	T5	60	2.5	164	23	10
01286 1	T6	60	3.5	164	23	10
01287 8	T7	60	3.5	164	23	10
01288 5	T8	60	3.5	164	23	10
01289 2	T9	60	4.0	171	30	10
01290 8	T10	80	4.0	191	30	10
01291 5	T15	80	4.0	191	30	10
01292 2	T20	100	4.0	218	36	10
01293 9	T25	100	4.5	218	36	10
01294 6	T27	115	5.5	233	36	10
01295 3	T30	115	6.0	233	36	10
01296 0	T40	130	7.0	254	41	10
01297 7	T45	130	8.0	254	41	5



362BE SoftFinish® TORX® ball end screwdriver.
Hex blade.
 Blade: High-quality chrome-molybdenum steel, through-hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: For all hard-to-reach TORX® screws.
 Extra: The TORX® ball end enables fastening and unfastening at an angle of up to 25°.
 With elongated TORX® profile behind ball end.

Order-No.	Blade	Length	Width	Tip	Tip	Tip	
32250 2	T9	60	7/64	2.8	164	23	10
32251 9	T10	60	1/8	3.2	184	23	10
32252 6	T15	80	9/64	3.6	191	30	10
32253 3	T20	80	5/32	4.0	211	30	10
32254 0	T25	100	3/16	4.8	218	36	10
32255 7	T27	115	7/32	5.6	233	36	10
32256 4	T30	115	1/4	6.4	233	36	10

For TORX® and TORX® tamper resistant screws.



362R SoftFinish® TORX® MagicSpring® screwdriver.
Retaining spring holds TORX® screws in place.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: For setting and tightening TORX® screws in difficult to access areas.

Order-No.	Blade	Length	Width	Tip	Tip	Tip
27736 9	T6	60	3.5	164	23	10
27737 6	T7	60	3.5	164	23	10
27738 3	T8	60	3.5	164	23	10
27739 0	T9	60	4.0	171	30	10
27740 6	T10	80	4.0	191	30	10
27741 3	T15	80	4.0	191	30	10
27742 0	T20	100	4.0	218	36	10
27743 7	T25	100	4.5	218	36	10
27811 3	T27	115	5.5	233	36	10
27744 4	T30	115	6.0	233	36	10
27745 1	T40	130	7.0	254	41	10



362TR SoftFinish® TORX® Tamper Resistant screwdriver.
With borehole in the blade tip.
For TORX® screws with locking pin.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 With borehole in the blade tip.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Order-No.	Blade	Length	Width	Tip	Tip	Tip
03106 0	T7H	60	3.5	164	23	10
03107 7	T8H	60	3.5	164	23	10
03108 4	T9H	60	4.0	171	30	10
26456 7	T9H	300	4.0	411	30	5
01300 4	T10H	80	4.0	191	30	10
26457 4	T10H	300	4.0	411	30	5
01301 1	T15H	80	4.0	191	30	10
26458 1	T15H	300	4.0	411	30	5
01302 8	T20H	100	4.0	211	30	10
28005 5	T20H	300	4.0	411	30	5
01303 5	T25H	100	4.5	211	30	10
01304 2	T27H	115	5.5	233	36	10
01305 9	T30H	115	6.0	233	36	10
01306 6	T40H	130	7.0	254	41	10

For TORX PLUS® and Allen screws.



362IP SoftFinish® TORX PLUS® screwdriver.
Round blade.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Order-No.	Blade	Length	Width	Tip	Tip	Tip
26091 0	6IP	60	3.5	164	23	10
26093 4	7IP	60	3.5	164	23	10
26095 8	8IP	60	3.5	164	23	10
26097 2	9IP	60	4.0	171	30	10
26099 6	10IP	80	4.0	191	30	10
26101 6	15IP	80	4.0	191	30	10
26103 0	20IP	100	4.0	218	36	10
26105 4	25IP	100	4.5	218	36	10
26107 8	27IP	115	5.5	233	36	10
26109 2	30IP	115	6.0	233	36	10
26111 5	40IP	130	7.0	254	41	10



362RIP SoftFinish® TORX PLUS® MagicSpring® screwdriver.
Retaining spring holds TORX PLUS® screws in place.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: For setting and tightening TORX PLUS® screws in hard to reach areas.

Order-No.	Blade	Length	Width	Tip	Tip	Tip
28760 3	6IP	60	3.5	164	23	10
28761 0	7IP	60	3.5	164	23	10
28762 7	8IP	60	3.5	164	23	10
28763 4	9IP	60	4.0	171	30	10
28764 1	10IP	80	4.0	191	30	10
28765 8	15IP	80	4.0	191	30	10
28766 5	20IP	100	4.0	218	36	10
28767 2	25IP	100	4.5	218	36	10
28768 9	27IP	115	5.5	233	36	10
28769 6	30IP	115	6.0	233	36	10
28770 2	40IP	130	7.0	254	41	10



356 SoftFinish® hex screwdriver.
Hex blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Order-No.	Blade	Length	Width	Tip	Tip	Tip
32264 9	1.5	60	164	23		10
32265 6	2.0	60	164	23		10
26190 0	2.5	75	179	23		10
26191 7	3	75	179	23		10
26192 4	4	75	186	30		10
26193 1	5	75	186	30		10
26194 8	6	100	218	36		10
26195 5	8	100	218	36		10

For hex socket screws.



367 SoftFinish® ball end hex screwdriver.
Hex blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: For all screws that are difficult to access.
 Extra: The ball end enables the user to work at angles up to 25°.

Order-No.	Blade	Length	Width	Tip	Tip	Tip
26303 4	1.5	75	179	23		10
26304 1	2	100	204	23		10
26305 8	2.5	100	204	23		10
26328 7	3	100	204	23		10
26329 4	4	100	211	30		10
26330 0	5	100	211	30		10
26331 7	6	125	243	36		10
26332 4	8	150	268	36		10
26333 1	10	150	271	41		5
26307 2	12	150	271	41		5



367R SoftFinish® MagicRing® ball end hex screwdriver.
Ring made of spring steel holds hex screws in place.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: For setting and turning screws in difficult to access areas.
 Extra: The ball end enables the user to work at angles up to 25°.

Order-No.	Blade	Length	Width	Tip	Tip	Tip
26077 4	3	100	204	23		10
26079 8	4	100	211	30		10
26081 1	5	100	211	30		10
26083 5	6	125	243	36		10
26085 9	8	150	268	36		10
26087 3	10	150	271	41		5



357 SoftFinish® offset hex screwdriver.
Hex blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: Ideal for high-torque applications, e.g. in workshops.

Order-No.	Blade	Length	Width	Tip	Tip	Tip
26230 3	3	35	20	139	23	10
26231 0	4	40	25	151	30	10
26232 7	5	45	28	156	30	10
26233 4	6	50	32	168	36	10
26234 1	8	60	36	178	36	10
26235 8	10	70	40	199	41	10



► See VDE tools, page 228 – 237

Wiha SoftFinish®.

The specialist for dry and general applications.

For hex nuts.



341 SoftFinish® hex nut driver.
Round blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Deep drawn socket.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Standards: DIN 3125.
 Application: Especially for dry and general applications.

Order-No.	Ø	→	←	→	←	→	←
01018 8	4	125	236	30	6.9		10
01020 1	5	125	236	30	7.9		10
01021 8	5.5	125	236	30	7.9		10
01022 5	6	125	236	30	8.9		10
01023 2	7	125	243	36	10.9		10
01024 9	8	125	243	36	11.9		10
01025 6	9	125	243	36	12.9		10
01026 3	10	125	243	36	14.4		10
01027 0	11	125	249	41	15.9		5
01028 7	12	125	249	41	16.9		5
01029 4	13	125	249	41	18.4		5
01030 0	14	125	249	41	19.4		5
01031 7	15	125	249	41	21.9		5
01032 4	16	125	249	41	21.9		5
01033 1	17	125	249	41	23.4		5



347 SoftFinish® hex nut driver.
Round blade with hex bolster.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Deep drawn socket.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Standards: DIN 3125.
 Application: Especially for dry and general applications.

Order-No.	Ø	→	←	→	←	→	←
01092 8	7	125	10	238	36	11.0	10
01093 5	8	125	10	238	36	12.0	10
01094 2	9	125	10	238	36	13.0	10
01095 9	10	125	10	238	36	14.5	10
01096 6	11	125	13	246	41	16.0	5
01097 3	12	125	13	246	41	17.0	5
01098 0	13	125	13	246	41	19.0	5

347 Zoll SoftFinish® hex nut driver. Inch sizes.

Round blade with hex bolster.
 Blade: Chrome-vanadium steel, through hardened, nickel-plated.
 Deep drawn socket.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: Especially for dry and general applications.

Order-No.	Ø	→	←	→	←	mm	→	←
02836 7	3/16	125	10	231	30	4.76	8	10
02837 4	1/4	125	10	238	36	6.35	10	10
02838 1	5/16	125	10	238	36	7.94	12	10
02839 8	3/8	125	10	238	36	9.53	14	10
02840 4	7/16	125	13	246	41	11.11	16	10
02841 1	1/2	125	13	246	41	12.70	19	10

For hex and triangular nuts.



343 SoftFinish® hex nut driver.
Short round blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Deep drawn socket.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: For working in confined spaces.

Order-No.	Ø	→	←	→	←	→	←
01076 8	5.5	65	176	30	8		10
01077 5	6	65	176	30	9		10
01078 2	7	65	183	36	11		10
01079 9	8	65	183	36	12		10
01081 2	10	65	183	36	14		10



372 SoftFinish® hex nut driver.
Flexible shaft for hard to reach areas.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: E.g. for tightening and loosening adjustable hose clamps.

Order-No.	Ø	→	←	→	←	→	←
01435 3	5	150	261	30	8		10
01436 0	5.5	150	261	30	8		10
01437 7	6	150	261	30	9		10
01438 4	7	150	268	36	11		10
01439 1	8	150	268	36	12		10
01440 7	10	175	293	41	14		10
01443 8	13	175	293	41	19		5



344 SoftFinish® triangular nut driver.
Round blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Standards: DIN 22416.
 Application: For triangular screws DIN 22424 and triangular nuts DIN 22425.

Order-No.	Ø	→	←	→	←	→	←
26212 9	M4	125	6.8	236	30	11	10
26213 6	M5	125	8.3	236	30	13	10
26216 7	M6	125	10.05	236	30	16	10
26214 3	M8	125	12.05	243	36	18	10
26217 4	M10	125	15.05	243	36	22	10
26218 1	M12	125	16.55	249	41	24	10

For slotted nuts. Sets with round blades.



305 SoftFinish® slotted nut driver.
Round blade.
 Blade: Chrome-vanadium steel, through hardened, chrome-plated.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Standards: DIN 3125.
 Application: For nuts DIN 546.

Order-No.	Ø	→	←	→	←	→	←
32364 6	M1.7	80	0.5	4.0	184	23	5
32363 9	M2	80	1.0	4.5	184	23	5
32362 2	M2.3	90	1.0	5.0	201	30	5
32361 5	M2.6	90	1.2	5.5	201	30	5
32360 8	M3	100	1.2	6.0	211	30	5
32358 5	M3.5	100	1.4	7.0	218	36	5
32359 2	M4	100	1.4	8.0	218	36	5
32357 8	M5	125	2.0	10.0	243	36	5
32356 1	M6	125	2.5	11.0	243	36	5
32355 4	M8	150	3.0	14.0	274	41	5
32354 7	M10	150	3.5	18.0	274	41	5



302 HK6 SO SoftFinish® slotted/ Phillips screwdriver set, 6 pcs.
Round blades.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: Especially for dry and general applications.

Order-No.	Series	→	←		
07152 3	302 HK6 SO		1		
⓪	302	3.5x100	4.5x125	5.5x150	6.5x150
⊕	311	PH1x80	PH2x100		



302 ZK6 SO SoftFinish® slotted/ Pozidriv screwdriver set, 6 pcs.
Round blades.

Order-No.	Series	→	←		
07153 0	302 ZK6 SO		1		
⓪	302	3.5x100	4.5x125	5.5x150	6.5x150
⊕	313	PZ1x80	PZ2x100		

Sets with round blades.



311 K6 SoftFinish® Phillips/ Pozidriv screwdriver set, 6 pcs.
Round blades.
 Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.
 Wiha ChromTop® finish on tip for a perfect fit every time.
 Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.
 Application: Especially for dry and general applications.

Order-No.	Series	→	←	
26146 7	311 K6		1	
⊕	311	PH1x80	PH2x100	PH3x150
⊕	313	PZ1x80	PZ2x100	PZ3x150



302 HK6 01 SoftFinish® slotted/Phillips/ Pozidriv screwdriver set, 6 pcs.
Round blades.

Order-No.	Series	→	←	
26113 9	302 HK6 01		1	
⓪	302	4.0x100	5.5x125	6.5x150
⊕	311	PH1x80	PH2x100	
⊕	313	PZ2x100		

Wiha SoftFinish®.

The specialist for dry and general applications.



► See VDE tools,
page 228 – 237

Sets with hex blades.



308 HK6 SoftFinish® slotted/ Phillips screwdriver set, 6 pcs. Hex blades with hex bolster.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: Especially for dry and general applications.

Order-No.	Series					
21248 3	308 HK6					1
⓪	308	3.5x75	4.5x90	5.5x100	7.0x125	
⊕	312	PH1x80	PH2x100			



308 ZK6 SoftFinish® slotted/ Pozidriv screwdriver set, 6 pcs. Hex blades with hex bolster.

Order-No.	Series					
21249 0	308 ZK6					1
⓪	308	3.5x75	4.5x90	5.5x100	7.0x125	
⊕	314	PZ1x80	PZ2x100			

Sets with steel caps. Nut driver set.



530 HK6 SoftFinish® slotted/ Phillips screwdriver set, 6 pcs. Hex blades with hex bolster, solid steel cap.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: Especially for dry and general applications.

Order-No.	Series					
21250 6	530 HK6					1
⓪	530	3.5x75	4.5x90	5.5x100	6.5x125	
⊕	531	PH1x80	PH2x100			



530 ZK6 SoftFinish® slotted/ Pozidriv screwdriver set, 6 pcs. Hex blades with hex bolster, solid steel cap.

Order-No.	Series					
21251 3	530 ZK6					1
⓪	530	3.5x75	4.5x90	5.5x100	6.5x125	
⊕	532	PZ1x80	PZ2x100			



341 K5 SoftFinish® hex nut driver set, 5 pcs. Round blades.

Blade: Chrome-vanadium steel, through hardened, chrome-plated. Deep drawn socket.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: Especially for dry and general applications.

Order-No.	Series				
01034 8	341 K5				1
⊙	341	5.5x125	7x125	8x125	
		10x125	13x125		

TORX® sets.



362 K6 S0 SoftFinish® TORX® screwdriver set, 6 pcs. Round blades.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: Especially for dry and general applications.

Order-No.	Series					
07155 4	362 K6 S0					1
⊙	362	T10x80	T15x80	T20x100		
		T25x100	T30x115	T40x130		



362 K7 SoftFinish® TORX® screwdriver set, 7 pcs. Round blades.

Order-No.	Series					
01299 1	362 K7					1
⊙	362	T8x60	T9x60	T10x80	T15x80	
		T20x100	T25x100	T30x115		



362BE K6 SoftFinish® TORX® ball end screwdriver set, 6 pcs. Hex blade.

Blade: High-quality chrome-molybdenum steel, through-hardened, chrome-plated. Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: For all hard-to-reach TORX® screws.

Extra: The TORX® ball end enables fastening and unfastening at an angle of up to 25°.

With elongated TORX® profile behind ball end.

Order-No.	Series				
32249 6	362BE K6				1
⊙	362BE	T9x60	T10x60	T15x80	
		T20x80	T25x100	T30x115	

Sets.



362R K6 S0 SoftFinish® TORX® MagicSpring® screwdriver set, 6 pcs. Retaining spring holds TORX® screws in place.

Blade: High quality chrome-vanadium-molybdenum steel, through hardened, chrome-plated.

Wiha ChromTop® finish on tip for a perfect fit every time.

Handle: Ergonomic Wiha SoftFinish® multi-component handle with roll-off protection.

Application: For setting and tightening TORX® screws in difficult to access areas.

Order-No.	Series					
27746 8	362R K6 S0					1
⊙	362R	T10x80	T15x80	T20x100		
		T25x100	T30x115	T40x130		



362 K6 01 SoftFinish® Pozidriv/ TORX® screwdriver set, 6 pcs. Round blades.

Order-No.	Series					
26114 6	362 K6 01					1
⊕	313	PZ1x80	PZ2x100			
⊙	362	T10x80	T15x80	T20x100	T25x100	



362TR K6 SoftFinish® TORX® Tamper Resistant screwdriver set, 6 pcs. For TORX® screws with locking pin.

Order-No.	Series					
24506 1	362TR K6					1
⊙	362TR	T10Hx80	T15Hx80	T20Hx100		
		T25Hx100	T30Hx115	T40Hx130		