






1	MHz frequency range:	2400-2500
2	Polarization:	Vertical
3	Koeff.usil. (DBI):	9
4	Impedance (Ω):	50
5	Maximum input power (W):	50
6	VSWR:	≤ 2.0
7	connector:	RPSMA-J
8	Length (mm):	378 +/- 5
9	Jacket Material:	ABS
10	sheath color:	black
11	Working temperature ($^{\circ}$ C):	(-30 ~ + 60)
12	Humidity (%):	5 ~ 95





RUICHI