


Shape

KSS-3008



Model Number	KSS-3008
Rated Input (W)	0.1
Maximum Input (W)	0.2
Impedance (Ω)	$8 \pm 20\%$ @2KHz1.0V
Rated Frequency (Hz)	$1200 \pm 20\%$ @1.0V
Sound Pressure Level (dB)	$78 \pm 3\text{dB}(0.1\text{W}/10\text{cm}), 68 \pm 3\text{dB}(1\text{W}/1\text{m})$ @2.0K,2.5K,3.0K,4.0KHz
Frequency Range (Hz)	Fo--10K
Magnet (mm)	$\phi 12.5 \times 1.5$ Cobalt
Operating Temperature ($^{\circ}\text{C}$)	-20 ~ +55
Weight (Gram)	11.0
Material	PBT+30%Glass UL 94V-0

Dimension



Tol : ± 0.3 Unit : mm

Characteristic

