


vacuum suction cup

ESV-20-ES

Part number: 191025

FESTO

Wearing part, easily replaceable



Data sheet

| Feature | Value |
|---|---|
| Min. workpiece radius | 30 mm |
| suction cup diameter | 20 mm |
| suction cup volume | 0.722 cm ³ |
| Position of connection | on top |
| Assembly position | Any |
| Suction cup shape | Round, extra deep |
| Operating medium | Atmospheric air based on ISO 8573-1:2010 [7:-:-] |
| Food-safe | See Supplementary material information |
| Ambient temperature | -30 ... 180 °C |
| Retention force at nominal operating pressure | 17 N |
| Product weight | 1.6 g |
| Colour | transparent |
| Shore hardness | 50 +/- 5 |
| Materials note | Free of copper and PTFE Contains PWIS substances Conforms to RoHS |
| Material suction cup | VMQ (silicon) |