

STANDARD DATA C TYPE CHASSIS RECEPTACLES

		VALUE	
		LOW PROFILE TYPE	STANDARD C TYPE
GENERAL CHARACTERISTICS	Number of contacts	5, 6, 9 or 10	
	Termination	Printed Circuit Board (PCB)	Printed Circuit Board (PCB) or Solder Bucket
	Flammability	UL 94HB	
	Environmental	Complies with EU RoHS 2 Directive 2011/65/EU	
ELECTRICAL CHARACTERISTICS	Service Voltage RMS	50V	
	Test Voltage AC RMS	1500V	
	Current carrying capacity	7.5A	
	Typical Contact Resistance	≤50mΩ	
	Insulation Resistance (initial)	> 0.5GΩ	
	Insulation Resistance (after damp heat test)	> 0.2GΩ	
CLIMATIC CHARACTERISTICS	Protection Class	IP40	
	Operating Temperature	-25 °C to +70 °C	
MECHANICAL CHARACTERISTICS	Weight**	9.2g (0.02lb)	14g (0.030lb)
	Retention Spring separating force	≥20N	
	Mounting Screw torque max.	1.5Nm	
	Mechanical Operations	1500 mating cycles	
	Fastening***	Self-Tapping PT screw with thread 2.9 x 1.06 and of Tri-rondular configuration	
MATERIALS	Connector Shell	PA6.6 + 30% glass fibre reinforced, UL94HB	PA6.6 + 20% glass fibre reinforced, UL94HB
	Shell Finish		Black
	Insulators	PA6.6 glass fibre reinforced, UL94HB	PA6.6 + 20% glass fibre reinforced, UL94HB
	XLR Contact		
	Material	Bronze	
	Plating	Gold over Nickel plated	
	Jack Contact		
	Material	Bronze	Brass
Plating	Gold over Nickel plated	Silver over Copper plated	
Latch lock and Spring	Nickel Plated		
Ground element	Nickel Plated	Silver over Copper plated	

**Approximate weight in grams not including packaging. Please contact us for exact weight for shipping purposes.

***Refer to Page 132

Rev 6 - 03/2013

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

[ACJC5H BULK](#) [ACJC5HL BULK](#) [ACJC5V BULK](#) [ACJC5VL BULK](#) [ACJC6H BULK](#) [ACJC6HL BULK](#) [ACJC6V BULK](#)
[ACJC6VL BULK](#) [ACJC9H BULK](#) [ACJC9HL BULK](#) [ACJC9V BULK](#) [ACJC9VL BULK](#) [ACJC10H BULK](#) [ACJC10HL](#)
[BULK](#) [ACJC10V BULK](#) [ACJC10VL BULK](#) [ACJC5S BULK](#) [ACJC5SL BULK](#) [ACJC6S BULK](#) [ACJC6SL BULK](#)
[ACJC9S BULK](#) [ACJC9SL BULK](#) [ACJC10S BULK](#) [ACJC10SL BULK](#) [ACJC9AH BULK](#) [ACJC10AH BULK](#) [ACJC6AV](#)
[BULK](#) [ACJC10AV BULK](#) [ACJC6AH BULK](#) [ACJC6AHL BULK](#) [ACJC10AV2 BULK](#) [ACJC9AHL BULK](#) [ACJC6AV2L](#)
[BULK](#) [ACJC10AV2L BULK](#) [ACJC9AV2L BULK](#) [ACJC6AV2 BULK](#) [ACJC9AV2 BULK](#)