



6950

ESD TOOL CASE EPA 40 PCS

content: article listing see below

ESD dissipative hard case, with dissipative interior

made of dissipative material

case lid locking

pockets made of high-quality dissipative synthetic leather

document compartment in the lid
lockable locks
stabiler Handgriff
measures 500 x 370 x 210 mm
weight 6900 g, empty 5800 g

AREA OF APPLICATION

A dissipative ESD tool case with an extensive equipment of ESD special tools. Ideal for electrostatically sensitive components and systems. This high-quality ESD case offers all the advantages of a standard tool case but ist the only large-format tool case made of dissipative materials!

TECHNICAL DESCRIPTION

The case shells, tool boards and the variably subdivided bottom tray are made of dissipative material and comply with DIN EN IEC Standard 10 00 15 Section 5. The tools have been successfully tested by several test laboratories in accordance with DIN EN 61340-5-1, 61340-2-1 and 61340-2-3 for work in ESD-protected areas. The robust case shells are pressed with a stable double aluminium frame. On two panels, one of which can be fitted on both sides, 32 tools are stored in insertable compartments, ready to hand. The lid of the case contains a document compartment for storing written documents. The freely divisible tray in the bottom of the case allows additional tools and instruments to be stored. The case has 2 locks and a combination lock.

GENERAL INFORMATION

EPA suitable for electrostatically protected areas (ESD workplace / ESD protection zone).

CONTENT

ESD tool case EPA consists of:

- 6915 ESD tool case EPA 42 empty pockets
- 1-909 Engineer mirror with extension Ø 23mm
- 2-101 Tin knife with ceramic blade
- 2-113 ESD opening tool
- 2-123 ESD crowbar SPUDGER metal opener flat
- 2-126 ESD desoldering lever with slot 0.7x2.0mm
- 2-155-13 ESD claw-type gripper with 3 hardened wire claws, dissipative

2-265-1 Test prod red blade 1 mm
2-265-2 Test prod black blade 1 mm
2-298 ESD hand magnifier 5x magnification LED
3-651-15 ESD mini side cutters EUROline dissipative 120 mm flush
3-672-15 ESD end cutters EUROline dissipative 130 mm flush
3-682-15 ESD flat nose pliers EUROline dissipative 130 mm smooth gripping jaws
4-603 ESD screwdriver slot blade 1.5x0.25x60mm
4-605 ESD screwdriver slot blade 2.0x0.4x60mm
4-607 ESD screwdriver slot blade 3.0x0.5x60mm
4-621 ESD screwdriver Phillips PH000
4-622 ESD screwdriver Phillips PH00
4-623 ESD screwdriver Phillips PH0
4-624 ESD screwdriver Phillips PH1
5-049-13 ESD SMD tweezers 110mm form 4 stainless steel, dissipative
5-055-13 ESD SMD tweezers 120mm form 7a stainless steel angle 40° dissipative
5-079-13 ESD cutting tweezers (oblique) 115 mm form 15 AGW, dissipative
5-519 ESD cutter knife dissipative
5-352 ESD scissors with dissipative handle
5-542 ESD precision stripper Ø 0,25-0,80mm
6-656 ESD screwdriver TORX T1
6-657 ESD screwdriver TORX T2
6-658 ESD screwdriver TORX T3
6-659 ESD screwdriver TORX T4
6-661 ESD screwdriver TORX T5
6-662 ESD screwdriver TORX T6
7-421 ESD brush bristles Ø 6mm
9-342-1 ESD contact bracelet blue
9-342-2 ESD spiral cord for bracelet 2.5m black
9-343-1 ESD grounding cable 1 MOhm, 1800mm 2 press-studs 10/10mm
9-353 ESD crocodile clip
9-354-100 ESD table mat black (500x400x0.5) with 2x10 mm press button
9-359-2 ESD earth bonding plug 2x10mm and M5 socket
9-321 ESD boxes for SMD components 5pcs (inside measures 16x12x15 mm)
9-322 ESD boxes for SMD components 5pcs (inside measures 37x12x15 mm)