

**UNIVERSAL SPI PROGRAMMER ON USB PORT FOR SERIAL EEPROMs, SERIAL SPI FLASH PIC MICROCHIP, AVR ATMEL, MSP TEXAS, ARM, STM8, STM32 ST-Micro. MICROCONTROLLERS**



# FORTE Programmer




**Introduction:**

FORTE programmer is dedicating to program microcontrollers thanks to its ISP/ICSP (In Circuit Serial Programming) cable. It supports a wide range of MCU like PIC/Atmel/Texas, ARM architecture MCU like STM8/STM32 (ST-Micro.) but also serial EEPROMs / SPi EEPROMs / SPi Flash. Much faster than PRESTO programmer, it doesn't require any adapters for all power supply from 1,8V to 5,5V. It is equipped with high-speed USB port (480mbps) to connect it to the PC and using a dedicated cable with 10 wires to connect it directly to devices soldered on printed circuit or devices in special packages without having to add an adapter: 2 wires with overcurrent protections can be an output and supply the target application, others 8 wires are configured individually in Inputs/Outputs with pull-up/pull-down transistors. GO button makes repetitive operations easy and quick. The software works with Windows XP/Vista/7/8/8.1/10 (32 bits and 64 bits) and Linux (using Wine). This programmer does not require any external power supply.

**Features :**

- Very fast programmer (30MHz out, 15MHz in/out).
- Embedded processor for fast execution of complex operations.
- Supported voltage range 1,8V to 5,5V without additional accessories.
- Overcurrent protection on supply and programming voltage sources
- GO button makes repetitive operations easy and quick.
- New software versions with new devices support are freely available.



**Supported devices:**

- MICROCHIP PIC10Fxxx / PIC12Fxxx / PIC12Cxxx / rPIC12 / PIC16Fxxx / PIC16Cxxx / PIC18Fxxx  
PIC24Fxxx / PIC24FJxxx / PIC24FVxxx / PIC24HJxxx / PIC24EPxxx  
PIC32MMxxx / PIC32MXxxx / PIC32MZxxx / dsPIC30Fxxx / dsPIC33EVxxx / dsPIC33EXxx / dsPIC33FJxx
- ATMEL AT89LPxxx / AT89LSxxx / AT89Sxxx / AT90CANxxx / AT90PWxxx / AT90Sxxx / AT90USBxxx  
ATtinyxx / ATmegaxx / ATxmegaxx / AT32UCxx / ATSAMxx / AT91SAMxx
- SILICON LAB EFM32Gxx / EFM32HGxx / EFM32JGxx / EFM32LGxx / EFM32TGxx / EFM32WGxx / EFM32ZGxx / EFM8
- NXP LPC1xxx / LPC2xxx / LPC8xxx / MKVxx RENESAS R5Fxx
- ST-MICRO. STM8AFxx / STM8Lxx / STM8Sxx / STM32Fxx / STM32Lxx / STM32Gxx
- TEXAS MSP430F1xx / MSP430F2xx / MSP430F4xx / MSP430F5xx / MSP430F6xx / MSP430G2xx / MSP430I2xx
- CHIPCON CC430Fxxx / CCxxxx
- INTEL : C8051Fxx
- CYPRESS : CY8Cxxx
- 1-WIRE : DS1xx / DS2xx
- UN I/O : 11Axx / 11LCxx
- I2C EEPROM : 24AAxx / 24Cxx / 24FCxxx / 24LCxxx
- SPI EEPROM : 25AAxx / 25LCxxx / AT25xxx / M95xxx
- SPI FLASH EPROM : AT25DFxxx / AT25Fxxx / AT26DFxxx / AT45DBxxx / M25Pxxx / IS25xx  
MX25Lxxx / N25Qxx / PM25LVxxx / S25FLxxx / SST25VFxxx / W25Qxxx
- MicroWire EEPROM : 93AAxx / 93Cxx / 93LCxx / M93Sxx



**Item includes:**

- Programmer
- SPI cable with 10 wires + SPI cable with 7 wires.
- USB cable type A-B.
- Software on CD.
- User manual in English and French.

**Products informations : [www.seeit.fr](http://www.seeit.fr)**

↓ **Devices list programmed below** ↓



## DEVICES LIST FORTE PROGRAMMER

Push "CTRL + F" keys to find a component

Universal SPI programmer for microcontrôleurs PIC / AVR / ARM / TEXAS / serial EEPROMs / SPI FLASHs  
 Total devices : 4978  
 Version : 3.51

### NOTES:

**YES** - supported, 5V only

**YES, 1.8V-5.5V** - full range support (1.8V - 5.5V)

**(4)** - Currently only a Single Partition Flash mode is supported.

If there is only PICxxFxxxx version defined in the table and PICxxLFxxxx version of this chip exists, the PICxxFxxxx type can be selected in the UP program and it will suit for the LF version as well.

DEVICES	FORTE
PIC10Fxxx	
PIC10F200	YES, 4.5-5.5V
PIC10F202	YES, 4.5-5.5V
PIC10F204	YES, 4.5-5.5V
PIC10F206	YES, 4.5-5.5V
PIC10F220	YES, 4.5-5.5V
PIC10F222	YES, 4.5-5.5V
PIC10F320	YES, 2.3-5.5V
PIC10F322	YES, 2.3-5.5V
PIC10LF320	YES, 1.8-3.6V
PIC10LF322	YES, 1.8-3.6V
PIC12Fxxx	
PIC12F1501	YES, 2.3-5.5V
PIC12F1571	YES, 2.3-5.5V
PIC12F1572	YES, 2.3-5.5V
PIC12F1612	YES, 2.3-5.5V
PIC12F1822	YES, 2.1-5.5V
PIC12F1840	YES, 2.1-5.5V
PIC12F508	YES, 4.5-5.5V
PIC12F509	YES, 4.5-5.5V
PIC12F510	YES, 4.5-5.5V
PIC12F519	YES, 4.5-5.5V
PIC12F529T39A	YES, 2.7-3.7V
PIC12F609	YES, 2.0-5.5V
PIC12F615	YES, 2.0-5.5V
PIC12F617	YES, 2.0-5.5V
PIC12F629	YES, 4.5-5.5V
PIC12F635	YES, 4.5-5.5V
PIC12F675	YES, 4.5-5.5V
PIC12F683	YES, 2.0-5.5V
PIC12F752	YES, 2.0-5.5V
PIC12LF1501	YES, 2.0-3.6V
PIC12LF1552	YES, 1.8-3.6V
PIC12LF1571	YES, 1.8-3.6V
PIC12LF1572	YES, 1.8-3.6V
PIC12LF1612	YES, 1.8-3.6V
PIC12LF1822	YES, 2.1-3.6V
PIC12LF1840	YES, 2.1-3.6V
PIC16F14xx	
PIC16F1454	YES, 2.3-5.5V
PIC16F1455	YES, 2.3-5.5V

SUPPORTED FAMILIES
PIC10Fxxx
PIC12Fxxx
PIC16F14xx
PIC16F15xx
PIC16F16xx
PIC16F17xx
PIC16F18xx
PIC16F19xx
PIC16F5x
PIC16F6xx
PIC16F7xx
PIC16F8xx
PIC16F87x
PIC16F9xx
PIC18Fxxx
PIC18Fxx20
PIC18Fxx2x
PIC18F2/4xx0/5
PIC18Fxx30
PIC18Fxx31
PIC18Fxx39
PIC18Fxx8x
PIC18Fxx90
PIC18F2xJxx
PIC18F4xJxx
PIC18F6xJxx
PIC18F8xJxx
PIC18F9xJxx
PIC18FxxKxx
PIC18FxxQxx
PIC12Cxxx
rfPIC12xxxx
PIC16C43x
PIC16C5xx
PIC16C6xx
PIC16C7xx
PIC16C9xx
PIC24
PIC32MK
PIC32MM
PIC32MX

PIC16F1459	YES, 2.3-5.5V
PIC16LF1454	YES, 1.8-3.6V
PIC16LF1455	YES, 1.8-3.6V
PIC16LF1459	YES, 1.8-3.6V
PIC16F15xx	
PIC16F1503	YES, 2.3-5.5V
PIC16F1507	YES, 2.3-5.5V
PIC16F1508	YES, 2.3-5.5V
PIC16F1509	YES, 2.3-5.5V
PIC16F1512	YES, 2.1-5.5V
PIC16F1513	YES, 2.1-5.5V
PIC16F1516	YES, 2.1-5.5V
PIC16F1517	YES, 2.1-5.5V
PIC16F1518	YES, 2.1-5.5V
PIC16F1519	YES, 2.1-5.5V
PIC16F15213	YES, 1.8-5.5V
PIC16F15214	YES, 1.8-5.5V
PIC16F15223	YES, 1.8-5.5V
PIC16F15224	YES, 1.8-5.5V
PIC16F15243	YES, 1.8-5.5V
PIC16F15244	YES, 1.8-5.5V
PIC16F15254	YES, 1.8-5.5V
PIC16F1526	YES, 2.1-5.5V
PIC16F1527	YES, 2.1-5.5V
PIC16F15313	YES, 2.3-5.5V
PIC16F15323	YES, 2.3-5.5V
PIC16F15324	YES, 2.3-5.5V
PIC16F15325	YES, 2.3-5.5V
PIC16F15344	YES, 2.3-5.5V
PIC16F15345	YES, 2.3-5.5V
PIC16F15354	YES, 2.3-5.5V
PIC16F15355	YES, 2.3-5.5V
PIC16F15356	YES, 2.3-5.5V
PIC16F15375	YES, 2.3-5.5V
PIC16F15376	YES, 2.3-5.5V
PIC16F15385	YES, 2.3-5.5V
PIC16F15386	YES, 2.3-5.5V
PIC16F1574	YES, 2.3-5.5V
PIC16F1575	YES, 2.3-5.5V
PIC16F1578	YES, 2.3-5.5V
PIC16F1579	YES, 2.3-5.5V
PIC16LF1503	YES, 2.0-3.6V
PIC16LF1507	YES, 2.0-3.6V
PIC16LF1508	YES, 2.0-3.6V
PIC16LF1509	YES, 2.0-3.6V
PIC16LF1512	YES, 2.1-3.6V
PIC16LF1513	YES, 2.1-3.6V
PIC16LF1516	YES, 2.1-3.6V
PIC16LF1517	YES, 2.1-3.6V
PIC16LF1518	YES, 2.1-3.6V
PIC16LF1519	YES, 2.1-3.6V
PIC16LF1526	YES, 2.1-3.6V
PIC16LF1527	YES, 2.1-3.6V
PIC16LF15313	YES, 2.3-3.6V
PIC16LF15323	YES, 2.3-3.6V
PIC16LF15324	YES, 2.3-3.6V
PIC16LF15325	YES, 2.3-3.6V
PIC16LF15344	YES, 2.3-3.6V
PIC16LF15345	YES, 2.3-3.6V

PIC32MZ
dsPIC30F
dsPIC33
AVR
AVR TPI
AVR UPDI
AVR ATxmega
AVR-32
Atmel 8051 arch.
ARM
R5F1xx (RL78)
R5F56x (RX600)
MSP430F1xx
MSP430F2xx
MSP430F4xx
MSP430F5xx
MSP430F6xxx
MSP430FR2xxx
MSP430G2xxx
MSP430I2xxx
CC430xxxx
CCxxxx
EFM8
C8051
STM8
HCS08
PSoC
1-Wire
UNI/O EEPROM
I2C EEPROM
SPI EEPROM
SPI FLASH EPROM
MicroWire EEPROM
HCSxxx

PIC16LF15354	YES, 2.3-3.6V
PIC16LF15355	YES, 2.3-3.6V
PIC16LF15356	YES, 2.3-3.6V
PIC16LF15375	YES, 2.3-3.6V
PIC16LF15376	YES, 2.3-3.6V
PIC16LF15385	YES, 2.3-3.6V
PIC16LF15386	YES, 2.3-3.6V
PIC16LF1554	YES, 1.8-3.6V
PIC16LF1559	YES, 1.8-3.6V
PIC16LF1566	YES, 1.8-3.6V
PIC16LF1567	YES, 1.8-3.6V
PIC16LF1574	YES, 1.8-3.6V
PIC16LF1575	YES, 1.8-3.6V
PIC16LF1578	YES, 1.8-3.6V
PIC16LF1579	YES, 1.8-3.6V
<b>PIC16F16xx</b>	
PIC16F1613	YES, 2.3-5.5V
PIC16F1614	YES, 2.3-5.5V
PIC16F1615	YES, 2.3-5.5V
PIC16F1618	YES, 2.3-5.5V
PIC16F1619	YES, 2.3-5.5V
PIC16LF1612	YES, 1.8-3.6V
PIC16LF1613	YES, 1.8-3.6V
PIC16LF1615	YES, 1.8-3.6V
PIC16LF1618	YES, 1.8-3.6V
PIC16LF1619	YES, 1.8-3.6V
<b>PIC16F17xx</b>	
PIC16F1703	YES, 2.3-5.5V
PIC16F1704	YES, 2.3-5.5V
PIC16F1705	YES, 2.3-5.5V
PIC16F1707	YES, 2.3-5.5V
PIC16F1708	YES, 2.3-5.5V
PIC16F1709	YES, 2.3-5.5V
PIC16F1713	YES, 2.3-5.5V
PIC16F1716	YES, 2.3-5.5V
PIC16F1717	YES, 2.3-5.5V
PIC16F1718	YES, 2.3-5.5V
PIC16F1719	YES, 2.3-5.5V
PIC16F1764	YES, 2.3-5.5V
PIC16F1765	YES, 2.3-5.5V
PIC16F1768	YES, 2.3-5.5V
PIC16F1769	YES, 2.3-5.5V
PIC16F1773	YES, 2.3-5.5V
PIC16F1776	YES, 2.3-5.5V
PIC16F1777	YES, 2.3-5.5V
PIC16F1778	YES, 2.3-5.5V
PIC16F1779	YES, 2.3-5.5V
PIC16F1782	YES, 2.3-5.5V
PIC16F1783	YES, 2.3-5.5V
PIC16F1784	YES, 2.3-5.5V
PIC16F1786	YES, 2.3-5.5V
PIC16F1787	YES, 2.3-5.5V
PIC16F1788	YES, 2.3-5.5V
PIC16F1789	YES, 2.3-5.5V
PIC16LF1703	YES, 1.8-3.6V
PIC16LF1704	YES, 1.8-3.6V
PIC16LF1705	YES, 1.8-3.6V
PIC16LF1707	YES, 1.8-3.6V
PIC16LF1708	YES, 1.8-3.6V

PIC16LF1709	YES, 1.8-3.6V
PIC16LF1713	YES, 1.8-3.6V
PIC16LF1716	YES, 1.8-3.6V
PIC16LF1717	YES, 1.8-3.6V
PIC16LF1718	YES, 1.8-3.6V
PIC16LF1719	YES, 1.8-3.6V
PIC16LF1764	YES, 1.8-3.6V
PIC16LF1765	YES, 1.8-3.6V
PIC16LF1768	YES, 1.8-3.6V
PIC16LF1769	YES, 1.8-3.6V
PIC16LF1773	YES, 1.8-3.6V
PIC16LF1776	YES, 1.8-3.6V
PIC16LF1777	YES, 1.8-3.6V
PIC16LF1778	YES, 1.8-3.6V
PIC16LF1779	YES, 1.8-3.6V
PIC16LF1782	YES, 1.8-3.6V
PIC16LF1783	YES, 1.8-3.6V
PIC16LF1784	YES, 1.8-3.6V
PIC16LF1786	YES, 1.8-3.6V
PIC16LF1787	YES, 1.8-3.6V
PIC16LF1788	YES, 1.8-3.6V
PIC16LF1789	YES, 1.8-3.6V
<b>PIC16F18xx</b>	
PIC16F1823	YES, 2.1-5.5V
PIC16F1824	YES, 2.1-5.5V
PIC16F1825	YES, 2.1-5.5V
PIC16F1826	YES, 2.1-5.5V
PIC16F1827	YES, 2.1-5.5V
PIC16F1828	YES, 2.1-5.5V
PIC16F1829	YES, 2.1-5.5V
PIC16F18313	YES, 2.5-5.5V
PIC16F18323	YES, 2.5-5.5V
PIC16F18324	YES, 2.5-5.5V
PIC16F18325	YES, 2.5-5.5V
PIC16F18326	YES, 2.5-5.5V
PIC16F18344	YES, 2.5-5.5V
PIC16F18345	YES, 2.5-5.5V
PIC16F18346	YES, 2.5-5.5V
PIC16F18424	YES, 2.5-5.5V
PIC16F18425	YES, 2.5-5.5V
PIC16F18426	YES, 2.5-5.5V
PIC16F18444	YES, 2.5-5.5V
PIC16F18445	YES, 2.5-5.5V
PIC16F18446	YES, 2.5-5.5V
PIC16F18455	YES, 2.5-5.5V
PIC16F18456	YES, 2.5-5.5V
PIC16F1847	YES, 2.1-5.5V
PIC16F18854	YES, 2.3-5.5V
PIC16F18855	YES, 2.3-5.5V
PIC16F18856	YES, 2.3-5.5V
PIC16F18857	YES, 2.3-5.5V
PIC16F18875	YES, 2.3-5.5V
PIC16F18876	YES, 2.3-5.5V
PIC16F18877	YES, 2.3-5.5V
PIC16LF1823	YES, 2.1-3.6V
PIC16LF1824	YES, 2.1-3.6V
PIC16LF1825	YES, 2.1-3.6V
PIC16LF1826	YES, 2.1-3.6V
PIC16LF1827	YES, 2.1-3.6V

PIC16LF1828	YES, 2.1-3.6V
PIC16LF1829	YES, 2.1-3.6V
PIC16LF18313	YES, 2.5-3.6V
PIC16LF18323	YES, 2.5-3.6V
PIC16LF18324	YES, 2.5-3.6V
PIC16LF18325	YES, 2.5-3.6V
PIC16LF18326	YES, 2.5-3.6V
PIC16LF18344	YES, 2.5-3.6V
PIC16LF18345	YES, 2.5-3.6V
PIC16LF18346	YES, 2.5-3.6V
PIC16LF18424	YES, 1.8-3.6V
PIC16LF18425	YES, 1.8-3.6V
PIC16LF18426	YES, 1.8-3.6V
PIC16LF18444	YES, 1.8-3.6V
PIC16LF18445	YES, 1.8-3.6V
PIC16LF18446	YES, 1.8-3.6V
PIC16LF18455	YES, 1.8-3.6V
PIC16LF18456	YES, 1.8-3.6V
PIC16LF1847	YES, 2.1-3.6V
PIC16LF18854	YES, 1.8-3.6V
PIC16LF18855	YES, 1.8-3.6V
PIC16LF18856	YES, 1.8-3.6V
PIC16LF18857	YES, 1.8-3.6V
PIC16LF18875	YES, 1.8-3.6V
PIC16LF18876	YES, 1.8-3.6V
PIC16LF18877	YES, 1.8-3.6V
<b>PIC16F19xx</b>	
PIC16F19155	YES, 2.3-5.5V
PIC16F19156	YES, 2.3-5.5V
PIC16F19175	YES, 2.3-5.5V
PIC16F19176	YES, 2.3-5.5V
PIC16F19185	YES, 2.3-5.5V
PIC16F19186	YES, 2.3-5.5V
PIC16F19195	YES, 2.3-5.5V
PIC16F19196	YES, 2.3-5.5V
PIC16F19197	YES, 2.3-5.5V
PIC16F1933	YES, 2.1-5.5V
PIC16F1934	YES, 2.1-5.5V
PIC16F1936	YES, 2.1-5.5V
PIC16F1937	YES, 2.1-5.5V
PIC16F1938	YES, 2.1-5.5V
PIC16F1939	YES, 2.1-5.5V
PIC16F1946	YES, 2.1-5.5V
PIC16F1947	YES, 2.1-5.5V
PIC16LF1902	YES, 1.8-3.6V
PIC16LF1903	YES, 1.8-3.6V
PIC16LF1904	YES, 1.8-3.6V
PIC16LF1906	YES, 1.8-3.6V
PIC16LF1907	YES, 1.8-3.6V
PIC16LF19155	YES, 1.8-3.6V
PIC16LF19156	YES, 1.8-3.6V
PIC16LF19175	YES, 1.8-3.6V
PIC16LF19176	YES, 1.8-3.6V
PIC16LF19185	YES, 1.8-3.6V
PIC16LF19186	YES, 1.8-3.6V
PIC16LF19195	YES, 1.8-3.6V
PIC16LF19196	YES, 1.8-3.6V
PIC16LF19197	YES, 1.8-3.6V
PIC16LF1933	YES, 2.1-3.6V

PIC16LF1934	YES, 2.1-3.6V
PIC16LF1936	YES, 2.1-3.6V
PIC16LF1937	YES, 2.1-3.6V
PIC16LF1938	YES, 1.8-3.6V
PIC16LF1939	YES, 1.8-3.6V
PIC16LF1946	YES, 1.8-3.6V
PIC16LF1947	YES, 1.8-3.6V
<b>PIC16F5x</b>	
PIC16F505	YES, 4.5-5.5V
PIC16F506	YES, 4.5-5.5V
PIC16F526	YES, 4.5-5.5V
PIC16F527	YES, 4.5-5.5V
PIC16F54	YES, 4.5-5.5V
PIC16F57	YES, 4.5-5.5V
PIC16F570	YES, 4.5-5.5V
PIC16F59	YES, 4.5-5.5V
<b>PIC16F6xx</b>	
PIC16F610	YES, 2.0-5.5V
PIC16F616	YES, 2.0-5.5V
PIC16F627	YES, 4.5-5.5V
PIC16F627A	YES, 2.0-5.5V
PIC16F628	YES, 4.5-5.5V
PIC16F628A	YES, 2.0-5.5V
PIC16F630	YES, 2.0-5.5V
PIC16F631	YES, 2.0-5.5V
PIC16F636	YES, 4.5-5.5V
PIC16F639	YES, 4.5-5.5V
PIC16F648A	YES, 2.0-5.5V
PIC16F676	YES, 2.0-5.5V
PIC16F677	YES, 2.0-5.5V
PIC16F684	YES, 2.0-5.5V
PIC16F685	YES, 2.0-5.5V
PIC16F687	YES, 2.0-5.5V
PIC16F688	YES, 2.0-5.5V
PIC16F689	YES, 2.0-5.5V
PIC16F690	YES, 2.0-5.5V
<b>PIC16F7xx</b>	
PIC16F707	YES, 2.7-5.5V
PIC16F716	YES, 4.5-5.5V
PIC16F72	YES, 4.7-5.2V
PIC16F720	YES, 2.1-5.5V
PIC16F721	YES, 2.1-5.5V
PIC16F722	YES, 2.7-5.5V
PIC16F722A	YES, 2.7-5.5V
PIC16F723	YES, 2.7-5.5V
PIC16F723A	YES, 2.7-5.5V
PIC16F724	YES, 2.7-5.5V
PIC16F726	YES, 2.7-5.5V
PIC16F727	YES, 2.7-5.5V
PIC16F73	YES, 4.7-5.2V
PIC16F737	YES, 4.7-5.2V
PIC16F74	YES, 4.7-5.2V
PIC16F747	YES, 4.7-5.2V
PIC16F753	YES, 2.0-5.5V
PIC16F76	YES, 4.7-5.2V
PIC16F767	YES, 4.7-5.2V
PIC16F77	YES, 4.7-5.2V
PIC16F777	YES, 4.7-5.2V
PIC16F785	YES, 4.5-5.5V

PIC16LF707	YES, 2.1-3.6V
PIC16LF720	YES, 2.1-3.6V
PIC16LF721	YES, 2.1-3.6V
PIC16LF722	YES, 2.1-3.6V
PIC16LF723	YES, 2.1-3.6V
PIC16LF724	YES, 2.1-3.6V
PIC16LF726	YES, 2.1-3.6V
PIC16LF727	YES, 2.1-3.6V
<b>PIC16F8xx</b>	
PIC16C84	YES, 4.5-5.5V
PIC16F818	YES, 2.0-5.5V
PIC16F819	YES, 2.0-5.5V
PIC16F83	YES, 4.5-5.5V
PIC16F84	YES, 4.5-5.5V
PIC16F84A	YES, 4.5-5.5V
PIC16F87	YES, 2.0-5.5V
PIC16F88	YES, 2.0-5.5V
PIC16F882	YES, 2.0-5.5V
PIC16F883	YES, 2.0-5.5V
PIC16F884	YES, 2.0-5.5V
PIC16F886	YES, 2.0-5.5V
PIC16F887	YES, 2.0-5.5V
<b>PIC16F87x</b>	
PIC16F870	YES, 2.2-5.5V
PIC16F871	YES, 2.2-5.5V
PIC16F872	YES, 2.2-5.5V
PIC16F873	YES, 2.2-5.5V
PIC16F873A	YES, 2.2-5.5V
PIC16F874	YES, 2.2-5.5V
PIC16F874A	YES, 2.2-5.5V
PIC16F876	YES, 2.2-5.5V
PIC16F876A	YES, 2.2-5.5V
PIC16F877	YES, 2.2-5.5V
PIC16F877A	YES, 2.2-5.5V
<b>PIC16F9xx</b>	
PIC16F913	YES, 2.0-5.5V
PIC16F914	YES, 2.0-5.5V
PIC16F916	YES, 2.0-5.5V
PIC16F917	YES, 2.0-5.5V
PIC16F946	YES, 2.0-5.5V
<b>PIC18Fxxx</b>	
PIC18F242	YES, 2.1-5.5V
PIC18F248	YES, 2.1-5.5V
PIC18F252	YES, 2.1-5.5V
PIC18F258	YES, 2.1-5.5V
PIC18F442	YES, 2.1-5.5V
PIC18F448	YES, 2.1-5.5V
PIC18F452	YES, 2.1-5.5V
PIC18F458	YES, 2.1-5.5V
<b>PIC18Fxx20</b>	
PIC18F1220	YES, 2.0-5.5V
PIC18F1320	YES, 2.0-5.5V
PIC18F2220	YES, 2.0-5.5V
PIC18F2320	YES, 2.0-5.5V
PIC18F4220	YES, 2.0-5.5V
PIC18F4320	YES, 2.0-5.5V
PIC18F6520	YES, 2.0-5.5V
PIC18F6620	YES, 2.0-5.5V
PIC18F6720	YES, 2.0-5.5V



PIC18F8520	YES, 2.0-5.5V
PIC18F8620	YES, 2.0-5.5V
PIC18F8720	YES, 2.0-5.5V
PIC18Fxx2x	
PIC18F2221	YES, 2.2-5.5V
PIC18F2321	YES, 2.2-5.5V
PIC18F2423	YES, 2.0-5.5V
PIC18F2523	YES, 2.0-5.5V
PIC18F4221	YES, 2.2-5.5V
PIC18F4321	YES, 2.2-5.5V
PIC18F4423	YES, 2.0-5.5V
PIC18F4523	YES, 2.0-5.5V
PIC18F6525	YES, 2.0-5.5V
PIC18F6527	YES, 2.0-5.5V
PIC18F6621	YES, 2.0-5.5V
PIC18F6622	YES, 2.0-5.5V
PIC18F6627	YES, 2.0-5.5V
PIC18F6628	YES, 2.0-5.5V
PIC18F6722	YES, 2.0-5.5V
PIC18F6723	YES, 2.0-5.5V
PIC18F8525	YES, 2.0-5.5V
PIC18F8527	YES, 2.0-5.5V
PIC18F8621	YES, 2.0-5.5V
PIC18F8622	YES, 2.0-5.5V
PIC18F8627	YES, 2.0-5.5V
PIC18F8628	YES, 2.0-5.5V
PIC18F8722	YES, 2.0-5.5V
PIC18F8723	YES, 2.0-5.5V
PIC18F2/4xx0/5	
PIC18F2410	YES, 3.0-5.5V
PIC18F2420	YES, 2.2-5.5V
PIC18F2450	YES, 3.0-5.5V
PIC18F2455	YES, 2.0-5.5V
PIC18F2458	YES, 2.0-5.5V
PIC18F2480	YES, 2.0-5.5V
PIC18F2510	YES, 2.0-5.5V
PIC18F2515	YES, 2.0-5.5V
PIC18F2520	YES, 2.0-5.5V
PIC18F2525	YES, 2.0-5.5V
PIC18F2550	YES, 2.0-5.5V
PIC18F2553	YES, 2.0-5.5V
PIC18F2580	YES, 2.0-5.5V
PIC18F2585	YES, 2.0-5.5V
PIC18F2610	YES, 2.0-5.5V
PIC18F2620	YES, 2.0-5.5V
PIC18F2680	YES, 2.0-5.5V
PIC18F4410	YES, 2.0-5.5V
PIC18F4420	YES, 2.0-5.5V
PIC18F4450	YES, 2.0-5.5V
PIC18F4455	YES, 2.0-5.5V
PIC18F4458	YES, 2.0-5.5V
PIC18F4480	YES, 2.0-5.5V
PIC18F4510	YES, 2.0-5.5V
PIC18F4515	YES, 2.0-5.5V
PIC18F4520	YES, 2.0-5.5V
PIC18F4525	YES, 2.0-5.5V
PIC18F4550	YES, 2.0-5.5V
PIC18F4553	YES, 2.0-5.5V
PIC18F4580	YES, 2.0-5.5V

PIC18F4585	YES, 2.0-5.5V
PIC18F4610	YES, 2.0-5.5V
PIC18F4620	YES, 2.0-5.5V
PIC18F4680	YES, 2.0-5.5V
<b>PIC18Fxx30</b>	
PIC18F1230	YES, 2.0-5.5V
PIC18F1330	YES, 2.0-5.5V
<b>PIC18Fxx31</b>	
PIC18F2331	YES, 2.0-5.5V
PIC18F2431	YES, 2.0-5.5V
PIC18F4331	YES, 2.0-5.5V
PIC18F4431	YES, 2.0-5.5V
<b>PIC18Fxx39</b>	
PIC18F2439	YES, 2.0-5.5V
PIC18F2539	YES, 2.0-5.5V
PIC18F4439	YES, 2.0-5.5V
PIC18F4539	YES, 2.0-5.5V
<b>PIC18Fxx8x</b>	
PIC18F2682	YES, 2.0-5.5V
PIC18F2685	YES, 2.0-5.5V
PIC18F4682	YES, 2.0-5.5V
PIC18F4685	YES, 2.0-5.5V
PIC18F6585	YES, 2.0-5.5V
PIC18F6680	YES, 2.0-5.5V
PIC18F8585	YES, 2.0-5.5V
PIC18F8680	YES, 2.0-5.5V
<b>PIC18Fxx90</b>	
PIC18F6310	YES, 2.0-5.5V
PIC18F6390	YES, 2.0-5.5V
PIC18F6393	YES, 2.0-5.5V
PIC18F6410	YES, 2.0-5.5V
PIC18F6490	YES, 2.0-5.5V
PIC18F6493	YES, 2.0-5.5V
PIC18F8310	YES, 2.0-5.5V
PIC18F8390	YES, 2.0-5.5V
PIC18F8393	YES, 2.0-5.5V
PIC18F8410	YES, 2.0-5.5V
PIC18F8490	YES, 2.0-5.5V
PIC18F8493	YES, 2.0-5.5V
<b>PIC18F2xJxx</b>	
PIC18F24J10	YES, 2.9-3.6V
PIC18F24J11	YES, 2.9-3.6V
PIC18F24J50	YES, 2.9-3.6V
PIC18F25J10	YES, 2.9-3.6V
PIC18F25J11	YES, 2.9-3.6V
PIC18F25J50	YES, 2.9-3.6V
PIC18F26J11	YES, 2.9-3.6V
PIC18F26J13	YES, 2.9-3.6V
PIC18F26J50	YES, 2.9-3.6V
PIC18F26J53	YES, 2.9-3.6V
PIC18F27J13	YES, 2.9-3.6V
PIC18F27J53	YES, 2.9-3.6V
PIC18LF24J10	YES, 2.9-3.6V
PIC18LF24J11	YES, 2.9-3.6V
PIC18LF24J50	YES, 2.9-3.6V
PIC18LF25J10	YES, 2.9-3.6V
PIC18LF25J11	YES, 2.9-3.6V
PIC18LF25J50	YES, 2.9-3.6V
PIC18LF26J11	YES, 2.9-3.6V

PIC18LF26J13	YES, 2.9-3.6V
PIC18LF26J50	YES, 2.9-3.6V
PIC18LF26J53	YES, 2.9-3.6V
PIC18LF27J13	YES, 2.9-3.6V
PIC18LF27J53	YES, 2.9-3.6V
<b>PIC18F4xJxx</b>	
PIC18F44J10	YES, 2.9-3.6V
PIC18F44J11	YES, 2.9-3.6V
PIC18F44J50	YES, 2.9-3.6V
PIC18F45J10	YES, 2.9-3.6V
PIC18F45J11	YES, 2.9-3.6V
PIC18F45J50	YES, 2.9-3.6V
PIC18F46J11	YES, 2.9-3.6V
PIC18F46J13	YES, 2.9-3.6V
PIC18F46J50	YES, 2.9-3.6V
PIC18F46J53	YES, 2.9-3.6V
PIC18F47J13	YES, 2.9-3.6V
PIC18F47J53	YES, 2.9-3.6V
PIC18LF44J10	YES, 2.9-3.6V
PIC18LF44J11	YES, 2.9-3.6V
PIC18LF44J50	YES, 2.9-3.6V
PIC18LF45J10	YES, 2.9-3.6V
PIC18LF45J11	YES, 2.9-3.6V
PIC18LF45J50	YES, 2.9-3.6V
PIC18LF46J11	YES, 2.9-3.6V
PIC18LF46J13	YES, 2.9-3.6V
PIC18LF46J50	YES, 2.9-3.6V
PIC18LF46J53	YES, 2.9-3.6V
PIC18LF47J13	YES, 2.9-3.6V
PIC18LF47J53	YES, 2.9-3.6V
<b>PIC18F6xJxx</b>	
PIC18F63J11	YES, 2.5-3.6V
PIC18F63J90	YES, 2.5-3.6V
PIC18F64J11	YES, 2.5-3.6V
PIC18F64J90	YES, 2.5-3.6V
PIC18F65J10	YES, 2.5-3.6V
PIC18F65J11	YES, 2.5-3.6V
PIC18F65J15	YES, 2.5-3.6V
PIC18F65J50	YES, 2.5-3.6V
PIC18F65J90	YES, 2.5-3.6V
PIC18F65J94	YES, 2.2-3.6V
PIC18F66J10	YES, 2.5-3.6V
PIC18F66J11	YES, 2.5-3.6V
PIC18F66J15	YES, 2.5-3.6V
PIC18F66J16	YES, 2.5-3.6V
PIC18F66J50	YES, 2.5-3.6V
PIC18F66J55	YES, 2.5-3.6V
PIC18F66J60	YES, 3.0-3.6V
PIC18F66J65	YES, 3.0-3.6V
PIC18F66J90	YES, 2.5-3.6V
PIC18F66J93	YES, 2.5-3.6V
PIC18F66J94	YES, 2.2-3.6V
PIC18F67J10	YES, 2.5-3.6V
PIC18F67J11	YES, 2.5-3.6V
PIC18F67J50	YES, 2.5-3.6V
PIC18F67J60	YES, 3.0-3.6V
PIC18F67J90	YES, 2.5-3.6V
PIC18F67J93	YES, 2.5-3.6V
PIC18F67J94	YES, 2.2-3.6V

<b>PIC18F8xJxx</b>	
PIC18F83J11	YES, 2.5-3.6V
PIC18F83J90	YES, 2.5-3.6V
PIC18F84J11	YES, 2.5-3.6V
PIC18F84J90	YES, 2.5-3.6V
PIC18F85J10	YES, 2.5-3.6V
PIC18F85J11	YES, 2.5-3.6V
PIC18F85J15	YES, 2.5-3.6V
PIC18F85J50	YES, 2.5-3.6V
PIC18F85J90	YES, 2.5-3.6V
PIC18F85J94	YES, 2.2-3.6V
PIC18F86J10	YES, 2.5-3.6V
PIC18F86J11	YES, 2.5-3.6V
PIC18F86J15	YES, 2.5-3.6V
PIC18F86J16	YES, 2.5-3.6V
PIC18F86J50	YES, 2.5-3.6V
PIC18F86J55	YES, 2.5-3.6V
PIC18F86J60	YES, 3.0-3.6V
PIC18F86J65	YES, 3.0-3.6V
PIC18F86J72	YES, 2.5-3.6V
PIC18F86J90	YES, 2.5-3.6V
PIC18F86J93	YES, 2.5-3.6V
PIC18F86J94	YES, 2.2-3.6V
PIC18F87J10	YES, 2.5-3.6V
PIC18F87J11	YES, 2.5-3.6V
PIC18F87J50	YES, 2.5-3.6V
PIC18F87J60	YES, 3.0-3.6V
PIC18F87J72	YES, 2.5-3.6V
PIC18F87J90	YES, 2.5-3.6V
PIC18F87J93	YES, 2.5-3.6V
PIC18F87J94	YES, 2.2-3.6V
<b>PIC18F9xJxx</b>	
PIC18F95J94	YES, 2.2-3.6V
PIC18F96J60	YES, 3.0-3.6V
PIC18F96J65	YES, 3.0-3.6V
PIC18F96J94	YES, 2.2-3.6V
PIC18F97J60	YES, 3.0-3.6V
PIC18F97J94	YES, 2.2-3.6V
<b>PIC18FxxKxx</b>	
PIC18F13K22	YES, 2.7-5.5V
PIC18F13K50	YES, 2.7-3.3V
PIC18F14K22	YES, 2.7-5.5V
PIC18F14K50	YES, 2.7-3.3V
PIC18F23K20	YES, 1.8-3.6V
PIC18F23K22	YES, 1.8-5.5V
PIC18F24K20	YES, 1.8-3.6V
PIC18F24K22	YES, 1.8-5.5V
PIC18F24K40	YES, 2.3-5.5V
PIC18F24K42	YES, 2.3-5.5V
PIC18F24K50	YES, 2.3-5.5V
PIC18F25K20	YES, 2.3-3.6V
PIC18F25K22	YES, 1.8-5.5V
PIC18F25K40	YES, 2.3-5.5V
PIC18F25K42	YES, 2.3-5.5V
PIC18F25K50	YES, 2.3-5.5V
PIC18F25K80	YES, 2.1-5.5V
PIC18F25K83	YES, 2.3-3.6V
PIC18F26K20	YES, 1.8-3.6V
PIC18F26K22	YES, 1.8-5.5V

PIC18F26K40	YES, 2.3-5.5V
PIC18F26K42	YES, 2.3-5.5V
PIC18F26K80	YES, 2.1-5.5V
PIC18F26K83	YES, 2.3-5.5V
PIC18F27K40	YES, 2.3-5.5V
PIC18F27K42	YES, 2.3-5.5V
PIC18F43K20	YES, 1.8-3.6V
PIC18F43K22	YES, 1.8-5.5V
PIC18F44K20	YES, 1.8-3.6V
PIC18F44K22	YES, 1.8-5.5V
PIC18F45K20	YES, 2.3-3.6V
PIC18F45K22	YES, 1.8-5.5V
PIC18F45K40	YES, 2.3-5.5V
PIC18F45K42	YES, 2.3-5.5V
PIC18F45K50	YES, 2.3-5.5V
PIC18F45K80	YES, 2.1-5.5V
PIC18F46K20	YES, 1.8-3.6V
PIC18F46K22	YES, 1.8-5.5V
PIC18F46K40	YES, 2.3-5.5V
PIC18F46K42	YES, 2.3-5.5V
PIC18F46K80	YES, 2.1-5.5V
PIC18F47K40	YES, 2.3-5.5V
PIC18F47K42	YES, 2.3-5.5V
PIC18F55K42	YES, 2.3-5.5V
PIC18F56K42	YES, 2.3-5.5V
PIC18F57K42	YES, 2.3-5.5V
PIC18F65K22	YES, 2.1-5.5V
PIC18F65K40	YES, 2.3-5.5V
PIC18F65K80	YES, 2.1-5.5V
PIC18F65K90	YES, 2.1-5.5V
PIC18F66K22	YES, 2.1-5.5V
PIC18F66K40	YES, 2.3-5.5V
PIC18F66K80	YES, 2.1-5.5V
PIC18F66K90	YES, 2.1-5.5V
PIC18F67K22	YES, 2.1-5.5V
PIC18F67K40	YES, 2.3-5.5V
PIC18F67K90	YES, 2.1-5.5V
PIC18F85K22	YES, 2.1-5.5V
PIC18F85K90	YES, 2.1-5.5V
PIC18F86K22	YES, 2.1-5.5V
PIC18F86K90	YES, 2.1-5.5V
PIC18F87K22	YES, 2.1-5.5V
PIC18F87K90	YES, 2.1-5.5V
PIC18LF13K22	YES, 2.7-3.6V
PIC18LF13K50	YES, 2.7-3.3V
PIC18LF14K22	YES, 2.7-3.6V
PIC18LF14K50	YES, 2.7-3.3V
PIC18LF23K22	YES, 1.8-3.6V
PIC18LF24K22	YES, 1.8-3.6V
PIC18LF24K40	YES, 1.8-3.6V
PIC18LF24K42	YES, 1.8-3.6V
PIC18LF24K50	YES, 1.8-3.6V
PIC18LF25K22	YES, 1.8-3.6V
PIC18LF25K40	YES, 1.8-3.6V
PIC18LF25K42	YES, 1.8-3.6V
PIC18LF25K50	YES, 1.8-3.6V
PIC18LF25K80	YES, 2.1-3.6V
PIC18LF25K83	YES, 1.8-3.6V
PIC18LF26K22	YES, 1.8-3.6V

PIC18LF26K40	YES, 1.8-3.6V
PIC18LF26K42	YES, 1.8-3.6V
PIC18LF26K80	YES, 2.1-3.6V
PIC18LF26K83	YES, 1.8-3.6V
PIC18LF27K40	YES, 1.8-3.6V
PIC18LF27K42	YES, 1.8-3.6V
PIC18LF43K22	YES, 1.8-3.6V
PIC18LF44K22	YES, 1.8-3.6V
PIC18LF45K22	YES, 1.8-3.6V
PIC18LF45K40	YES, 1.8-3.6V
PIC18LF45K42	YES, 1.8-3.6V
PIC18LF45K50	YES, 1.8-3.6V
PIC18LF45K80	YES, 2.1-3.6V
PIC18LF46K22	YES, 1.8-3.6V
PIC18LF46K40	YES, 1.8-3.6V
PIC18LF46K42	YES, 1.8-3.6V
PIC18LF46K80	YES, 2.1-3.6V
PIC18LF47K40	YES, 1.8-3.6V
PIC18LF47K42	YES, 1.8-3.6V
PIC18LF55K42	YES, 1.8-3.6V
PIC18LF56K42	YES, 1.8-3.6V
PIC18LF57K42	YES, 1.8-3.6V
PIC18LF65K40	YES, 1.8-3.6V
PIC18LF65K80	YES, 2.1-3.6V
PIC18LF66K40	YES, 1.8-3.6V
PIC18LF66K80	YES, 2.1-3.6V
PIC18LF67K40	YES, 1.8-3.6V
PIC18FxxQxx	
PIC18F04Q40	YES, 1.8-5.5V
PIC18F04Q41	YES, 1.8-5.5V
PIC18F05Q40	YES, 1.8-5.5V
PIC18F05Q41	YES, 1.8-5.5V
PIC18F06Q40	YES, 1.8-5.5V
PIC18F06Q41	YES, 1.8-5.5V
PIC18F14Q40	YES, 1.8-5.5V
PIC18F14Q41	YES, 1.8-5.5V
PIC18F15Q40	YES, 1.8-5.5V
PIC18F15Q41	YES, 1.8-5.5V
PIC18F16Q40	YES, 1.8-5.5V
PIC18F16Q41	YES, 1.8-5.5V
PIC18F24Q10	YES, 1.8-5.5V
PIC18F25Q10	YES, 1.8-5.5V
PIC18F25Q43	YES, 1.8-5.5V
PIC18F26Q10	YES, 1.8-5.5V
PIC18F26Q43	YES, 1.8-5.5V
PIC18F27Q10	YES, 1.8-5.5V
PIC18F27Q43	YES, 1.8-5.5V
PIC18F45Q10	YES, 1.8-5.5V
PIC18F45Q43	YES, 1.8-5.5V
PIC18F46Q10	YES, 1.8-5.5V
PIC18F46Q43	YES, 1.8-5.5V
PIC18F47Q10	YES, 1.8-5.5V
PIC18F47Q43	YES, 1.8-5.5V
PIC18F55Q43	YES, 1.8-5.5V
PIC18F56Q43	YES, 1.8-5.5V
PIC18F57Q43	YES, 1.8-5.5V
rfPIC12xxxx	
rfPIC12F675x	YES, 4.5-5.5V
PIC24	

PIC24EP128GP202	YES, 3.0-3.6V
PIC24EP128GP204	YES, 3.0-3.6V
PIC24EP128GP206	YES, 3.0-3.6V
PIC24EP128MC202	YES, 3.0-3.6V
PIC24EP128MC204	YES, 3.0-3.6V
PIC24EP128MC206	YES, 3.0-3.6V
PIC24EP256GP202	YES, 3.0-3.6V
PIC24EP256GP204	YES, 3.0-3.6V
PIC24EP256GP206	YES, 3.0-3.6V
PIC24EP256GU810	YES, 3.0-3.6V
PIC24EP256GU814	YES, 3.0-3.6V
PIC24EP256MC202	YES, 3.0-3.6V
PIC24EP256MC204	YES, 3.0-3.6V
PIC24EP256MC206	YES, 3.0-3.6V
PIC24EP32GP202	YES, 3.0-3.6V
PIC24EP32GP203	YES, 3.0-3.6V
PIC24EP32GP204	YES, 3.0-3.6V
PIC24EP32MC202	YES, 3.0-3.6V
PIC24EP32MC203	YES, 3.0-3.6V
PIC24EP32MC204	YES, 3.0-3.6V
PIC24EP512GP202	YES, 3.0-3.6V
PIC24EP512GP204	YES, 3.0-3.6V
PIC24EP512GP206	YES, 3.0-3.6V
PIC24EP512GP806	YES, 3.0-3.6V
PIC24EP512GU810	YES, 3.0-3.6V
PIC24EP512GU814	YES, 3.0-3.6V
PIC24EP512MC202	YES, 3.0-3.6V
PIC24EP512MC204	YES, 3.0-3.6V
PIC24EP512MC206	YES, 3.0-3.6V
PIC24EP64GP202	YES, 3.0-3.6V
PIC24EP64GP203	YES, 3.0-3.6V
PIC24EP64GP204	YES, 3.0-3.6V
PIC24EP64GP206	YES, 3.0-3.6V
PIC24EP64MC202	YES, 3.0-3.6V
PIC24EP64MC203	YES, 3.0-3.6V
PIC24EP64MC204	YES, 3.0-3.6V
PIC24EP64MC206	YES, 3.0-3.6V
PIC24F04KA200	YES, 2.6-3.6V
PIC24F04KA201	YES, 2.6-3.6V
PIC24F04KL100	YES, 1.8-3.6V
PIC24F04KL101	YES, 1.8-3.6V
PIC24F08KA101	YES, 2.6-3.6V
PIC24F08KA102	YES, 2.6-3.6V
PIC24F08KL200	YES, 1.8-3.6V
PIC24F08KL201	YES, 1.8-3.6V
PIC24F08KL301	YES, 1.8-3.6V
PIC24F08KL302	YES, 1.8-3.6V
PIC24F08KL401	YES, 1.8-3.6V
PIC24F08KL402	YES, 1.8-3.6V
PIC24F08KM101	YES, 1.8-3.6V
PIC24F08KM102	YES, 1.8-3.6V
PIC24F08KM202	YES, 1.8-3.6V
PIC24F08KM204	YES, 1.8-3.6V
PIC24F16KA101	YES, 2.6-3.6V
PIC24F16KA102	YES, 2.6-3.6V
PIC24F16KA301	YES, 2.6-3.6V
PIC24F16KA302	YES, 2.6-3.6V
PIC24F16KA304	YES, 2.6-3.6V
PIC24F16KL401	YES, 1.8-3.6V

PIC24F16KL402	YES, 1.8-3.6V
PIC24F16KM102	YES, 1.8-3.6V
PIC24F16KM104	YES, 1.8-3.6V
PIC24F16KM202	YES, 1.8-3.6V
PIC24F16KM204	YES, 1.8-3.6V
PIC24F32KA301	YES, 2.6-3.6V
PIC24F32KA302	YES, 2.6-3.6V
PIC24F32KA304	YES, 2.6-3.6V
PIC24FJ1024GA606	YES, 2.0-3.6V 4)
PIC24FJ1024GA610	YES, 2.0-3.6V 4)
PIC24FJ1024GB606	YES, 2.0-3.6V 4)
PIC24FJ1024GB610	YES, 2.0-3.6V 4)
PIC24FJ128DA106	YES, 2.6-3.6V
PIC24FJ128DA110	YES, 2.6-3.6V
PIC24FJ128DA206	YES, 2.6-3.6V
PIC24FJ128DA210	YES, 2.6-3.6V
PIC24FJ128GA006	YES, 2.6-3.6V
PIC24FJ128GA008	YES, 2.6-3.6V
PIC24FJ128GA010	YES, 2.6-3.6V
PIC24FJ128GA106	YES, 2.6-3.6V
PIC24FJ128GA108	YES, 2.6-3.6V
PIC24FJ128GA110	YES, 2.6-3.6V
PIC24FJ128GA202	YES, 2.2-3.6V
PIC24FJ128GA204	YES, 2.2-3.6V
PIC24FJ128GA306	YES, 2.6-3.6V
PIC24FJ128GA308	YES, 2.6-3.6V
PIC24FJ128GA310	YES, 2.6-3.6V
PIC24FJ128GA406	YES, 2.0-3.6V 4)
PIC24FJ128GA410	YES, 2.0-3.6V 4)
PIC24FJ128GA412	YES, 2.0-3.6V 4)
PIC24FJ128GA606	YES, 2.0-3.6V 4)
PIC24FJ128GA610	YES, 2.0-3.6V 4)
PIC24FJ128GA702	YES, 2.0-3.6V
PIC24FJ128GA704	YES, 2.0-3.6V
PIC24FJ128GA705	YES, 2.0-3.6V
PIC24FJ128GB106	YES, 2.6-3.6V
PIC24FJ128GB108	YES, 2.6-3.6V
PIC24FJ128GB110	YES, 2.6-3.6V
PIC24FJ128GB202	YES, 2.2-3.6V
PIC24FJ128GB204	YES, 2.2-3.6V
PIC24FJ128GB206	YES, 2.6-3.6V
PIC24FJ128GB210	YES, 2.6-3.6V
PIC24FJ128GB406	YES, 2.0-3.6V 4)
PIC24FJ128GB410	YES, 2.0-3.6V 4)
PIC24FJ128GB412	YES, 2.0-3.6V 4)
PIC24FJ128GB606	YES, 2.0-3.6V 4)
PIC24FJ128GB610	YES, 2.0-3.6V 4)
PIC24FJ128GC006	YES, 2.2-3.6V
PIC24FJ128GC010	YES, 2.2-3.6V
PIC24FJ128GL302	YES, 2.0-3.6V
PIC24FJ128GL303	YES, 2.0-3.6V
PIC24FJ128GL305	YES, 2.0-3.6V
PIC24FJ128GL306	YES, 2.0-3.6V
PIC24FJ16GA002	YES, 2.6-3.6V
PIC24FJ16GA004	YES, 2.6-3.6V
PIC24FJ16MC101	YES, 3.0-3.6V
PIC24FJ16MC102	YES, 3.0-3.6V
PIC24FJ192GA106	YES, 2.6-3.6V
PIC24FJ192GA108	YES, 2.6-3.6V



PIC24FJ192GA110	YES, 2.6-3.6V
PIC24FJ192GB106	YES, 2.6-3.6V
PIC24FJ192GB108	YES, 2.6-3.6V
PIC24FJ192GB110	YES, 2.6-3.6V
PIC24FJ256DA106	YES, 2.6-3.6V
PIC24FJ256DA110	YES, 2.6-3.6V
PIC24FJ256DA206	YES, 2.6-3.6V
PIC24FJ256DA210	YES, 2.6-3.6V
PIC24FJ256GA106	YES, 2.6-3.6V
PIC24FJ256GA108	YES, 2.6-3.6V
PIC24FJ256GA110	YES, 2.6-3.6V
PIC24FJ256GA406	YES, 2.0-3.6V 4)
PIC24FJ256GA410	YES, 2.0-3.6V 4)
PIC24FJ256GA412	YES, 2.0-3.6V 4)
PIC24FJ256GA606	YES, 2.0-3.6V 4)
PIC24FJ256GA610	YES, 2.0-3.6V 4)
PIC24FJ256GA702	YES, 2.0-3.6V
PIC24FJ256GA704	YES, 2.0-3.6V
PIC24FJ256GA705	YES, 2.0-3.6V
PIC24FJ256GB106	YES, 2.6-3.6V
PIC24FJ256GB108	YES, 2.6-3.6V
PIC24FJ256GB110	YES, 2.6-3.6V
PIC24FJ256GB206	YES, 2.6-3.6V
PIC24FJ256GB210	YES, 2.6-3.6V
PIC24FJ256GB406	YES, 2.0-3.6V 4)
PIC24FJ256GB410	YES, 2.0-3.6V 4)
PIC24FJ256GB412	YES, 2.0-3.6V 4)
PIC24FJ256GB606	YES, 2.0-3.6V 4)
PIC24FJ256GB610	YES, 2.0-3.6V 4)
PIC24FJ32GA002	YES, 2.6-3.6V
PIC24FJ32GA004	YES, 2.6-3.6V
PIC24FJ32GA102	YES, 2.6-3.6V
PIC24FJ32GA104	YES, 2.6-3.6V
PIC24FJ32GB002	YES, 2.6-3.6V
PIC24FJ32GB004	YES, 2.6-3.6V
PIC24FJ32MC101	YES, 3.0-3.6V
PIC24FJ32MC102	YES, 3.0-3.6V
PIC24FJ32MC104	YES, 3.0-3.6V
PIC24FJ48GA002	YES, 2.6-3.6V
PIC24FJ48GA004	YES, 2.6-3.6V
PIC24FJ512GA606	YES, 2.0-3.6V 4)
PIC24FJ512GA610	YES, 2.0-3.6V 4)
PIC24FJ512GB606	YES, 2.0-3.6V 4)
PIC24FJ512GB610	YES, 2.0-3.6V 4)
PIC24FJ64GA002	YES, 2.6-3.6V
PIC24FJ64GA004	YES, 2.6-3.6V
PIC24FJ64GA006	YES, 2.6-3.6V
PIC24FJ64GA008	YES, 2.6-3.6V
PIC24FJ64GA010	YES, 2.6-3.6V
PIC24FJ64GA102	YES, 2.6-3.6V
PIC24FJ64GA104	YES, 2.6-3.6V
PIC24FJ64GA106	YES, 2.6-3.6V
PIC24FJ64GA108	YES, 2.6-3.6V
PIC24FJ64GA110	YES, 2.6-3.6V
PIC24FJ64GA202	YES, 2.2-3.6V
PIC24FJ64GA204	YES, 2.2-3.6V
PIC24FJ64GA306	YES, 2.6-3.6V
PIC24FJ64GA308	YES, 2.6-3.6V
PIC24FJ64GA310	YES, 2.6-3.6V

PIC24FJ64GA406	YES, 2.0-3.6V 4)
PIC24FJ64GA410	YES, 2.0-3.6V 4)
PIC24FJ64GA412	YES, 2.0-3.6V 4)
PIC24FJ64GA702	YES, 2.0-3.6V
PIC24FJ64GA704	YES, 2.0-3.6V
PIC24FJ64GA705	YES, 2.0-3.6V
PIC24FJ64GB002	YES, 2.6-3.6V
PIC24FJ64GB004	YES, 2.6-3.6V
PIC24FJ64GB106	YES, 2.6-3.6V
PIC24FJ64GB108	YES, 2.6-3.6V
PIC24FJ64GB110	YES, 2.6-3.6V
PIC24FJ64GB202	YES, 2.2-3.6V
PIC24FJ64GB204	YES, 2.2-3.6V
PIC24FJ64GB406	YES, 2.0-3.6V 4)
PIC24FJ64GB410	YES, 2.0-3.6V 4)
PIC24FJ64GB412	YES, 2.0-3.6V 4)
PIC24FJ64GC006	YES, 2.2-3.6V
PIC24FJ64GC010	YES, 2.2-3.6V
PIC24FJ64GL302	YES, 2.0-3.6V
PIC24FJ64GL303	YES, 2.0-3.6V
PIC24FJ64GL305	YES, 2.0-3.6V
PIC24FJ64GL306	YES, 2.0-3.6V
PIC24FJ96GA006	YES, 2.6-3.6V
PIC24FJ96GA008	YES, 2.6-3.6V
PIC24FJ96GA010	YES, 2.6-3.6V
PIC24FV08KM101	YES, 2.0-5.5V
PIC24FV08KM102	YES, 2.0-5.5V
PIC24FV08KM202	YES, 2.0-5.5V
PIC24FV08KM204	YES, 2.0-5.5V
PIC24FV16KA301	YES, 2.6-5.5V
PIC24FV16KA302	YES, 2.6-5.5V
PIC24FV16KA304	YES, 2.6-5.5V
PIC24FV16KM102	YES, 2.0-5.5V
PIC24FV16KM104	YES, 2.0-5.5V
PIC24FV16KM202	YES, 2.0-5.5V
PIC24FV16KM204	YES, 2.0-5.5V
PIC24FV32KA301	YES, 2.6-5.5V
PIC24FV32KA302	YES, 2.6-5.5V
PIC24FV32KA304	YES, 2.6-5.5V
PIC24HJ128GP202	YES, 3.0-3.6V
PIC24HJ128GP204	YES, 3.0-3.6V
PIC24HJ128GP206	YES, 3.0-3.6V
PIC24HJ128GP206A	YES, 3.0-3.6V
PIC24HJ128GP210	YES, 3.0-3.6V
PIC24HJ128GP210A	YES, 3.0-3.6V
PIC24HJ128GP306	YES, 3.0-3.6V
PIC24HJ128GP306A	YES, 3.0-3.6V
PIC24HJ128GP310	YES, 3.0-3.6V
PIC24HJ128GP310A	YES, 3.0-3.6V
PIC24HJ128GP502	YES, 3.0-3.6V
PIC24HJ128GP504	YES, 3.0-3.6V
PIC24HJ128GP506	YES, 3.0-3.6V
PIC24HJ128GP506A	YES, 3.0-3.6V
PIC24HJ128GP510	YES, 3.0-3.6V
PIC24HJ128GP510A	YES, 3.0-3.6V
PIC24HJ12GP201	YES, 3.0-3.6V
PIC24HJ12GP202	YES, 3.0-3.6V
PIC24HJ16GP304	YES, 3.0-3.6V
PIC24HJ256GP206	YES, 3.0-3.6V

PIC24HJ256GP206A	YES, 3.0-3.6V
PIC24HJ256GP210	YES, 3.0-3.6V
PIC24HJ256GP210A	YES, 3.0-3.6V
PIC24HJ256GP610	YES, 3.0-3.6V
PIC24HJ256GP610A	YES, 3.0-3.6V
PIC24HJ32GP202	YES, 3.0-3.6V
PIC24HJ32GP204	YES, 3.0-3.6V
PIC24HJ32GP302	YES, 3.0-3.6V
PIC24HJ32GP304	YES, 3.0-3.6V
PIC24HJ64GP202	YES, 3.0-3.6V
PIC24HJ64GP204	YES, 3.0-3.6V
PIC24HJ64GP206	YES, 3.0-3.6V
PIC24HJ64GP206A	YES, 3.0-3.6V
PIC24HJ64GP210	YES, 3.0-3.6V
PIC24HJ64GP210A	YES, 3.0-3.6V
PIC24HJ64GP502	YES, 3.0-3.6V
PIC24HJ64GP504	YES, 3.0-3.6V
PIC24HJ64GP506	YES, 3.0-3.6V
PIC24HJ64GP506A	YES, 3.0-3.6V
PIC24HJ64GP510	YES, 3.0-3.6V
PIC24HJ64GP510A	YES, 3.0-3.6V
<b>PIC32MK</b>	
PIC32MK0512GPD064	YES, 2.2-3.6V
PIC32MK0512GPD100	YES, 2.2-3.6V
PIC32MK0512GPE064	YES, 2.2-3.6V
PIC32MK0512GPE100	YES, 2.2-3.6V
PIC32MK0512GPK064	YES, 2.3-3.6V
PIC32MK0512GPK100	YES, 2.3-3.6V
PIC32MK0512MCF064	YES, 2.2-3.6V
PIC32MK0512MCF100	YES, 2.2-3.6V
PIC32MK0512MCM064	YES, 2.3-3.6V
PIC32MK0512MCM100	YES, 2.3-3.6V
PIC32MK1024GPD064	YES, 2.2-3.6V
PIC32MK1024GPD100	YES, 2.2-3.6V
PIC32MK1024GPE064	YES, 2.2-3.6V
PIC32MK1024GPE100	YES, 2.2-3.6V
PIC32MK1024GPK064	YES, 2.3-3.6V
PIC32MK1024GPK100	YES, 2.3-3.6V
PIC32MK1024MCF064	YES, 2.2-3.6V
PIC32MK1024MCF100	YES, 2.2-3.6V
PIC32MK1024MCM064	YES, 2.3-3.6V
PIC32MK1024MCM100	YES, 2.3-3.6V
<b>PIC32MM</b>	
PIC32MM0016GPL020	YES, 2.0-3.6V
PIC32MM0016GPL028	YES, 2.0-3.6V
PIC32MM0016GPL036	YES, 2.0-3.6V
PIC32MM0032GPL020	YES, 2.0-3.6V
PIC32MM0032GPL028	YES, 2.0-3.6V
PIC32MM0032GPL036	YES, 2.0-3.6V
PIC32MM0064GPL020	YES, 2.0-3.6V
PIC32MM0064GPL028	YES, 2.0-3.6V
PIC32MM0064GPL036	YES, 2.0-3.6V
PIC32MM0064GPM028	YES, 2.0-3.6V
PIC32MM0064GPM036	YES, 2.0-3.6V
PIC32MM0064GPM048	YES, 2.0-3.6V
PIC32MM0064GPM064	YES, 2.0-3.6V
PIC32MM0128GPM028	YES, 2.0-3.6V
PIC32MM0128GPM036	YES, 2.0-3.6V
PIC32MM0128GPM048	YES, 2.0-3.6V

PIC32MM0128GPM064	YES, 2.0-3.6V
PIC32MM0256GPM028	YES, 2.0-3.6V
PIC32MM0256GPM036	YES, 2.0-3.6V
PIC32MM0256GPM048	YES, 2.0-3.6V
PIC32MM0256GPM064	YES, 2.0-3.6V
<b>PIC32MX</b>	
PIC32MX110F016B	YES, 2.3-3.6V
PIC32MX110F016C	YES, 2.3-3.6V
PIC32MX110F016D	YES, 2.3-3.6V
PIC32MX120F032B	YES, 2.3-3.6V
PIC32MX120F032C	YES, 2.3-3.6V
PIC32MX120F032D	YES, 2.3-3.6V
PIC32MX120F064H	YES, 2.3-3.6V
PIC32MX130F064B	YES, 2.3-3.6V
PIC32MX130F064C	YES, 2.3-3.6V
PIC32MX130F064D	YES, 2.3-3.6V
PIC32MX130F128H	YES, 2.3-3.6V
PIC32MX130F128L	YES, 2.3-3.6V
PIC32MX130F256B	YES, 2.3-3.6V
PIC32MX130F256D	YES, 2.3-3.6V
PIC32MX150F128B	YES, 2.3-3.6V
PIC32MX150F128C	YES, 2.3-3.6V
PIC32MX150F128D	YES, 2.3-3.6V
PIC32MX150F256H	YES, 2.3-3.6V
PIC32MX150F256L	YES, 2.3-3.6V
PIC32MX170F256B	YES, 2.3-3.6V
PIC32MX170F256D	YES, 2.3-3.6V
PIC32MX170F512H	YES, 2.3-3.6V
PIC32MX170F512L	YES, 2.3-3.6V
PIC32MX210F016B	YES, 2.3-3.6V
PIC32MX210F016C	YES, 2.3-3.6V
PIC32MX210F016D	YES, 2.3-3.6V
PIC32MX220F032B	YES, 2.3-3.6V
PIC32MX220F032C	YES, 2.3-3.6V
PIC32MX220F032D	YES, 2.3-3.6V
PIC32MX230F064B	YES, 2.3-3.6V
PIC32MX230F064C	YES, 2.3-3.6V
PIC32MX230F064D	YES, 2.3-3.6V
PIC32MX230F128H	YES, 2.3-3.6V
PIC32MX230F128L	YES, 2.3-3.6V
PIC32MX230F256B	YES, 2.3-3.6V
PIC32MX230F256D	YES, 2.3-3.6V
PIC32MX250F128B	YES, 2.3-3.6V
PIC32MX250F128C	YES, 2.3-3.6V
PIC32MX250F128D	YES, 2.3-3.6V
PIC32MX250F256H	YES, 2.3-3.6V
PIC32MX250F256L	YES, 2.3-3.6V
PIC32MX270F256B	YES, 2.3-3.6V
PIC32MX270F256D	YES, 2.3-3.6V
PIC32MX270F512H	YES, 2.3-3.6V
PIC32MX270F512L	YES, 2.3-3.6V
PIC32MX320F032H	YES, 3.0-3.6V
PIC32MX320F064H	YES, 3.0-3.6V
PIC32MX320F128H	YES, 3.0-3.6V
PIC32MX320F128L	YES, 3.0-3.6V
PIC32MX330F064H	YES, 2.3-3.6V
PIC32MX330F064L	YES, 2.3-3.6V
PIC32MX340F128H	YES, 3.0-3.6V
PIC32MX340F128L	YES, 3.0-3.6V

PIC32MX340F256H	YES, 3.0-3.6V
PIC32MX340F512H	YES, 3.0-3.6V
PIC32MX350F128H	YES, 2.3-3.6V
PIC32MX350F128L	YES, 2.3-3.6V
PIC32MX350F256H	YES, 2.3-3.6V
PIC32MX350F256L	YES, 2.3-3.6V
PIC32MX360F256L	YES, 3.0-3.6V
PIC32MX360F512L	YES, 3.0-3.6V
PIC32MX370F512H	YES, 2.3-3.6V
PIC32MX370F512L	YES, 2.3-3.6V
PIC32MX420F032H	YES, 3.0-3.6V
PIC32MX430F064H	YES, 2.3-3.6V
PIC32MX430F064L	YES, 2.3-3.6V
PIC32MX440F128H	YES, 3.0-3.6V
PIC32MX440F128L	YES, 3.0-3.6V
PIC32MX440F256H	YES, 3.0-3.6V
PIC32MX440F512H	YES, 3.0-3.6V
PIC32MX450F128H	YES, 2.3-3.6V
PIC32MX450F128L	YES, 2.3-3.6V
PIC32MX450F256H	YES, 2.3-3.6V
PIC32MX450F256L	YES, 2.3-3.6V
PIC32MX460F256L	YES, 3.0-3.6V
PIC32MX460F512L	YES, 3.0-3.6V
PIC32MX470F512H	YES, 2.3-3.6V
PIC32MX470F512L	YES, 2.3-3.6V
PIC32MX530F128H	YES, 2.3-3.6V
PIC32MX530F128L	YES, 2.3-3.6V
PIC32MX534F064H	YES, 3.0-3.6V
PIC32MX534F064L	YES, 3.0-3.6V
PIC32MX550F256H	YES, 2.3-3.6V
PIC32MX550F256L	YES, 2.3-3.6V
PIC32MX564F064H	YES, 3.0-3.6V
PIC32MX564F064L	YES, 3.0-3.6V
PIC32MX564F128H	YES, 3.0-3.6V
PIC32MX564F128L	YES, 3.0-3.6V
PIC32MX570F512L	YES, 2.3-3.6V
PIC32MX575F256H	YES, 3.0-3.6V
PIC32MX575F256L	YES, 3.0-3.6V
PIC32MX575F512H	YES, 3.0-3.6V
PIC32MX575F512L	YES, 3.0-3.6V
PIC32MX664F064H	YES, 3.0-3.6V
PIC32MX664F064L	YES, 3.0-3.6V
PIC32MX664F128H	YES, 3.0-3.6V
PIC32MX664F128L	YES, 3.0-3.6V
PIC32MX675F256H	YES, 3.0-3.6V
PIC32MX675F256L	YES, 3.0-3.6V
PIC32MX675F512H	YES, 3.0-3.6V
PIC32MX675F512L	YES, 3.0-3.6V
PIC32MX695F512H	YES, 3.0-3.6V
PIC32MX695F512L	YES, 3.0-3.6V
PIC32MX764F128H	YES, 3.0-3.6V
PIC32MX764F128L	YES, 3.0-3.6V
PIC32MX775F256H	YES, 3.0-3.6V
PIC32MX775F256L	YES, 3.0-3.6V
PIC32MX775F512H	YES, 3.0-3.6V
PIC32MX775F512L	YES, 3.0-3.6V
PIC32MX795F512H	YES, 3.0-3.6V
PIC32MX795F512L	YES, 3.0-3.6V
PIC32MZ	

PIC32MZ0512EFE064	YES, 2.1-3.6V
PIC32MZ0512EFE100	YES, 2.1-3.6V
PIC32MZ0512EFE124	YES, 2.1-3.6V
PIC32MZ0512EFE144	YES, 2.1-3.6V
PIC32MZ0512EFF064	YES, 2.1-3.6V
PIC32MZ0512EFF100	YES, 2.1-3.6V
PIC32MZ0512EFF124	YES, 2.1-3.6V
PIC32MZ0512EFF144	YES, 2.1-3.6V
PIC32MZ0512EFK064	YES, 2.1-3.6V
PIC32MZ0512EFK100	YES, 2.1-3.6V
PIC32MZ0512EFK124	YES, 2.1-3.6V
PIC32MZ0512EFK144	YES, 2.1-3.6V
PIC32MZ1024ECG064	YES, 2.3-3.6V
PIC32MZ1024ECG100	YES, 2.3-3.6V
PIC32MZ1024ECG124	YES, 2.3-3.6V
PIC32MZ1024ECG144	YES, 2.3-3.6V
PIC32MZ1024ECM064	YES, 2.3-3.6V
PIC32MZ1024ECM100	YES, 2.3-3.6V
PIC32MZ1024ECM124	YES, 2.3-3.6V
PIC32MZ1024ECM144	YES, 2.3-3.6V
PIC32MZ1024EFE064	YES, 2.1-3.6V
PIC32MZ1024EFE100	YES, 2.1-3.6V
PIC32MZ1024EFE124	YES, 2.1-3.6V
PIC32MZ1024EFE144	YES, 2.1-3.6V
PIC32MZ1024EFF064	YES, 2.1-3.6V
PIC32MZ1024EFF100	YES, 2.1-3.6V
PIC32MZ1024EFF124	YES, 2.1-3.6V
PIC32MZ1024EFF144	YES, 2.1-3.6V
PIC32MZ1024EFG064	YES, 2.1-3.6V
PIC32MZ1024EFG100	YES, 2.1-3.6V
PIC32MZ1024EFG124	YES, 2.1-3.6V
PIC32MZ1024EFG144	YES, 2.1-3.6V
PIC32MZ1024EFH064	YES, 2.1-3.6V
PIC32MZ1024EFH100	YES, 2.1-3.6V
PIC32MZ1024EFH124	YES, 2.1-3.6V
PIC32MZ1024EFH144	YES, 2.1-3.6V
PIC32MZ1024EFK064	YES, 2.1-3.6V
PIC32MZ1024EFK100	YES, 2.1-3.6V
PIC32MZ1024EFK124	YES, 2.1-3.6V
PIC32MZ1024EFK144	YES, 2.1-3.6V
PIC32MZ1024EFM064	YES, 2.1-3.6V
PIC32MZ1024EFM100	YES, 2.1-3.6V
PIC32MZ1024EFM124	YES, 2.1-3.6V
PIC32MZ1024EFM144	YES, 2.1-3.6V
PIC32MZ1024ECH064	YES, 2.3-3.6V
PIC32MZ1024ECH100	YES, 2.3-3.6V
PIC32MZ1024ECH124	YES, 2.3-3.6V
PIC32MZ1024ECH144	YES, 2.3-3.6V
PIC32MZ2048ECG064	YES, 2.3-3.6V
PIC32MZ2048ECG100	YES, 2.3-3.6V
PIC32MZ2048ECG124	YES, 2.3-3.6V
PIC32MZ2048ECG144	YES, 2.3-3.6V
PIC32MZ2048ECM064	YES, 2.3-3.6V
PIC32MZ2048ECM100	YES, 2.3-3.6V
PIC32MZ2048ECM124	YES, 2.3-3.6V
PIC32MZ2048ECM144	YES, 2.3-3.6V
PIC32MZ2048EFG064	YES, 2.1-3.6V
PIC32MZ2048EFG100	YES, 2.1-3.6V
PIC32MZ2048EFG124	YES, 2.1-3.6V

PIC32MZ2048EFG144	YES, 2.1-3.6V
PIC32MZ2048EFH064	YES, 2.1-3.6V
PIC32MZ2048EFH100	YES, 2.1-3.6V
PIC32MZ2048EFH124	YES, 2.1-3.6V
PIC32MZ2048EFH144	YES, 2.1-3.6V
PIC32MZ2048EFM064	YES, 2.1-3.6V
PIC32MZ2048EFM100	YES, 2.1-3.6V
PIC32MZ2048EFM124	YES, 2.1-3.6V
PIC32MZ2048EFM144	YES, 2.1-3.6V
PIC32MZ2048ECH064	YES, 2.3-3.6V
PIC32MZ2048ECH100	YES, 2.3-3.6V
PIC32MZ2048ECH124	YES, 2.3-3.6V
PIC32MZ2048ECH144	YES, 2.3-3.6V
<b>dsPIC30F</b>	
dsPIC30F1010	YES, 3.0-5.5V
dsPIC30F2010	YES, 2.5-5.5V
dsPIC30F2011	YES, 2.5-5.5V
dsPIC30F2012	YES, 2.5-5.5V
dsPIC30F2020	YES, 3.0-5.5V
dsPIC30F2023	YES, 3.0-5.5V
dsPIC30F3010	YES, 2.5-5.5V
dsPIC30F3011	YES, 2.5-5.5V
dsPIC30F3012	YES, 2.5-5.5V
dsPIC30F3013	YES, 2.5-5.5V
dsPIC30F3014	YES, 2.5-5.5V
dsPIC30F4011	YES, 2.5-5.5V
dsPIC30F4012	YES, 2.5-5.5V
dsPIC30F4013	YES, 2.5-5.5V
dsPIC30F5011	YES, 2.5-5.5V
dsPIC30F5013	YES, 2.5-5.5V
dsPIC30F5015	YES, 2.5-5.5V
dsPIC30F5016	YES, 2.5-5.5V
dsPIC30F6010	YES, 2.5-5.5V
dsPIC30F6010A	YES, 2.5-5.5V
dsPIC30F6011	YES, 2.5-5.5V
dsPIC30F6011A	YES, 2.5-5.5V
dsPIC30F6012	YES, 2.5-5.5V
dsPIC30F6012A	YES, 2.5-5.5V
dsPIC30F6013	YES, 2.5-5.5V
dsPIC30F6013A	YES, 2.5-5.5V
dsPIC30F6014	YES, 2.5-5.5V
dsPIC30F6014A	YES, 2.5-5.5V
dsPIC30F6015	YES, 2.5-5.5V
<b>dsPIC33</b>	
dsPIC33CK128MP202	YES, 3.0-3.6V 4)
dsPIC33CK128MP203	YES, 3.0-3.6V 4)
dsPIC33CK128MP205	YES, 3.0-3.6V 4)
dsPIC33CK128MP206	YES, 3.0-3.6V 4)
dsPIC33CK128MP208	YES, 3.0-3.6V 4)
dsPIC33CK128MP502	YES, 3.0-3.6V 4)
dsPIC33CK128MP503	YES, 3.0-3.6V 4)
dsPIC33CK128MP505	YES, 3.0-3.6V 4)
dsPIC33CK128MP506	YES, 3.0-3.6V 4)
dsPIC33CK128MP508	YES, 3.0-3.6V 4)
dsPIC33CK256MP202	YES, 3.0-3.6V 4)
dsPIC33CK256MP203	YES, 3.0-3.6V 4)
dsPIC33CK256MP205	YES, 3.0-3.6V 4)
dsPIC33CK256MP206	YES, 3.0-3.6V 4)
dsPIC33CK256MP208	YES, 3.0-3.6V 4)

dsPIC33CK256MP502	YES, 3.0-3.6V 4)
dsPIC33CK256MP503	YES, 3.0-3.6V 4)
dsPIC33CK256MP505	YES, 3.0-3.6V 4)
dsPIC33CK256MP506	YES, 3.0-3.6V 4)
dsPIC33CK256MP508	YES, 3.0-3.6V 4)
dsPIC33CK32MP202	YES, 3.0-3.6V 4)
dsPIC33CK32MP203	YES, 3.0-3.6V 4)
dsPIC33CK32MP205	YES, 3.0-3.6V 4)
dsPIC33CK32MP206	YES, 3.0-3.6V 4)
dsPIC33CK32MP502	YES, 3.0-3.6V 4)
dsPIC33CK32MP503	YES, 3.0-3.6V 4)
dsPIC33CK32MP505	YES, 3.0-3.6V 4)
dsPIC33CK32MP506	YES, 3.0-3.6V 4)
dsPIC33CK64MP202	YES, 3.0-3.6V 4)
dsPIC33CK64MP203	YES, 3.0-3.6V 4)
dsPIC33CK64MP205	YES, 3.0-3.6V 4)
dsPIC33CK64MP206	YES, 3.0-3.6V 4)
dsPIC33CK64MP208	YES, 3.0-3.6V 4)
dsPIC33CK64MP502	YES, 3.0-3.6V 4)
dsPIC33CK64MP503	YES, 3.0-3.6V 4)
dsPIC33CK64MP505	YES, 3.0-3.6V 4)
dsPIC33CK64MP506	YES, 3.0-3.6V 4)
dsPIC33CK64MP508	YES, 3.0-3.6V 4)
dsPIC33EP128GM304	YES, 3.0-3.6V
dsPIC33EP128GM306	YES, 3.0-3.6V
dsPIC33EP128GM310	YES, 3.0-3.6V
dsPIC33EP128GM604	YES, 3.0-3.6V
dsPIC33EP128GM706	YES, 3.0-3.6V
dsPIC33EP128GM710	YES, 3.0-3.6V
dsPIC33EP128GP502	YES, 3.0-3.6V
dsPIC33EP128GP504	YES, 3.0-3.6V
dsPIC33EP128GP506	YES, 3.0-3.6V
dsPIC33EP128GS702	YES, 3.0-3.6V 4)
dsPIC33EP128GS704	YES, 3.0-3.6V 4)
dsPIC33EP128GS705	YES, 3.0-3.6V 4)
dsPIC33EP128GS706	YES, 3.0-3.6V 4)
dsPIC33EP128GS708	YES, 3.0-3.6V 4)
dsPIC33EP128GS804	YES, 3.0-3.6V 4)
dsPIC33EP128GS805	YES, 3.0-3.6V 4)
dsPIC33EP128GS806	YES, 3.0-3.6V 4)
dsPIC33EP128GS808	YES, 3.0-3.6V 4)
dsPIC33EP128MC202	YES, 3.0-3.6V
dsPIC33EP128MC204	YES, 3.0-3.6V
dsPIC33EP128MC206	YES, 3.0-3.6V
dsPIC33EP128MC502	YES, 3.0-3.6V
dsPIC33EP128MC504	YES, 3.0-3.6V
dsPIC33EP128MC506	YES, 3.0-3.6V
dsPIC33EP16GS202	YES, 3.0-3.6V
dsPIC33EP16GS502	YES, 3.0-3.6V
dsPIC33EP16GS504	YES, 3.0-3.6V
dsPIC33EP16GS505	YES, 3.0-3.6V
dsPIC33EP16GS506	YES, 3.0-3.6V
dsPIC33EP256GM304	YES, 3.0-3.6V
dsPIC33EP256GM306	YES, 3.0-3.6V
dsPIC33EP256GM310	YES, 3.0-3.6V
dsPIC33EP256GM604	YES, 3.0-3.6V
dsPIC33EP256GM706	YES, 3.0-3.6V
dsPIC33EP256GM710	YES, 3.0-3.6V
dsPIC33EP256GP502	YES, 3.0-3.6V



dsPIC33EP256GP504	YES, 3.0-3.6V
dsPIC33EP256GP506	YES, 3.0-3.6V
dsPIC33EP256MC202	YES, 3.0-3.6V
dsPIC33EP256MC204	YES, 3.0-3.6V
dsPIC33EP256MC206	YES, 3.0-3.6V
dsPIC33EP256MC502	YES, 3.0-3.6V
dsPIC33EP256MC504	YES, 3.0-3.6V
dsPIC33EP256MC506	YES, 3.0-3.6V
dsPIC33EP256MU806	YES, 3.0-3.6V
dsPIC33EP256MU810	YES, 3.0-3.6V
dsPIC33EP256MU814	YES, 3.0-3.6V
dsPIC33EP32GP502	YES, 3.0-3.6V
dsPIC33EP32GP503	YES, 3.0-3.6V
dsPIC33EP32GP504	YES, 3.0-3.6V
dsPIC33EP32GS202	YES, 3.0-3.6V
dsPIC33EP32GS502	YES, 3.0-3.6V
dsPIC33EP32GS504	YES, 3.0-3.6V
dsPIC33EP32GS505	YES, 3.0-3.6V
dsPIC33EP32GS506	YES, 3.0-3.6V
dsPIC33EP32MC202	YES, 3.0-3.6V
dsPIC33EP32MC203	YES, 3.0-3.6V
dsPIC33EP32MC204	YES, 3.0-3.6V
dsPIC33EP32MC502	YES, 3.0-3.6V
dsPIC33EP32MC503	YES, 3.0-3.6V
dsPIC33EP32MC504	YES, 3.0-3.6V
dsPIC33EP512GM304	YES, 3.0-3.6V
dsPIC33EP512GM306	YES, 3.0-3.6V
dsPIC33EP512GM310	YES, 3.0-3.6V
dsPIC33EP512GM604	YES, 3.0-3.6V
dsPIC33EP512GM706	YES, 3.0-3.6V
dsPIC33EP512GM710	YES, 3.0-3.6V
dsPIC33EP512GP502	YES, 3.0-3.6V
dsPIC33EP512GP504	YES, 3.0-3.6V
dsPIC33EP512GP506	YES, 3.0-3.6V
dsPIC33EP512GP806	YES, 3.0-3.6V
dsPIC33EP512MC502	YES, 3.0-3.6V
dsPIC33EP512MC504	YES, 3.0-3.6V
dsPIC33EP512MC506	YES, 3.0-3.6V
dsPIC33EP512MC806	YES, 3.0-3.6V
dsPIC33EP512MU810	YES, 3.0-3.6V
dsPIC33EP512MU814	YES, 3.0-3.6V
dsPIC33EP64GP502	YES, 3.0-3.6V
dsPIC33EP64GP503	YES, 3.0-3.6V
dsPIC33EP64GP504	YES, 3.0-3.6V
dsPIC33EP64GP506	YES, 3.0-3.6V
dsPIC33EP64GS502	YES, 3.0-3.6V 4)
dsPIC33EP64GS504	YES, 3.0-3.6V 4)
dsPIC33EP64GS505	YES, 3.0-3.6V 4)
dsPIC33EP64GS506	YES, 3.0-3.6V 4)
dsPIC33EP64GS708	YES, 3.0-3.6V 4)
dsPIC33EP64GS804	YES, 3.0-3.6V 4)
dsPIC33EP64GS805	YES, 3.0-3.6V 4)
dsPIC33EP64GS806	YES, 3.0-3.6V 4)
dsPIC33EP64GS808	YES, 3.0-3.6V 4)
dsPIC33EP64MC202	YES, 3.0-3.6V
dsPIC33EP64MC203	YES, 3.0-3.6V
dsPIC33EP64MC204	YES, 3.0-3.6V
dsPIC33EP64MC206	YES, 3.0-3.6V
dsPIC33EP64MC502	YES, 3.0-3.6V

dsPIC33EP64MC503	YES, 3.0-3.6V
dsPIC33EP64MC504	YES, 3.0-3.6V
dsPIC33EP64MC506	YES, 3.0-3.6V
dsPIC33EV128GM002	YES, 4.7-5.5V
dsPIC33EV128GM004	YES, 4.7-5.5V
dsPIC33EV128GM006	YES, 4.7-5.5V
dsPIC33EV128GM102	YES, 4.7-5.5V
dsPIC33EV128GM104	YES, 4.7-5.5V
dsPIC33EV128GM106	YES, 4.7-5.5V
dsPIC33EV256GM002	YES, 4.7-5.5V
dsPIC33EV256GM004	YES, 4.7-5.5V
dsPIC33EV256GM006	YES, 4.7-5.5V
dsPIC33EV256GM102	YES, 4.7-5.5V
dsPIC33EV256GM104	YES, 4.7-5.5V
dsPIC33EV256GM106	YES, 4.7-5.5V
dsPIC33EV32GM002	YES, 4.7-5.5V
dsPIC33EV32GM004	YES, 4.7-5.5V
dsPIC33EV32GM006	YES, 4.7-5.5V
dsPIC33EV32GM102	YES, 4.7-5.5V
dsPIC33EV32GM104	YES, 4.7-5.5V
dsPIC33EV32GM106	YES, 4.7-5.5V
dsPIC33EV64GM002	YES, 4.7-5.5V
dsPIC33EV64GM004	YES, 4.7-5.5V
dsPIC33EV64GM006	YES, 4.7-5.5V
dsPIC33EV64GM102	YES, 4.7-5.5V
dsPIC33EV64GM104	YES, 4.7-5.5V
dsPIC33EV64GM106	YES, 4.7-5.5V
dsPIC33FJ06GS001	YES, 3.0-3.6V
dsPIC33FJ06GS101	YES, 3.0-3.6V
dsPIC33FJ06GS101A	YES, 3.0-3.6V
dsPIC33FJ06GS102	YES, 3.0-3.6V
dsPIC33FJ06GS102A	YES, 3.0-3.6V
dsPIC33FJ06GS202	YES, 3.0-3.6V
dsPIC33FJ06GS202A	YES, 3.0-3.6V
dsPIC33FJ09GS302	YES, 3.0-3.6V
dsPIC33FJ128GP202	YES, 3.0-3.6V
dsPIC33FJ128GP204	YES, 3.0-3.6V
dsPIC33FJ128GP206	YES, 3.0-3.6V
dsPIC33FJ128GP206A	YES, 3.0-3.6V
dsPIC33FJ128GP306	YES, 3.0-3.6V
dsPIC33FJ128GP306A	YES, 3.0-3.6V
dsPIC33FJ128GP310	YES, 3.0-3.6V
dsPIC33FJ128GP310A	YES, 3.0-3.6V
dsPIC33FJ128GP706	YES, 3.0-3.6V
dsPIC33FJ128GP706A	YES, 3.0-3.6V
dsPIC33FJ128GP708	YES, 3.0-3.6V
dsPIC33FJ128GP708A	YES, 3.0-3.6V
dsPIC33FJ128GP710	YES, 3.0-3.6V
dsPIC33FJ128GP710A	YES, 3.0-3.6V
dsPIC33FJ128GP802	YES, 3.0-3.6V
dsPIC33FJ128GP804	YES, 3.0-3.6V
dsPIC33FJ128MC202	YES, 3.0-3.6V
dsPIC33FJ128MC204	YES, 3.0-3.6V
dsPIC33FJ128MC506	YES, 3.0-3.6V
dsPIC33FJ128MC506A	YES, 3.0-3.6V
dsPIC33FJ128MC510	YES, 3.0-3.6V
dsPIC33FJ128MC510A	YES, 3.0-3.6V
dsPIC33FJ128MC706	YES, 3.0-3.6V
dsPIC33FJ128MC706A	YES, 3.0-3.6V

dsPIC33FJ128MC708	YES, 3.0-3.6V
dsPIC33FJ128MC708A	YES, 3.0-3.6V
dsPIC33FJ128MC710	YES, 3.0-3.6V
dsPIC33FJ128MC710A	YES, 3.0-3.6V
dsPIC33FJ128MC802	YES, 3.0-3.6V
dsPIC33FJ128MC804	YES, 3.0-3.6V
dsPIC33FJ12GP201	YES, 3.0-3.6V
dsPIC33FJ12GP202	YES, 3.0-3.6V
dsPIC33FJ12MC201	YES, 3.0-3.6V
dsPIC33FJ12MC202	YES, 3.0-3.6V
dsPIC33FJ16GP101	YES, 3.0-3.6V
dsPIC33FJ16GP102	YES, 3.0-3.6V
dsPIC33FJ16GP304	YES, 3.0-3.6V
dsPIC33FJ16GS402	YES, 3.0-3.6V
dsPIC33FJ16GS404	YES, 3.0-3.6V
dsPIC33FJ16GS502	YES, 3.0-3.6V
dsPIC33FJ16GS504	YES, 3.0-3.6V
dsPIC33FJ16MC101	YES, 3.0-3.6V
dsPIC33FJ16MC102	YES, 3.0-3.6V
dsPIC33FJ16MC304	YES, 3.0-3.6V
dsPIC33FJ256GP506	YES, 3.0-3.6V
dsPIC33FJ256GP506A	YES, 3.0-3.6V
dsPIC33FJ256GP510	YES, 3.0-3.6V
dsPIC33FJ256GP510A	YES, 3.0-3.6V
dsPIC33FJ256GP710	YES, 3.0-3.6V
dsPIC33FJ256GP710A	YES, 3.0-3.6V
dsPIC33FJ256MC510	YES, 3.0-3.6V
dsPIC33FJ256MC510A	YES, 3.0-3.6V
dsPIC33FJ256MC710	YES, 3.0-3.6V
dsPIC33FJ256MC710A	YES, 3.0-3.6V
dsPIC33FJ32GP101	YES, 3.0-3.6V
dsPIC33FJ32GP102	YES, 3.0-3.6V
dsPIC33FJ32GP104	YES, 3.0-3.6V
dsPIC33FJ32GP202	YES, 3.0-3.6V
dsPIC33FJ32GP204	YES, 3.0-3.6V
dsPIC33FJ32GP302	YES, 3.0-3.6V
dsPIC33FJ32GP304	YES, 3.0-3.6V
dsPIC33FJ32GS406	YES, 3.0-3.6V
dsPIC33FJ32GS606	YES, 3.0-3.6V
dsPIC33FJ32GS608	YES, 3.0-3.6V
dsPIC33FJ32GS610	YES, 3.0-3.6V
dsPIC33FJ32MC101	YES, 3.0-3.6V
dsPIC33FJ32MC102	YES, 3.0-3.6V
dsPIC33FJ32MC104	YES, 3.0-3.6V
dsPIC33FJ32MC202	YES, 3.0-3.6V
dsPIC33FJ32MC204	YES, 3.0-3.6V
dsPIC33FJ32MC302	YES, 3.0-3.6V
dsPIC33FJ32MC304	YES, 3.0-3.6V
dsPIC33FJ64GP202	YES, 3.0-3.6V
dsPIC33FJ64GP204	YES, 3.0-3.6V
dsPIC33FJ64GP206	YES, 3.0-3.6V
dsPIC33FJ64GP206A	YES, 3.0-3.6V
dsPIC33FJ64GP306	YES, 3.0-3.6V
dsPIC33FJ64GP306A	YES, 3.0-3.6V
dsPIC33FJ64GP310	YES, 3.0-3.6V
dsPIC33FJ64GP310A	YES, 3.0-3.6V
dsPIC33FJ64GP706	YES, 3.0-3.6V
dsPIC33FJ64GP706A	YES, 3.0-3.6V
dsPIC33FJ64GP708	YES, 3.0-3.6V

dsPIC33FJ64GP708A	YES, 3.0-3.6V
dsPIC33FJ64GP710	YES, 3.0-3.6V
dsPIC33FJ64GP710A	YES, 3.0-3.6V
dsPIC33FJ64GP802	YES, 3.0-3.6V
dsPIC33FJ64GP804	YES, 3.0-3.6V
dsPIC33FJ64GS406	YES, 3.0-3.6V
dsPIC33FJ64GS606	YES, 3.0-3.6V
dsPIC33FJ64GS608	YES, 3.0-3.6V
dsPIC33FJ64GS610	YES, 3.0-3.6V
dsPIC33FJ64MC202	YES, 3.0-3.6V
dsPIC33FJ64MC204	YES, 3.0-3.6V
dsPIC33FJ64MC506	YES, 3.0-3.6V
dsPIC33FJ64MC506A	YES, 3.0-3.6V
dsPIC33FJ64MC508	YES, 3.0-3.6V
dsPIC33FJ64MC508A	YES, 3.0-3.6V
dsPIC33FJ64MC510	YES, 3.0-3.6V
dsPIC33FJ64MC510A	YES, 3.0-3.6V
dsPIC33FJ64MC706	YES, 3.0-3.6V
dsPIC33FJ64MC706A	YES, 3.0-3.6V
dsPIC33FJ64MC710	YES, 3.0-3.6V
dsPIC33FJ64MC710A	YES, 3.0-3.6V
dsPIC33FJ64MC802	YES, 3.0-3.6V
dsPIC33FJ64MC804	YES, 3.0-3.6V
dsPIC33CH256MP205	YES, 3.0-3.6V 4)
dsPIC33CH256MP206	YES, 3.0-3.6V 4)
dsPIC33CH256MP208	YES, 3.0-3.6V 4)
dsPIC33CH256MP505	YES, 3.0-3.6V 4)
dsPIC33CH256MP506	YES, 3.0-3.6V 4)
dsPIC33CH256MP508	YES, 3.0-3.6V 4)
dsPIC33CH512MP205	YES, 3.0-3.6V 4)
dsPIC33CH512MP206	YES, 3.0-3.6V 4)
dsPIC33CH512MP208	YES, 3.0-3.6V 4)
dsPIC33CH512MP505	YES, 3.0-3.6V 4)
dsPIC33CH512MP506	YES, 3.0-3.6V 4)
dsPIC33CH512MP508	YES, 3.0-3.6V 4)
<b>AVR</b>	
AT86RF401	YES, 2.0-5.0V
AT90CAN128	YES, 2.7-5.5V
AT90CAN32	YES, 2.7-5.5V
AT90CAN64	YES, 2.7-5.5V
AT90PWM1	YES, 2.7-5.5V
AT90PWM161	YES, 2.7-5.5V
AT90PWM2	YES, 2.7-5.5V
AT90PWM216	YES, 2.7-5.5V
AT90PWM2B	YES, 2.7-5.5V
AT90PWM3	YES, 2.7-5.5V
AT90PWM316	YES, 2.7-5.5V
AT90PWM3B	YES, 2.7-5.5V
AT90PWM81	YES, 2.7-5.5V
AT90S1200	YES, 2.7-5.5V
AT90S2313	YES, 2.7-5.5V
AT90S2323	YES, 2.7-5.5V
AT90S2343	YES, 2.7-5.5V
AT90S4414	YES, 2.7-5.5V
AT90S8515	YES, 2.7-5.5V
AT90S8535	YES, 2.7-5.5V
AT90USB1286	YES, 2.7-5.5V
AT90USB1287	YES, 2.7-5.5V
AT90USB162	YES, 2.7-5.5V

AT90USB646	YES, 2.7-5.5V
AT90USB647	YES, 2.7-5.5V
AT90USB82	YES, 2.7-5.5V
ATmega103	YES, 2.7-5.5V
ATmega128	YES, 2.7-5.5V
ATmega1280	YES, 1.8-5.5V
ATmega1281	YES, 1.8-5.5V
ATmega1284	YES, 1.8-5.5V
ATmega1284P	YES, 1.8-5.5V
ATmega128A	YES, 2.7-5.5V
ATmega16	YES, 2.7-5.5V
ATmega161	YES, 2.7-5.5V
ATmega162	YES, 1.8-5.5V
ATmega163	YES, 2.7-5.5V
ATmega164A	YES, 1.8-5.5V
ATmega164P	YES, 1.8-5.5V
ATmega164PA	YES, 1.8-5.5V
ATmega165	YES, 1.8-5.5V
ATmega165A	YES, 1.8-5.5V
ATmega165PA	YES, 1.8-5.5V
ATmega168	YES, 1.8-5.5V
ATmega168A	YES, 1.8-5.5V
ATmega168P	YES, 1.8-5.5V
ATmega168PA	YES, 1.8-5.5V
ATmega168PB	YES, 1.8-5.5V
ATmega169	YES, 1.8-5.5V
ATmega169A	YES, 1.8-5.5V
ATmega169PA	YES, 1.8-5.5V
ATmega16A	YES, 2.7-5.5V
ATmega16M1	YES, 2.7-5.5V
ATmega16U2	YES, 2.7-5.5V
ATmega16U4	YES, 2.7-5.5V
ATmega2560	YES, 1.8-5.5V
ATmega2561	YES, 1.8-5.5V
ATmega256RFR2	YES, 1.8-3.6V
ATmega32	YES, 2.7-5.5V
ATmega324A	YES, 1.8-5.5V
ATmega324P	YES, 1.8-5.5V
ATmega324PA	YES, 1.8-5.5V
ATmega324PB	YES, 1.8-5.5V
ATmega325	YES, 1.8-5.5V
ATmega3250	YES, 1.8-5.5V
ATmega3250A	YES, 1.8-5.5V
ATmega3250P	YES, 1.8-5.5V
ATmega3250PA	YES, 1.8-5.5V
ATmega325A	YES, 1.8-5.5V
ATmega325P	YES, 1.8-5.5V
ATmega325PA	YES, 1.8-5.5V
ATmega328	YES, 1.8-5.5V
ATmega328P	YES, 1.8-5.5V
ATmega328PB	YES, 1.8-5.5V
ATmega329	YES, 1.8-5.5V
ATmega3290	YES, 1.8-5.5V
ATmega3290A	YES, 1.8-5.5V
ATmega3290P	YES, 1.8-5.5V
ATmega3290PA	YES, 1.8-5.5V
ATmega329A	YES, 1.8-5.5V
ATmega329P	YES, 1.8-5.5V
ATmega329PA	YES, 1.8-5.5V

ATmega32A	YES, 2.7-5.5V
ATmega32C1	YES, 2.7-5.5V
ATmega32M1	YES, 2.7-5.5V
ATmega32U2	YES, 2.7-5.5V
ATmega32U4	YES, 2.7-5.5V
ATmega48	YES, 1.8-5.5V
ATmega48A	YES, 1.8-5.5V
ATmega48P	YES, 1.8-5.5V
ATmega48PA	YES, 1.8-5.5V
ATmega48PB	YES, 1.8-5.5V
ATmega64	YES, 2.7-5.5V
ATmega640	YES, 1.8-5.5V
ATmega644	YES, 1.8-5.5V
ATmega644A	YES, 1.8-5.5V
ATmega644P	YES, 1.8-5.5V
ATmega644PA	YES, 1.8-5.5V
ATmega645	YES, 1.8-5.5V
ATmega6450	YES, 1.8-5.5V
ATmega6450A	YES, 1.8-5.5V
ATmega6450P	YES, 1.8-5.5V
ATmega645A	YES, 1.8-5.5V
ATmega645P	YES, 1.8-5.5V
ATmega649	YES, 1.8-5.5V
ATmega6490	YES, 1.8-5.5V
ATmega6490A	YES, 1.8-5.5V
ATmega6490P	YES, 1.8-5.5V
ATmega649A	YES, 1.8-5.5V
ATmega649P	YES, 1.8-5.5V
ATmega64A	YES, 2.7-5.5V
ATmega64C1	YES, 2.7-5.5V
ATmega64M1	YES, 2.7-5.5V
ATmega8	YES, 2.7-5.5V
ATmega8515	YES, 2.7-5.5V
ATmega8535	YES, 2.7-5.5V
ATmega88	YES, 1.8-5.5V
ATmega88A	YES, 1.8-5.5V
ATmega88P	YES, 1.8-5.5V
ATmega88PA	YES, 1.8-5.5V
ATmega88PB	YES, 1.8-5.5V
ATmega8A	YES, 2.7-5.5V
ATmega8U2	YES, 2.7-5.5V
ATtiny12	YES, 1.8-5.5V
ATtiny13	YES, 1.8-5.5V
ATtiny15	YES, 2.7-5.5V
ATtiny1634	YES, 1.8-5.5V
ATtiny167	YES, 1.8-5.5V
ATtiny2313	YES, 1.8-5.5V
ATtiny2313A	YES, 1.8-5.5V
ATtiny24	YES, 1.8-5.5V
ATtiny24A	YES, 1.8-5.5V
ATtiny25	YES, 1.8-5.5V
ATtiny26	YES, 2.7-5.5V
ATtiny261	YES, 1.8-5.5V
ATtiny261A	YES, 1.8-5.5V
ATtiny4313	YES, 1.8-5.5V
ATtiny44	YES, 1.8-5.5V
ATtiny441	YES, 1.8-5.5V
ATtiny44A	YES, 1.8-5.5V
ATtiny45	YES, 1.8-5.5V

ATtiny461	YES, 1.8-5.5V
ATtiny461A	YES, 1.8-5.5V
ATtiny48	YES, 1.8-5.5V
ATtiny828	YES, 1.8-5.5V
ATtiny84	YES, 1.8-5.5V
ATtiny841	YES, 1.8-5.5V
ATtiny84A	YES, 1.8-5.5V
ATtiny85	YES, 1.8-5.5V
ATtiny861	YES, 1.8-5.5V
ATtiny861A	YES, 1.8-5.5V
ATtiny87	YES, 1.8-5.5V
ATtiny88	YES, 1.8-5.5V
<b>AVR TPI</b>	
ATtiny10	YES, 4.5-5.5V
ATtiny102	YES, 2.7-5.5V
ATtiny104	YES, 2.7-5.5V
ATtiny20	YES, 4.5-5.5V
ATtiny4	YES, 4.5-5.5V
ATtiny40	YES, 4.5-5.5V
ATtiny5	YES, 4.5-5.5V
ATtiny9	YES, 4.5-5.5V
<b>AVR UPDI</b>	
ATmega1608	YES, 3.0-5.5V
ATmega1609	YES, 3.0-5.5V
ATmega3208	YES, 3.0-5.5V
ATmega3209	YES, 3.0-5.5V
ATmega4808	YES, 3.0-5.5V
ATmega4809	YES, 3.0-5.5V
ATmega808	YES, 3.0-5.5V
ATmega809	YES, 3.0-5.5V
ATtiny1604	YES, 1.8-5.5V
ATtiny1606	YES, 1.8-5.5V
ATtiny1607	YES, 1.8-5.5V
ATtiny1614	YES, 1.8-5.5V
ATtiny1616	YES, 1.8-5.5V
ATtiny1617	YES, 1.8-5.5V
ATtiny202	YES, 1.8-5.5V
ATtiny204	YES, 1.8-5.5V
ATtiny212	YES, 1.8-5.5V
ATtiny214	YES, 1.8-5.5V
ATtiny3216	YES, 1.8-5.5V
ATtiny3217	YES, 1.8-5.5V
ATtiny402	YES, 1.8-5.5V
ATtiny404	YES, 1.8-5.5V
ATtiny406	YES, 1.8-5.5V
ATtiny412	YES, 1.8-5.5V
ATtiny414	YES, 1.8-5.5V
ATtiny416	YES, 1.8-5.5V
ATtiny417	YES, 1.8-5.5V
ATtiny804	YES, 1.8-5.5V
ATtiny806	YES, 1.8-5.5V
ATtiny807	YES, 1.8-5.5V
ATtiny814	YES, 1.8-5.5V
ATtiny816	YES, 1.8-5.5V
ATtiny817	YES, 1.8-5.5V
AVR128DA28	YES, 1.8-5.5V
AVR128DA32	YES, 1.8-5.5V
AVR128DA48	YES, 1.8-5.5V
AVR128DA64	YES, 1.8-5.5V

AVR128DB28	YES, 1.8-5.5V
AVR128DB32	YES, 1.8-5.5V
AVR128DB48	YES, 1.8-5.5V
AVR128DB64	YES, 1.8-5.5V
AVR32DA28	YES, 1.8-5.5V
AVR32DA32	YES, 1.8-5.5V
AVR32DA48	YES, 1.8-5.5V
AVR64DA28	YES, 1.8-5.5V
AVR64DA32	YES, 1.8-5.5V
AVR64DA48	YES, 1.8-5.5V
AVR64DA64	YES, 1.8-5.5V
<b>AVR ATxmega</b>	
ATxmega128A1	YES, 1.8-3.6V
ATxmega128A1U	YES, 1.8-3.6V
ATxmega128A3	YES, 1.8-3.6V
ATxmega128A3U	YES, 1.8-3.6V
ATxmega128A4	YES, 1.8-3.6V
ATxmega128B1	YES, 1.8-3.6V
ATxmega128B3	YES, 1.8-3.6V
ATxmega128D3	YES, 1.8-3.6V
ATxmega128D4	YES, 1.8-3.6V
ATxmega16A4	YES, 1.8-3.6V
ATxmega16A4U	YES, 1.8-3.6V
ATxmega16D4	YES, 1.8-3.6V
ATxmega16E5	YES, 1.8-3.6V
ATxmega192A3U	YES, 1.8-3.6V
ATxmega192C3	YES, 1.8-3.6V
ATxmega192D3	YES, 1.8-3.6V
ATxmega256A3	YES, 1.8-3.6V
ATxmega256A3BU	YES, 1.8-3.6V
ATxmega256A3U	YES, 1.8-3.6V
ATxmega256C3	YES, 1.8-3.6V
ATxmega256D3	YES, 1.8-3.6V
ATxmega32A4	YES, 1.8-3.6V
ATxmega32A4U	YES, 1.8-3.6V
ATxmega32D4	YES, 1.8-3.6V
ATxmega32E5	YES, 1.8-3.6V
ATxmega384C3	YES, 1.8-3.6V
ATxmega384D3	YES, 1.8-3.6V
ATxmega64A1	YES, 1.8-3.6V
ATxmega64A1U	YES, 1.8-3.6V
ATxmega64A3	YES, 1.8-3.6V
ATxmega64A3U	YES, 1.8-3.6V
ATxmega64A4	YES, 1.8-3.6V
ATxmega64C3	YES, 1.8-3.6V
ATxmega64D3	YES, 1.8-3.6V
ATxmega64D4	YES, 1.8-3.6V
ATxmega8E5	YES, 1.8-3.6V
<b>AVR-32</b>	
AT32UC3A0128	YES, 3.0-3.6V
AT32UC3A0256	YES, 3.0-3.6V
AT32UC3A0512	YES, 3.0-3.6V
AT32UC3A1128	YES, 3.0-3.6V
AT32UC3A1256	YES, 3.0-3.6V
AT32UC3A1512	YES, 3.0-3.6V
AT32UC3A3128	YES, 3.0-3.6V
AT32UC3A3128S	YES, 3.0-3.6V
AT32UC3A3256	YES, 3.0-3.6V
AT32UC3A3256S	YES, 3.0-3.6V



AT32UC3A364	YES, 3.0-3.6V
AT32UC3A364S	YES, 3.0-3.6V
AT32UC3B0128	YES, 3.0-3.6V
AT32UC3B0256	YES, 3.0-3.6V
AT32UC3B0512	YES, 3.0-3.6V
AT32UC3B064	YES, 3.0-3.6V
AT32UC3B1128	YES, 3.0-3.6V
AT32UC3B1256	YES, 3.0-3.6V
AT32UC3B1512	YES, 3.0-3.6V
AT32UC3B164	YES, 3.0-3.6V
AT32UC3C0128C	YES, 3.0-5.5V
AT32UC3C0256C	YES, 3.0-5.5V
AT32UC3C0512C	YES, 3.0-5.5V
AT32UC3C064C	YES, 3.0-5.5V
AT32UC3C1128C	YES, 3.0-5.5V
AT32UC3C1256C	YES, 3.0-5.5V
AT32UC3C1512C	YES, 3.0-5.5V
AT32UC3C164C	YES, 3.0-5.5V
AT32UC3C2128C	YES, 3.0-5.5V
AT32UC3C2256C	YES, 3.0-5.5V
AT32UC3C2512C	YES, 3.0-5.5V
AT32UC3C264C	YES, 3.0-5.5V
AT32UC3L016	YES, 1.8-3.6V
AT32UC3L032	YES, 1.8-3.6V
AT32UC3L064	YES, 1.8-3.6V
<b>Atmel 8051 arch.</b>	
AT89C51CC01UA	YES, 3.0-5.5V
AT89LP2052	YES, 2.4-5.5V
AT89LP213	YES, 2.4-5.5V
AT89LP214	YES, 2.4-5.5V
AT89LP216	YES, 2.4-5.5V
AT89LP3240	YES, 2.4-3.6V
AT89LP4052	YES, 2.4-5.5V
AT89LP428	YES, 2.4-5.5V
AT89LP51	YES, 2.4-5.5V
AT89LP51ED2	YES, 2.4-5.5V
AT89LP51IC2	YES, 2.4-5.5V
AT89LP51ID2	YES, 2.4-5.5V
AT89LP51RB2	YES, 2.4-5.5V
AT89LP51RC2	YES, 2.4-5.5V
AT89LP51RD2	YES, 2.4-5.5V
AT89LP52	YES, 2.4-5.5V
AT89LP6440	YES, 2.4-3.6V
AT89LP828	YES, 2.4-5.5V
AT89LS51	YES, 2.7-4.0V
AT89LS52	YES, 2.7-4.0V
AT89S2051	YES, 2.7-5.5V
AT89S4051	YES, 2.7-5.5V
AT89S51	YES, 4.0-5.5V
AT89S52	YES, 4.0-5.5V
AT89S53	YES, 4.0-5.5V
AT89S8252	YES, 4.0-5.5V
AT89S8253	YES, 2.7-5.5V
<b>ARM</b>	
AT91SAM7S128	YES, 1.8-3.6V
AT91SAM7S16	YES, 1.8-3.6V
AT91SAM7S161	YES, 1.8-3.6V
AT91SAM7S256	YES, 1.8-3.6V
AT91SAM7S32	YES, 1.8-3.6V

AT91SAM7S321	YES, 1.8-3.6V
AT91SAM7S512	YES, 1.8-3.6V
AT91SAM7S64	YES, 1.8-3.6V
AT91SAM7SE256	YES, 1.8-3.6V
AT91SAM7SE32	YES, 1.8-3.6V
AT91SAM7SE512	YES, 1.8-3.6V
AT91SAM7X128	YES, 3.0-3.6V
AT91SAM7X256	YES, 3.0-3.6V
AT91SAM7X512	YES, 3.0-3.6V
AT91SAM7XC128	YES, 3.0-3.6V
AT91SAM7XC256	YES, 3.0-3.6V
AT91SAM7XC512	YES, 3.0-3.6V
ATSAM3A4C	YES, 1.8-3.6V
ATSAM3A8C	YES, 1.8-3.6V
ATSAM3N00A	YES, 1.8-3.6V
ATSAM3N00B	YES, 1.8-3.6V
ATSAM3N0A	YES, 1.8-3.6V
ATSAM3N0B	YES, 1.8-3.6V
ATSAM3N0C	YES, 1.8-3.6V
ATSAM3N1A	YES, 1.8-3.6V
ATSAM3N1B	YES, 1.8-3.6V
ATSAM3N1C	YES, 1.8-3.6V
ATSAM3N2A	YES, 1.8-3.6V
ATSAM3N2B	YES, 1.8-3.6V
ATSAM3N2C	YES, 1.8-3.6V
ATSAM3N4A	YES, 1.8-3.6V
ATSAM3N4B	YES, 1.8-3.6V
ATSAM3N4C	YES, 1.8-3.6V
ATSAM3S1A	YES, 1.8-3.6V
ATSAM3S1B	YES, 1.8-3.6V
ATSAM3S1C	YES, 1.8-3.6V
ATSAM3S2A	YES, 1.8-3.6V
ATSAM3S2B	YES, 1.8-3.6V
ATSAM3S2C	YES, 1.8-3.6V
ATSAM3S4A	YES, 1.8-3.6V
ATSAM3S4B	YES, 1.8-3.6V
ATSAM3S4C	YES, 1.8-3.6V
ATSAM3S8B	YES, 1.8-3.6V
ATSAM3S8C	YES, 1.8-3.6V
ATSAM3SD8B	YES, 1.8-3.6V
ATSAM3SD8C	YES, 1.8-3.6V
ATSAM3U1C	YES, 1.8-3.6V
ATSAM3U1E	YES, 1.8-3.6V
ATSAM3U2C	YES, 1.8-3.6V
ATSAM3U2E	YES, 1.8-3.6V
ATSAM3U4C	YES, 1.8-3.6V
ATSAM3U4E	YES, 1.8-3.6V
ATSAM3X4C	YES, 1.8-3.6V
ATSAM3X4E	YES, 1.8-3.6V
ATSAM3X8C	YES, 1.8-3.6V
ATSAM3X8E	YES, 1.8-3.6V
ATSAM4E16C	YES, 1.8-3.6V
ATSAM4E16E	YES, 1.8-3.6V
ATSAM4E8C	YES, 1.8-3.6V
ATSAM4E8E	YES, 1.8-3.6V
ATSAM4LC2A	YES, 1.8-3.6V
ATSAM4LC2B	YES, 1.8-3.6V
ATSAM4LC2C	YES, 1.8-3.6V
ATSAM4LC4A	YES, 1.8-3.6V

ATSAM4LC4B	YES, 1.8-3.6V
ATSAM4LC4C	YES, 1.8-3.6V
ATSAM4LC8A	YES, 1.8-3.6V
ATSAM4LC8B	YES, 1.8-3.6V
ATSAM4LC8C	YES, 1.8-3.6V
ATSAM4LS2A	YES, 1.8-3.6V
ATSAM4LS2B	YES, 1.8-3.6V
ATSAM4LS2C	YES, 1.8-3.6V
ATSAM4LS4A	YES, 1.8-3.6V
ATSAM4LS4B	YES, 1.8-3.6V
ATSAM4LS4C	YES, 1.8-3.6V
ATSAM4LS8A	YES, 1.8-3.6V
ATSAM4LS8B	YES, 1.8-3.6V
ATSAM4LS8C	YES, 1.8-3.6V
ATSAM4N16B	YES, 1.8-3.6V
ATSAM4N16C	YES, 1.8-3.6V
ATSAM4N8A	YES, 1.8-3.6V
ATSAM4N8B	YES, 1.8-3.6V
ATSAM4N8C	YES, 1.8-3.6V
ATSAM4S16B	YES, 1.8-3.6V
ATSAM4S16C	YES, 1.8-3.6V
ATSAM4S2A	YES, 1.8-3.6V
ATSAM4S2B	YES, 1.8-3.6V
ATSAM4S2C	YES, 1.8-3.6V
ATSAM4S4A	YES, 1.8-3.6V
ATSAM4S4B	YES, 1.8-3.6V
ATSAM4S4C	YES, 1.8-3.6V
ATSAM4S8B	YES, 1.8-3.6V
ATSAM4S8C	YES, 1.8-3.6V
ATSAM4SA16B	YES, 1.8-3.6V
ATSAM4SA16C	YES, 1.8-3.6V
ATSAM4SD16B	YES, 1.8-3.6V
ATSAM4SD16C	YES, 1.8-3.6V
ATSAM4SD32B	YES, 1.8-3.6V
ATSAM4SD32C	YES, 1.8-3.6V
ATSAMC20E15A	YES, 2.7-5.5V
ATSAMC20E16A	YES, 2.7-5.5V
ATSAMC20E17A	YES, 2.7-5.5V
ATSAMC20E18A	YES, 2.7-5.5V
ATSAMC20G15A	YES, 2.7-5.5V
ATSAMC20G16A	YES, 2.7-5.5V
ATSAMC20G17A	YES, 2.7-5.5V
ATSAMC20G18A	YES, 2.7-5.5V
ATSAMC20J15A	YES, 2.7-5.5V
ATSAMC20J16A	YES, 2.7-5.5V
ATSAMC20J17A	YES, 2.7-5.5V
ATSAMC20J18A	YES, 2.7-5.5V
ATSAMC20N17A	YES, 2.7-5.5V
ATSAMC20N18A	YES, 2.7-5.5V
ATSAMC21E15A	YES, 2.7-5.5V
ATSAMC21E16A	YES, 2.7-5.5V
ATSAMC21E17A	YES, 2.7-5.5V
ATSAMC21E18A	YES, 2.7-5.5V
ATSAMC21G15A	YES, 2.7-5.5V
ATSAMC21G16A	YES, 2.7-5.5V
ATSAMC21G17A	YES, 2.7-5.5V
ATSAMC21G18A	YES, 2.7-5.5V
ATSAMC21J15A	YES, 2.7-5.5V
ATSAMC21J16A	YES, 2.7-5.5V

ATSAMC21J17A	YES, 2.7-5.5V
ATSAMC21J18A	YES, 2.7-5.5V
ATSAMC21N17A	YES, 2.7-5.5V
ATSAMC21N18A	YES, 2.7-5.5V
ATSAMD09C13A	YES, 1.8-3.6V
ATSAMD09D14A	YES, 1.8-3.6V
ATSAMD10C13A	YES, 1.8-3.6V
ATSAMD10C14A	YES, 1.8-3.6V
ATSAMD10D13A	YES, 1.8-3.6V
ATSAMD10D14A	YES, 1.8-3.6V
ATSAMD11C14A	YES, 1.8-3.6V
ATSAMD11D14A	YES, 1.8-3.6V
ATSAMD20E14A/B	YES, 1.8-3.6V
ATSAMD20E15A/B	YES, 1.8-3.6V
ATSAMD20E16A/B	YES, 1.8-3.6V
ATSAMD20E17A/B	YES, 1.8-3.6V
ATSAMD20E18A/B	YES, 1.8-3.6V
ATSAMD20G14A/B	YES, 1.8-3.6V
ATSAMD20G15A/B	YES, 1.8-3.6V
ATSAMD20G16A/B	YES, 1.8-3.6V
ATSAMD20G17A/B	YES, 1.8-3.6V
ATSAMD20G18A/B	YES, 1.8-3.6V
ATSAMD20J14A/B	YES, 1.8-3.6V
ATSAMD20J15A/B	YES, 1.8-3.6V
ATSAMD20J16A/B	YES, 1.8-3.6V
ATSAMD20J17A/B	YES, 1.8-3.6V
ATSAMD20J18A/B	YES, 1.8-3.6V
ATSAMD21E15A	YES, 1.8-3.6V
ATSAMD21E15L	YES, 1.8-3.6V
ATSAMD21E16A	YES, 1.8-3.6V
ATSAMD21E16L	YES, 1.8-3.6V
ATSAMD21E17A	YES, 1.8-3.6V
ATSAMD21E17L	YES, 1.8-3.6V
ATSAMD21E18A	YES, 1.8-3.6V
ATSAMD21G15A	YES, 1.8-3.6V
ATSAMD21G15L	YES, 1.8-3.6V
ATSAMD21G16A	YES, 1.8-3.6V
ATSAMD21G16L	YES, 1.8-3.6V
ATSAMD21G17A	YES, 1.8-3.6V
ATSAMD21G17L	YES, 1.8-3.6V
ATSAMD21G18A	YES, 1.8-3.6V
ATSAMD21J15A	YES, 1.8-3.6V
ATSAMD21J16A	YES, 1.8-3.6V
ATSAMD21J17A	YES, 1.8-3.6V
ATSAMD21J18A	YES, 1.8-3.6V
ATSAMD51G18A	YES, 1.8-3.6V
ATSAMD51G19A	YES, 1.8-3.6V
ATSAMD51J18A	YES, 1.8-3.6V
ATSAMD51J19A	YES, 1.8-3.6V
ATSAMD51J20A	YES, 1.8-3.6V
ATSAMD51N19A	YES, 1.8-3.6V
ATSAMD51N20A	YES, 1.8-3.6V
ATSAMD51P19A	YES, 1.8-3.6V
ATSAMD51P20A	YES, 1.8-3.6V
ATSAMDA1E14B	YES, 2.7-3.6V
ATSAMDA1E15B	YES, 2.7-3.6V
ATSAMDA1E16B	YES, 2.7-3.6V
ATSAMDA1G14B	YES, 2.7-3.6V
ATSAMDA1G15B	YES, 2.7-3.6V

ATSAMDA1G16B	YES, 2.7-3.6V
ATSAMDA1J14B	YES, 2.7-3.6V
ATSAMDA1J15B	YES, 2.7-3.6V
ATSAMDA1J16B	YES, 2.7-3.6V
ATSAME51G18A	YES, 1.8-3.6V
ATSAME51G19A	YES, 1.8-3.6V
ATSAME51J18A	YES, 1.8-3.6V
ATSAME51J19A	YES, 1.8-3.6V
ATSAME51J20A	YES, 1.8-3.6V
ATSAME51N19A	YES, 1.8-3.6V
ATSAME51N20A	YES, 1.8-3.6V
ATSAME53J18A	YES, 1.8-3.6V
ATSAME53J19A	YES, 1.8-3.6V
ATSAME53J20A	YES, 1.8-3.6V
ATSAME53N19A	YES, 1.8-3.6V
ATSAME53N20A	YES, 1.8-3.6V
ATSAME54N19A	YES, 1.8-3.6V
ATSAME54N20A	YES, 1.8-3.6V
ATSAME54P19A	YES, 1.8-3.6V
ATSAME54P20A	YES, 1.8-3.6V
ATSAME70J19	YES, 1.8-3.6V
ATSAME70J20	YES, 1.8-3.6V
ATSAME70J21	YES, 1.8-3.6V
ATSAME70N19	YES, 1.8-3.6V
ATSAME70N20	YES, 1.8-3.6V
ATSAME70N21	YES, 1.8-3.6V
ATSAME70Q19	YES, 1.8-3.6V
ATSAME70Q20	YES, 1.8-3.6V
ATSAME70Q21	YES, 1.8-3.6V
ATSAMG51G18	YES, 1.8-2.0V
ATSAMG51N18	YES, 1.8-2.0V
ATSAMG53G19	YES, 1.8-3.6V
ATSAMG53N19	YES, 1.8-3.6V
ATSAMG54G19B	YES, 1.8-3.4V
ATSAMG54N19B	YES, 1.8-3.4V
ATSAMG55G19	YES, 1.8-3.6V
ATSAMG55J19	YES, 1.8-3.6V
ATSAML21E15B	YES, 1.8-3.6V
ATSAML21E16B	YES, 1.8-3.6V
ATSAML21E17B	YES, 1.8-3.6V
ATSAML21E18B	YES, 1.8-3.6V
ATSAML21G16B	YES, 1.8-3.6V
ATSAML21G17B	YES, 1.8-3.6V
ATSAML21G18B	YES, 1.8-3.6V
ATSAML21J16B	YES, 1.8-3.6V
ATSAML21J17B	YES, 1.8-3.6V
ATSAML21J18B	YES, 1.8-3.6V
ATSAML22G16A	YES, 1.8-3.6V
ATSAML22G17A	YES, 1.8-3.6V
ATSAML22G18A	YES, 1.8-3.6V
ATSAML22J16A	YES, 1.8-3.6V
ATSAML22J17A	YES, 1.8-3.6V
ATSAML22J18A	YES, 1.8-3.6V
ATSAML22N16A	YES, 1.8-3.6V
ATSAML22N17A	YES, 1.8-3.6V
ATSAML22N18A	YES, 1.8-3.6V
ATSAMS70J19	YES, 1.8-3.6V
ATSAMS70J20	YES, 1.8-3.6V
ATSAMS70J21	YES, 1.8-3.6V

ATSAMS70N19	YES, 1.8-3.6V
ATSAMS70N20	YES, 1.8-3.6V
ATSAMS70N21	YES, 1.8-3.6V
ATSAMS70Q19	YES, 1.8-3.6V
ATSAMS70Q20	YES, 1.8-3.6V
ATSAMS70Q21	YES, 1.8-3.6V
ATSAMV70J19	YES, 1.8-3.6V
ATSAMV70J20	YES, 1.8-3.6V
ATSAMV70N19	YES, 1.8-3.6V
ATSAMV70N20	YES, 1.8-3.6V
ATSAMV70Q19	YES, 1.8-3.6V
ATSAMV70Q20	YES, 1.8-3.6V
ATSAMV71J19	YES, 1.8-3.6V
ATSAMV71J20	YES, 1.8-3.6V
ATSAMV71J21	YES, 1.8-3.6V
ATSAMV71N19	YES, 1.8-3.6V
ATSAMV71N20	YES, 1.8-3.6V
ATSAMV71N21	YES, 1.8-3.6V
ATSAMV71Q19	YES, 1.8-3.6V
ATSAMV71Q20	YES, 1.8-3.6V
ATSAMV71Q21	YES, 1.8-3.6V
BlueNRG-1	YES, 1.7-3.6V
CY8C4045FNI-DS402	YES, 1.7-5.5V
CY8C4045PVI-DS402	YES, 1.7-5.5V
CY8C4124AXI-443	YES, 1.7-5.5V
CY8C4124AXQ-443	YES, 1.7-5.5V
CY8C4124AZI-443	YES, 1.7-5.5V
CY8C4124FNI-443	YES, 1.7-5.5V
CY8C4124LQI-443	YES, 1.7-5.5V
CY8C4124LQQ-443	YES, 1.7-5.5V
CY8C4124PVI-432	YES, 1.7-5.5V
CY8C4124PVI-442	YES, 1.7-5.5V
CY8C4124PVQ-432	YES, 1.7-5.5V
CY8C4125AXI-473	YES, 1.7-5.5V
CY8C4125AXI-483	YES, 1.7-5.5V
CY8C4125AXQ-473	YES, 1.7-5.5V
CY8C4125AXQ-483	YES, 1.7-5.5V
CY8C4125AZI-473	YES, 1.7-5.5V
CY8C4125AZI-483	YES, 1.7-5.5V
CY8C4125LQI-483	YES, 1.7-5.5V
CY8C4125LQQ-483	YES, 1.7-5.5V
CY8C4125PVI-482	YES, 1.7-5.5V
CY8C4244AXQ-443	YES, 1.7-5.5V
CY8C4244AZI-443	YES, 1.7-5.5V
CY8C4244FNI-443	YES, 1.7-5.5V
CY8C4244LQI-443	YES, 1.7-5.5V
CY8C4244LQQ-443	YES, 1.7-5.5V
CY8C4244PVI-442	YES, 1.7-5.5V
CY8C4244PVQ-432	YES, 1.7-5.5V
CY8C4244PVQ-442	YES, 1.7-5.5V
CY8C4245AXI-473	YES, 1.7-5.5V
CY8C4245AXI-483	YES, 1.7-5.5V
CY8C4245AXQ-473	YES, 1.7-5.5V
CY8C4245AXQ-483	YES, 1.7-5.5V
CY8C4245AZI-473	YES, 1.7-5.5V
CY8C4245AZI-483	YES, 1.7-5.5V
CY8C4245FNI-483	YES, 1.7-5.5V
CY8C4245FNI-DS402	YES, 1.7-5.5V
CY8C4245LQI-483	YES, 1.7-5.5V

CY8C4245LQQ-483	YES, 1.7-5.5V
CY8C4245PVI-482	YES, 1.7-5.5V
CY8C4245PVI-DS402	YES, 1.7-5.5V
CY8C4245PVQ-482	YES, 1.7-5.5V
CY8C4246FNI-DS402	YES, 1.7-5.5V
CY8C4246PVI-DS402	YES, 1.7-5.5V
EFM32G200F16	YES, 2.0-3.8V
EFM32G200F32	YES, 2.0-3.8V
EFM32G200F64	YES, 2.0-3.8V
EFM32G210F128	YES, 2.0-3.8V
EFM32G222F128	YES, 2.0-3.8V
EFM32G222F32	YES, 2.0-3.8V
EFM32G222F64	YES, 2.0-3.8V
EFM32G230F128	YES, 2.0-3.8V
EFM32G230F32	YES, 2.0-3.8V
EFM32G230F64	YES, 2.0-3.8V
EFM32G232F128	YES, 2.0-3.8V
EFM32G232F32	YES, 2.0-3.8V
EFM32G232F64	YES, 2.0-3.8V
EFM32G280F128	YES, 2.0-3.8V
EFM32G280F32	YES, 2.0-3.8V
EFM32G280F64	YES, 2.0-3.8V
EFM32G290F128	YES, 2.0-3.8V
EFM32G290F32	YES, 2.0-3.8V
EFM32G290F64	YES, 2.0-3.8V
EFM32G840F128	YES, 2.0-3.8V
EFM32G840F32	YES, 2.0-3.8V
EFM32G840F64	YES, 2.0-3.8V
EFM32G842F128	YES, 2.0-3.8V
EFM32G842F32	YES, 2.0-3.8V
EFM32G842F64	YES, 2.0-3.8V
EFM32G880F128	YES, 2.0-3.8V
EFM32G880F32	YES, 2.0-3.8V
EFM32G880F64	YES, 2.0-3.8V
EFM32G890F128	YES, 2.0-3.8V
EFM32G890F32	YES, 2.0-3.8V
EFM32G890F64	YES, 2.0-3.8V
EFM32GG11B110F2048	YES, 1.8-3.8V
EFM32GG11B120F2048	YES, 1.8-3.8V
EFM32GG11B310F2048	YES, 1.8-3.8V
EFM32GG11B320F2048	YES, 1.8-3.8V
EFM32GG11B420F2048	YES, 1.8-3.8V
EFM32GG11B510F2048	YES, 1.8-3.8V
EFM32GG11B520F2048	YES, 1.8-3.8V
EFM32GG11B820F2048	YES, 1.8-3.8V
EFM32GG11B840F1024	YES, 1.8-3.8V
EFM32GG12B110F1024	YES, 1.8-3.8V
EFM32GG12B130F512	YES, 1.8-3.8V
EFM32GG12B310F1024	YES, 1.8-3.8V
EFM32GG12B330F512	YES, 1.8-3.8V
EFM32GG12B410F1024	YES, 1.8-3.8V
EFM32GG12B430F512	YES, 1.8-3.8V
EFM32GG12B510F1024	YES, 1.8-3.8V
EFM32GG12B530F512	YES, 1.8-3.8V
EFM32GG12B810F1024	YES, 1.8-3.8V
EFM32GG12B830F512	YES, 1.8-3.8V
EFM32GG230F1024	YES, 2.0-3.8V
EFM32GG230F512	YES, 2.0-3.8V
EFM32GG232F1024	YES, 2.0-3.8V

EFM32GG232F512	YES, 2.0-3.8V
EFM32GG280F1024	YES, 2.0-3.8V
EFM32GG280F512	YES, 2.0-3.8V
EFM32GG290F1024	YES, 2.0-3.8V
EFM32GG290F512	YES, 2.0-3.8V
EFM32GG295F1024	YES, 2.0-3.8V
EFM32GG295F512	YES, 2.0-3.8V
EFM32GG330F1024	YES, 2.0-3.8V
EFM32GG330F512	YES, 2.0-3.8V
EFM32GG332F1024	YES, 2.0-3.8V
EFM32GG332F512	YES, 2.0-3.8V
EFM32GG380F1024	YES, 2.0-3.8V
EFM32GG380F512	YES, 2.0-3.8V
EFM32GG390F1024	YES, 2.0-3.8V
EFM32GG390F512	YES, 2.0-3.8V
EFM32GG395F1024	YES, 2.0-3.8V
EFM32GG395F512	YES, 2.0-3.8V
EFM32GG840F1024	YES, 2.0-3.8V
EFM32GG840F512	YES, 2.0-3.8V
EFM32GG842F1024	YES, 2.0-3.8V
EFM32GG842F512	YES, 2.0-3.8V
EFM32GG880F1024	YES, 2.0-3.8V
EFM32GG880F512	YES, 2.0-3.8V
EFM32GG890F1024	YES, 2.0-3.8V
EFM32GG890F512	YES, 2.0-3.8V
EFM32GG895F1024	YES, 2.0-3.8V
EFM32GG895F512	YES, 2.0-3.8V
EFM32GG940F1024	YES, 2.0-3.8V
EFM32GG940F512	YES, 2.0-3.8V
EFM32GG942F1024	YES, 2.0-3.8V
EFM32GG942F512	YES, 2.0-3.8V
EFM32GG980F1024	YES, 2.0-3.8V
EFM32GG980F512	YES, 2.0-3.8V
EFM32GG990F1024	YES, 2.0-3.8V
EFM32GG990F512	YES, 2.0-3.8V
EFM32GG995F1024	YES, 2.0-3.8V
EFM32GG995F512	YES, 2.0-3.8V
EFM32HG108F32	YES, 2.0-3.8V
EFM32HG108F64	YES, 2.0-3.8V
EFM32HG110F32	YES, 2.0-3.8V
EFM32HG110F64	YES, 2.0-3.8V
EFM32HG210F32	YES, 2.0-3.8V
EFM32HG210F64	YES, 2.0-3.8V
EFM32HG222F32	YES, 2.0-3.8V
EFM32HG222F64	YES, 2.0-3.8V
EFM32HG308F32	YES, 2.0-3.8V
EFM32HG308F64	YES, 2.0-3.8V
EFM32HG309F32	YES, 2.0-3.8V
EFM32HG309F64	YES, 2.0-3.8V
EFM32HG310F32	YES, 2.0-3.8V
EFM32HG310F64	YES, 2.0-3.8V
EFM32HG321F32	YES, 2.0-3.8V
EFM32HG321F64	YES, 2.0-3.8V
EFM32HG322F32	YES, 2.0-3.8V
EFM32HG322F64	YES, 2.0-3.8V
EFM32HG350F32	YES, 2.0-3.8V
EFM32HG350F64	YES, 2.0-3.8V
EFM32JG12B500F1024	YES, 1.8-3.8V
EFM32JG1B100F128	YES, 2.0-3.8V



EFM32JG1B100F256	YES, 2.0-3.8V
EFM32JG1B200F128	YES, 2.0-3.8V
EFM32JG1B200F256	YES, 2.0-3.8V
EFM32LG230F128	YES, 2.0-3.8V
EFM32LG230F256	YES, 2.0-3.8V
EFM32LG230F64	YES, 2.0-3.8V
EFM32LG232F128	YES, 2.0-3.8V
EFM32LG232F256	YES, 2.0-3.8V
EFM32LG232F64	YES, 2.0-3.8V
EFM32LG280F128	YES, 2.0-3.8V
EFM32LG280F256	YES, 2.0-3.8V
EFM32LG280F64	YES, 2.0-3.8V
EFM32LG290F128	YES, 2.0-3.8V
EFM32LG290F256	YES, 2.0-3.8V
EFM32LG290F64	YES, 2.0-3.8V
EFM32LG295F128	YES, 2.0-3.8V
EFM32LG295F256	YES, 2.0-3.8V
EFM32LG295F64	YES, 2.0-3.8V
EFM32LG330F128	YES, 2.0-3.8V
EFM32LG330F256	YES, 2.0-3.8V
EFM32LG330F64	YES, 2.0-3.8V
EFM32LG332F128	YES, 2.0-3.8V
EFM32LG332F256	YES, 2.0-3.8V
EFM32LG332F64	YES, 2.0-3.8V
EFM32LG360F128	YES, 2.0-3.8V
EFM32LG360F256	YES, 2.0-3.8V
EFM32LG360F64	YES, 2.0-3.8V
EFM32LG380F128	YES, 2.0-3.8V
EFM32LG380F256	YES, 2.0-3.8V
EFM32LG380F64	YES, 2.0-3.8V
EFM32LG390F128	YES, 2.0-3.8V
EFM32LG390F256	YES, 2.0-3.8V
EFM32LG390F64	YES, 2.0-3.8V
EFM32LG395F128	YES, 2.0-3.8V
EFM32LG395F256	YES, 2.0-3.8V
EFM32LG395F64	YES, 2.0-3.8V
EFM32LG840F128	YES, 2.0-3.8V
EFM32LG840F256	YES, 2.0-3.8V
EFM32LG840F64	YES, 2.0-3.8V
EFM32LG842F128	YES, 2.0-3.8V
EFM32LG842F256	YES, 2.0-3.8V
EFM32LG842F64	YES, 2.0-3.8V
EFM32LG880F128	YES, 2.0-3.8V
EFM32LG880F256	YES, 2.0-3.8V
EFM32LG880F64	YES, 2.0-3.8V
EFM32LG890F128	YES, 2.0-3.8V
EFM32LG890F256	YES, 2.0-3.8V
EFM32LG890F64	YES, 2.0-3.8V
EFM32LG895F128	YES, 2.0-3.8V
EFM32LG895F256	YES, 2.0-3.8V
EFM32LG895F64	YES, 2.0-3.8V
EFM32LG940F128	YES, 2.0-3.8V
EFM32LG940F256	YES, 2.0-3.8V
EFM32LG940F64	YES, 2.0-3.8V
EFM32LG942F128	YES, 2.0-3.8V
EFM32LG942F256	YES, 2.0-3.8V
EFM32LG942F64	YES, 2.0-3.8V
EFM32LG980F128	YES, 2.0-3.8V
EFM32LG980F256	YES, 2.0-3.8V

EFM32LG980F64	YES, 2.0-3.8V
EFM32LG990F128	YES, 2.0-3.8V
EFM32LG990F256	YES, 2.0-3.8V
EFM32LG990F64	YES, 2.0-3.8V
EFM32LG995F128	YES, 2.0-3.8V
EFM32LG995F256	YES, 2.0-3.8V
EFM32LG995F64	YES, 2.0-3.8V
EFM32PG1B100F128	YES, 2.0-3.8V
EFM32PG1B100F256	YES, 2.0-3.8V
EFM32PG1B200F128	YES, 2.0-3.8V
EFM32PG1B200F256	YES, 2.0-3.8V
EFM32TG108F16	YES, 2.0-3.8V
EFM32TG108F32	YES, 2.0-3.8V
EFM32TG108F4	YES, 2.0-3.8V
EFM32TG108F8	YES, 2.0-3.8V
EFM32TG110F16	YES, 2.0-3.8V
EFM32TG110F32	YES, 2.0-3.8V
EFM32TG110F4	YES, 2.0-3.8V
EFM32TG110F8	YES, 2.0-3.8V
EFM32TG11B120F128	YES, 1.8-3.8V
EFM32TG11B140F64	YES, 1.8-3.8V
EFM32TG11B320F128	YES, 1.8-3.8V
EFM32TG11B340F64	YES, 1.8-3.8V
EFM32TG11B520F128	YES, 1.8-3.8V
EFM32TG11B540F64	YES, 1.8-3.8V
EFM32TG210F16	YES, 2.0-3.8V
EFM32TG210F32	YES, 2.0-3.8V
EFM32TG210F8	YES, 2.0-3.8V
EFM32TG222F16	YES, 2.0-3.8V
EFM32TG222F32	YES, 2.0-3.8V
EFM32TG222F8	YES, 2.0-3.8V
EFM32TG225F16	YES, 2.0-3.8V
EFM32TG225F32	YES, 2.0-3.8V
EFM32TG225F8	YES, 2.0-3.8V
EFM32TG230F16	YES, 2.0-3.8V
EFM32TG230F32	YES, 2.0-3.8V
EFM32TG230F8	YES, 2.0-3.8V
EFM32TG232F16	YES, 2.0-3.8V
EFM32TG232F32	YES, 2.0-3.8V
EFM32TG232F8	YES, 2.0-3.8V
EFM32TG822F16	YES, 2.0-3.8V
EFM32TG822F32	YES, 2.0-3.8V
EFM32TG822F8	YES, 2.0-3.8V
EFM32TG825F16	YES, 2.0-3.8V
EFM32TG825F32	YES, 2.0-3.8V
EFM32TG825F8	YES, 2.0-3.8V
EFM32TG840F16	YES, 2.0-3.8V
EFM32TG840F32	YES, 2.0-3.8V
EFM32TG840F8	YES, 2.0-3.8V
EFM32TG842F16	YES, 2.0-3.8V
EFM32TG842F32	YES, 2.0-3.8V
EFM32TG842F8	YES, 2.0-3.8V
EFM32WG230F128	YES, 2.0-3.8V
EFM32WG230F256	YES, 2.0-3.8V
EFM32WG230F64	YES, 2.0-3.8V
EFM32WG232F128	YES, 2.0-3.8V
EFM32WG232F256	YES, 2.0-3.8V
EFM32WG232F64	YES, 2.0-3.8V
EFM32WG280F128	YES, 2.0-3.8V

EFM32WG280F256	YES, 2.0-3.8V
EFM32WG280F64	YES, 2.0-3.8V
EFM32WG290F128	YES, 2.0-3.8V
EFM32WG290F256	YES, 2.0-3.8V
EFM32WG290F64	YES, 2.0-3.8V
EFM32WG295F128	YES, 2.0-3.8V
EFM32WG295F256	YES, 2.0-3.8V
EFM32WG295F64	YES, 2.0-3.8V
EFM32WG330F128	YES, 2.0-3.8V
EFM32WG330F256	YES, 2.0-3.8V
EFM32WG330F64	YES, 2.0-3.8V
EFM32WG332F128	YES, 2.0-3.8V
EFM32WG332F256	YES, 2.0-3.8V
EFM32WG332F64	YES, 2.0-3.8V
EFM32WG360F128G	YES, 2.0-3.8V
EFM32WG360F256G	YES, 2.0-3.8V
EFM32WG360F64G	YES, 2.0-3.8V
EFM32WG380F128	YES, 2.0-3.8V
EFM32WG380F256	YES, 2.0-3.8V
EFM32WG380F64	YES, 2.0-3.8V
EFM32WG390F128	YES, 2.0-3.8V
EFM32WG390F256	YES, 2.0-3.8V
EFM32WG390F64	YES, 2.0-3.8V
EFM32WG395F128	YES, 2.0-3.8V
EFM32WG395F256	YES, 2.0-3.8V
EFM32WG395F64	YES, 2.0-3.8V
EFM32WG840F128	YES, 2.0-3.8V
EFM32WG840F256	YES, 2.0-3.8V
EFM32WG840F64	YES, 2.0-3.8V
EFM32WG842F128	YES, 2.0-3.8V
EFM32WG842F256	YES, 2.0-3.8V
EFM32WG842F64	YES, 2.0-3.8V
EFM32WG880F128	YES, 2.0-3.8V
EFM32WG880F256	YES, 2.0-3.8V
EFM32WG880F64	YES, 2.0-3.8V
EFM32WG890F128	YES, 2.0-3.8V
EFM32WG890F256	YES, 2.0-3.8V
EFM32WG890F64	YES, 2.0-3.8V
EFM32WG895F128	YES, 2.0-3.8V
EFM32WG895F256	YES, 2.0-3.8V
EFM32WG895F64	YES, 2.0-3.8V
EFM32WG940F128	YES, 2.0-3.8V
EFM32WG940F256	YES, 2.0-3.8V
EFM32WG940F64	YES, 2.0-3.8V
EFM32WG942F128	YES, 2.0-3.8V
EFM32WG942F256	YES, 2.0-3.8V
EFM32WG942F64	YES, 2.0-3.8V
EFM32WG980F128	YES, 2.0-3.8V
EFM32WG980F256	YES, 2.0-3.8V
EFM32WG980F64	YES, 2.0-3.8V
EFM32WG990F128	YES, 2.0-3.8V
EFM32WG990F256	YES, 2.0-3.8V
EFM32WG990F64	YES, 2.0-3.8V
EFM32WG995F128	YES, 2.0-3.8V
EFM32WG995F256	YES, 2.0-3.8V
EFM32WG995F64	YES, 2.0-3.8V
EFM32ZG108F16	YES, 2.0-3.8V
EFM32ZG108F32	YES, 2.0-3.8V
EFM32ZG108F4	YES, 2.0-3.8V

EFM32ZG108F8	YES, 2.0-3.8V
EFM32ZG110F16	YES, 2.0-3.8V
EFM32ZG110F32	YES, 2.0-3.8V
EFM32ZG110F4	YES, 2.0-3.8V
EFM32ZG110F8	YES, 2.0-3.8V
EFM32ZG210F16	YES, 2.0-3.8V
EFM32ZG210F32	YES, 2.0-3.8V
EFM32ZG210F4	YES, 2.0-3.8V
EFM32ZG210F8	YES, 2.0-3.8V
EFM32ZG222F16	YES, 2.0-3.8V
EFM32ZG222F32	YES, 2.0-3.8V
EFM32ZG222F4	YES, 2.0-3.8V
EFM32ZG222F8	YES, 2.0-3.8V
EFR32BG12P132F1024	YES, 1.8-3.8V
EFR32BG12P232F1024	YES, 1.8-3.8V
EFR32BG12P232F512	YES, 1.8-3.8V
EFR32BG12P332F1024	YES, 1.8-3.8V
EFR32BG12P432F1024	YES, 1.8-3.8V
EFR32BG12P433F1024	YES, 1.8-3.8V
EFR32BG13P532F512	YES, 1.8-3.8V
EFR32BG13P632F512	YES, 1.8-3.8V
EFR32BG13P732F512	YES, 1.8-3.8V
EFR32BG13P733F512	YES, 1.8-3.8V
EFR32BG14P532F256	YES, 1.9-3.8V
EFR32BG14P632F256	YES, 1.9-3.8V
EFR32BG14P732F256	YES, 1.9-3.8V
EFR32BG14P733F256	YES, 1.9-3.8V
EFR32BG1B132F128	YES, 1.9-3.8V
EFR32BG1B132F256	YES, 1.9-3.8V
EFR32BG1B232F128	YES, 1.9-3.8V
EFR32BG1B232F256	YES, 1.9-3.8V
EFR32BG1P232F256	YES, 1.9-3.8V
EFR32BG1P233F256	YES, 1.9-3.8V
EFR32BG1P332F256	YES, 1.9-3.8V
EFR32BG1P333F256	YES, 1.9-3.8V
EFR32BG1V132F128	YES, 1.9-3.8V
EFR32BG1V132F256	YES, 1.9-3.8V
EFR32FG12P231F1024	YES, 1.8-3.8V
EFR32FG12P231F512	YES, 1.8-3.8V
EFR32FG12P232F1024	YES, 1.8-3.8V
EFR32FG12P431F1024	YES, 1.8-3.8V
EFR32FG12P431F512	YES, 1.8-3.8V
EFR32FG12P432F1024	YES, 1.8-3.8V
EFR32FG12P433F1024	YES, 1.8-3.8V
EFR32FG13P231F512	YES, 1.8-3.8V
EFR32FG13P232F512	YES, 1.8-3.8V
EFR32FG13P233F512	YES, 1.8-3.8V
EFR32FG14P231F128	YES, 1.9-3.8V
EFR32FG14P231F256	YES, 1.9-3.8V
EFR32FG14P232F128	YES, 1.9-3.8V
EFR32FG14P232F256	YES, 1.9-3.8V
EFR32FG14P233F128	YES, 1.9-3.8V
EFR32FG14P233F256	YES, 1.9-3.8V
EFR32FG1P131F128	YES, 1.9-3.8V
EFR32FG1P131F256	YES, 1.9-3.8V
EFR32FG1P131F64	YES, 1.9-3.8V
EFR32FG1P132F128	YES, 1.9-3.8V
EFR32FG1P132F256	YES, 1.9-3.8V
EFR32FG1P132F64	YES, 1.9-3.8V

EFR32FG1P133F128	YES, 1.9-3.8V
EFR32FG1P133F256	YES, 1.9-3.8V
EFR32FG1P133F64	YES, 1.9-3.8V
EFR32FG1V032F128	YES, 1.9-3.8V
EFR32FG1V032F256	YES, 1.9-3.8V
EFR32FG1V131F128	YES, 1.9-3.8V
EFR32FG1V131F256	YES, 1.9-3.8V
EFR32FG1V131F32	YES, 1.9-3.8V
EFR32FG1V131F64	YES, 1.9-3.8V
EFR32FG1V132F128	YES, 1.9-3.8V
EFR32FG1V132F256	YES, 1.9-3.8V
EFR32FG1V132F32	YES, 1.9-3.8V
EFR32FG1V132F64	YES, 1.9-3.8V
EFR32MG12P132F1024	YES, 1.8-3.8V
EFR32MG12P132F512	YES, 1.8-3.8V
EFR32MG12P231F1024	YES, 1.8-3.8V
EFR32MG12P232F1024	YES, 1.8-3.8V
EFR32MG12P232F512	YES, 1.8-3.8V
EFR32MG12P332F1024	YES, 1.8-3.8V
EFR32MG12P431F1024	YES, 1.8-3.8V
EFR32MG12P432F1024	YES, 1.8-3.8V
EFR32MG12P433F1024	YES, 1.8-3.8V
EFR32MG13P632F512	YES, 1.8-3.8V
EFR32MG13P732F512	YES, 1.8-3.8V
EFR32MG13P733F512	YES, 1.8-3.8V
EFR32MG14P632F256	YES, 1.9-3.8V
EFR32MG14P732F256	YES, 1.9-3.8V
EFR32MG14P733F256	YES, 1.9-3.8V
EFR32MG1B132F256	YES, 1.9-3.8V
EFR32MG1B232F256	YES, 1.9-3.8V
EFR32MG1P132F256	YES, 1.9-3.8V
EFR32MG1P133F256	YES, 1.9-3.8V
EFR32MG1P232F256	YES, 1.9-3.8V
EFR32MG1P233F256	YES, 1.9-3.8V
EFR32MG1V132F256	YES, 1.9-3.8V
LPC1101LV	YES, 1.8-1.9V
LPC1102	YES, 1.8-3.6V
LPC1102LV	YES, 1.8-1.9V
LPC1104	YES, 1.8-3.6V
LPC1110	YES, 1.8-3.6V
LPC1111/002	YES, 1.8-3.6V
LPC1111/101	YES, 1.8-3.6V
LPC1111/102	YES, 1.8-3.6V
LPC1111/103	YES, 1.8-3.6V
LPC1111/201	YES, 1.8-3.6V
LPC1111/202	YES, 1.8-3.6V
LPC1111/203	YES, 1.8-3.6V
LPC1112/101	YES, 1.8-3.6V
LPC1112/102	YES, 1.8-3.6V
LPC1112/103	YES, 1.8-3.6V
LPC1112/201	YES, 1.8-3.6V
LPC1112/202	YES, 1.8-3.6V
LPC1112/203	YES, 1.8-3.6V
LPC1112LV/003	YES, 1.8-1.9V
LPC1112LV/103	YES, 1.8-1.9V
LPC1113/201	YES, 1.8-3.6V
LPC1113/202	YES, 1.8-3.6V
LPC1113/203	YES, 1.8-3.6V
LPC1113/301	YES, 1.8-3.6V

LPC1113/302	YES, 1.8-3.6V
LPC1113/303	YES, 1.8-3.6V
LPC1114/102	YES, 1.8-3.6V
LPC1114/201	YES, 1.8-3.6V
LPC1114/202	YES, 1.8-3.6V
LPC1114/203	YES, 1.8-3.6V
LPC1114/301	YES, 1.8-3.6V
LPC1114/302	YES, 1.8-3.6V
LPC1114/303	YES, 1.8-3.6V
LPC1114/323	YES, 1.8-3.6V
LPC1114/333	YES, 1.8-3.6V
LPC1114LV/103	YES, 1.8-1.9V
LPC1114LV/303	YES, 1.8-1.9V
LPC1115	YES, 1.8-3.6V
LPC1124	YES, 1.8-3.6V
LPC1125	YES, 1.8-3.6V
LPC11A02	YES, 2.6-3.6V
LPC11A04	YES, 2.6-3.6V
LPC11A11	YES, 2.6-3.6V
LPC11A12	YES, 2.6-3.6V
LPC11A13	YES, 2.6-3.6V
LPC11A14	YES, 2.6-3.6V
LPC11C12	YES, 1.8-3.6V
LPC11C14	YES, 1.8-3.6V
LPC11C22	YES, 1.8-3.6V
LPC11C24	YES, 1.8-3.6V
LPC11D14	YES, 1.8-3.6V
LPC11E11	YES, 1.8-3.6V
LPC11E12	YES, 1.8-3.6V
LPC11E13	YES, 1.8-3.6V
LPC11E14	YES, 1.8-3.6V
LPC11E35	YES, 1.8-3.6V
LPC11E36	YES, 1.8-3.6V
LPC11E37	YES, 1.8-3.6V
LPC11E66	YES, 2.4-3.6V
LPC11E67	YES, 2.4-3.6V
LPC11E68	YES, 2.4-3.6V
LPC11U12	YES, 1.8-3.6V
LPC11U13	YES, 1.8-3.6V
LPC11U14	YES, 1.8-3.6V
LPC11U22	YES, 1.8-3.6V
LPC11U23	YES, 1.8-3.6V
LPC11U24/301	YES, 1.8-3.6V
LPC11U24/401	YES, 1.8-3.6V
LPC11U34/311	YES, 1.8-3.6V
LPC11U34/421	YES, 1.8-3.6V
LPC11U35	YES, 1.8-3.6V
LPC11U36	YES, 1.8-3.6V
LPC11U37	YES, 1.8-3.6V
LPC11U66	YES, 2.4-3.6V
LPC11U67	YES, 2.4-3.6V
LPC11U68	YES, 2.4-3.6V
LPC1224/101	YES, 3.0-3.6V
LPC1224/121	YES, 2.4-3.6V
LPC1225/301	YES, 3.0-3.6V
LPC1225/321	YES, 3.0-3.6V
LPC1226	YES, 3.0-3.6V
LPC1227	YES, 3.0-3.6V
LPC1315	YES, 2.0-3.6V

LPC1316	YES, 2.0-3.6V
LPC1317	YES, 2.0-3.6V
LPC1345	YES, 2.0-3.6V
LPC1346	YES, 2.0-3.6V
LPC1347	YES, 2.0-3.6V
LPC1517	YES, 2.4-3.6V
LPC1518	YES, 2.4-3.6V
LPC1519	YES, 2.4-3.6V
LPC1547	YES, 2.4-3.6V
LPC1548	YES, 2.4-3.6V
LPC1549	YES, 2.4-3.6V
LPC1751	YES, 2.4-3.6V
LPC1752	YES, 2.4-3.6V
LPC1754	YES, 2.4-3.6V
LPC1756	YES, 2.4-3.6V
LPC1758	YES, 2.4-3.6V
LPC1759	YES, 2.4-3.6V
LPC1763	YES, 2.4-3.6V
LPC1764	YES, 2.4-3.6V
LPC1765	YES, 2.4-3.6V
LPC1766	YES, 2.4-3.6V
LPC1767	YES, 2.4-3.6V
LPC1768	YES, 2.4-3.6V
LPC1769	YES, 2.4-3.6V
LPC2101	YES, 2.6-3.6V
LPC2102	YES, 2.6-3.6V
LPC2103	YES, 2.6-3.6V
LPC2104	YES, 3.0-3.6V
LPC2105	YES, 3.0-3.6V
LPC2106	YES, 3.0-3.6V
LPC2109	YES, 3.0-3.6V
LPC2114	YES, 3.0-3.6V
LPC2119	YES, 3.0-3.6V
LPC2124	YES, 3.0-3.6V
LPC2129	YES, 3.0-3.6V
LPC2131	YES, 3.0-3.6V
LPC2132	YES, 3.0-3.6V
LPC2134	YES, 3.0-3.6V
LPC2136	YES, 3.0-3.6V
LPC2138	YES, 3.0-3.6V
LPC2141	YES, 3.0-3.6V
LPC2142	YES, 3.0-3.6V
LPC2144	YES, 3.0-3.6V
LPC2146	YES, 3.0-3.6V
LPC2148	YES, 3.0-3.6V
LPC2194	YES, 3.0-3.6V
LPC2212	YES, 3.0-3.6V
LPC2214	YES, 3.0-3.6V
LPC2292	YES, 3.0-3.6V
LPC2294	YES, 3.0-3.6V
LPC2361	YES, 3.0-3.6V
LPC2362	YES, 3.0-3.6V
LPC2364	YES, 3.0-3.6V
LPC2365	YES, 3.0-3.6V
LPC2366	YES, 3.0-3.6V
LPC2367	YES, 3.0-3.6V
LPC2368	YES, 3.0-3.6V
LPC2377	YES, 3.0-3.6V
LPC2378	YES, 3.0-3.6V

LPC2387	YES, 3.0-3.6V
LPC2388	YES, 3.0-3.6V
LPC2458	YES, 3.0-3.6V
LPC2468	YES, 3.0-3.6V
LPC2478	YES, 3.0-3.6V
LPC802	YES, 1.8-3.6V
LPC804	YES, 1.8-3.6V
LPC810	YES, 1.8-3.6V
LPC811	YES, 1.8-3.6V
LPC812	YES, 1.8-3.6V
LPC822	YES, 1.8-3.6V
LPC824	YES, 1.8-3.6V
LPC832	YES, 1.8-3.6V
LPC834	YES, 1.8-3.6V
LPC844	YES, 1.8-3.6V
LPC845	YES, 1.8-3.6V
MKE02Z16	YES, 2.7-5.5V
MKE02Z32	YES, 2.7-5.5V
MKE02Z64	YES, 2.7-5.5V
MKE04Z8	YES, 2.7-5.5V
MKL15Z128	YES, 1.8-3.6V
MKL15Z32	YES, 1.8-3.6V
MKL15Z64	YES, 1.8-3.6V
MKL33Z32	YES, 1.8-3.6V
MKL33Z64	YES, 1.8-3.6V
MKV10Z128	YES, 1.8-3.6V
MKV10Z16	YES, 1.8-3.6V
MKV10Z32	YES, 1.8-3.6V
MKV11Z128	YES, 1.8-3.6V
MKV11Z64	YES, 1.8-3.6V
MKV30F128	YES, 1.8-3.6V
MKV30F64	YES, 1.8-3.6V
MKV31F128	YES, 1.8-3.6V
MKV31F256	YES, 1.8-3.6V
MKV31F512	YES, 1.8-3.6V
MKV42F128	YES, 1.8-3.6V
MKV42F256	YES, 1.8-3.6V
MKV42F64	YES, 1.8-3.6V
MKV44F128	YES, 1.8-3.6V
MKV44F256	YES, 1.8-3.6V
MKV44F64	YES, 1.8-3.6V
MKV46F128	YES, 1.8-3.6V
MKV46F256	YES, 1.8-3.6V
MKW21Z256	YES, 1.8-3.6V
MKW21Z512	YES, 1.8-3.6V
MKW31Z256	YES, 1.8-3.6V
MKW31Z512	YES, 1.8-3.6V
MKW41Z256	YES, 1.8-3.6V
MKW41Z512	YES, 1.8-3.6V
nRF52832-CIAA	YES, 1.7-3.6V
nRF52832-QFAA	YES, 1.7-3.6V
nRF52832-QFAB	YES, 1.7-3.6V
nRF52840	YES, 1.7-3.6V
STM32F030C6	YES, 2.4-3.6V
STM32F030C8	YES, 2.4-3.6V
STM32F030CC	YES, 2.4-3.6V
STM32F030F4	YES, 2.4-3.6V
STM32F030K6	YES, 2.4-3.6V
STM32F030R8	YES, 2.4-3.6V



STM32F030RC	YES, 2.4-3.6V
STM32F031C4	YES, 2.0-3.6V
STM32F031C6	YES, 2.0-3.6V
STM32F031E6	YES, 2.0-3.6V
STM32F031F4	YES, 2.0-3.6V
STM32F031F6	YES, 2.0-3.6V
STM32F031G4	YES, 2.0-3.6V
STM32F031G6	YES, 2.0-3.6V
STM32F031K4	YES, 2.0-3.6V
STM32F031K6	YES, 2.0-3.6V
STM32F038C6	YES, 1.8-1.9V
STM32F038E6	YES, 1.8-1.9V
STM32F038F6	YES, 1.8-1.9V
STM32F038G6	YES, 1.8-1.9V
STM32F038K6	YES, 1.8-1.9V
STM32F042C4	YES, 2.0-3.6V
STM32F042C6	YES, 2.0-3.6V
STM32F042F4	YES, 2.0-3.6V
STM32F042F6	YES, 2.0-3.6V
STM32F042G4	YES, 2.0-3.6V
STM32F042G6	YES, 2.0-3.6V
STM32F042K4	YES, 2.0-3.6V
STM32F042K6	YES, 2.0-3.6V
STM32F042T6	YES, 2.0-3.6V
STM32F048C6	YES, 1.8-3.6V
STM32F048G6	YES, 1.8-3.6V
STM32F048T6	YES, 1.8-3.6V
STM32F051C4	YES, 2.0-3.6V
STM32F051C6	YES, 2.0-3.6V
STM32F051C8	YES, 2.0-3.6V
STM32F051K4	YES, 2.0-3.6V
STM32F051K6	YES, 2.0-3.6V
STM32F051K8	YES, 2.0-3.6V
STM32F051R4	YES, 2.0-3.6V
STM32F051R6	YES, 2.0-3.6V
STM32F051R8	YES, 2.0-3.6V
STM32F051T8	YES, 2.0-3.6V
STM32F058C8	YES, 1.8-1.9V
STM32F058R8	YES, 1.8-1.9V
STM32F058T8	YES, 1.8-1.9V
STM32F070C6	YES, 2.4-3.6V
STM32F070CB	YES, 2.4-3.6V
STM32F070F6	YES, 2.4-3.6V
STM32F070RB	YES, 2.4-3.6V
STM32F071CB	YES, 2.0-3.6V
STM32F071RB	YES, 2.0-3.6V
STM32F071V8	YES, 2.0-3.6V
STM32F071VB	YES, 2.0-3.6V
STM32F072C8	YES, 2.0-3.6V
STM32F072CB	YES, 2.0-3.6V
STM32F072R8	YES, 2.0-3.6V
STM32F072RB	YES, 2.0-3.6V
STM32F072V8	YES, 2.0-3.6V
STM32F072VB	YES, 2.0-3.6V
STM32F078CB	YES, 1.8-3.6V
STM32F078RB	YES, 1.8-3.6V
STM32F078VB	YES, 1.8-3.6V
STM32F091CB	YES, 2.0-3.6V
STM32F091CC	YES, 2.0-3.6V

STM32F091RB	YES, 2.0-3.6V
STM32F091RC	YES, 2.0-3.6V
STM32F091VB	YES, 2.0-3.6V
STM32F091VC	YES, 2.0-3.6V
STM32F098CC	YES, 1.8-3.6V
STM32F098RC	YES, 1.8-3.6V
STM32F098VC	YES, 1.8-3.6V
STM32F100C4	YES, 2.0-3.6V
STM32F100C6	YES, 2.0-3.6V
STM32F100C8	YES, 2.0-3.6V
STM32F100CB	YES, 2.0-3.6V
STM32F100R4	YES, 2.0-3.6V
STM32F100R6	YES, 2.0-3.6V
STM32F100R8	YES, 2.0-3.6V
STM32F100RB	YES, 2.0-3.6V
STM32F100RC	YES, 2.0-3.6V
STM32F100RD	YES, 2.0-3.6V
STM32F100RE	YES, 2.0-3.6V
STM32F100V8	YES, 2.0-3.6V
STM32F100VB	YES, 2.0-3.6V
STM32F100VC	YES, 2.0-3.6V
STM32F100VD	YES, 2.0-3.6V
STM32F100VE	YES, 2.0-3.6V
STM32F100ZC	YES, 2.0-3.6V
STM32F100ZD	YES, 2.0-3.6V
STM32F100ZE	YES, 2.0-3.6V
STM32F101C4	YES, 2.0-3.6V
STM32F101C6	YES, 2.0-3.6V
STM32F101C8	YES, 2.0-3.6V
STM32F101CB	YES, 2.0-3.6V
STM32F101R4	YES, 2.0-3.6V
STM32F101R6	YES, 2.0-3.6V
STM32F101R8	YES, 2.0-3.6V
STM32F101RB	YES, 2.0-3.6V
STM32F101RC	YES, 2.0-3.6V
STM32F101RD	YES, 2.0-3.6V
STM32F101RE	YES, 2.0-3.6V
STM32F101RF	YES, 2.0-3.6V
STM32F101RG	YES, 2.0-3.6V
STM32F101T4	YES, 2.0-3.6V
STM32F101T6	YES, 2.0-3.6V
STM32F101T8	YES, 2.0-3.6V
STM32F101TB	YES, 2.0-3.6V
STM32F101V8	YES, 2.0-3.6V
STM32F101VB	YES, 2.0-3.6V
STM32F101VC	YES, 2.0-3.6V
STM32F101VD	YES, 2.0-3.6V
STM32F101VE	YES, 2.0-3.6V
STM32F101VF	YES, 2.0-3.6V
STM32F101VG	YES, 2.0-3.6V
STM32F101ZC	YES, 2.0-3.6V
STM32F101ZD	YES, 2.0-3.6V
STM32F101ZE	YES, 2.0-3.6V
STM32F101ZF	YES, 2.0-3.6V
STM32F101ZG	YES, 2.0-3.6V
STM32F102C4	YES, 2.0-3.6V
STM32F102C6	YES, 2.0-3.6V
STM32F102C8	YES, 2.0-3.6V
STM32F102CB	YES, 2.0-3.6V

STM32F102R4	YES, 2.0-3.6V
STM32F102R6	YES, 2.0-3.6V
STM32F102R8	YES, 2.0-3.6V
STM32F102RB	YES, 2.0-3.6V
STM32F103C4	YES, 2.0-3.6V
STM32F103C6	YES, 2.0-3.6V
STM32F103C8	YES, 2.0-3.6V
STM32F103CB	YES, 2.0-3.6V
STM32F103R4	YES, 2.0-3.6V
STM32F103R6	YES, 2.0-3.6V
STM32F103R8	YES, 2.0-3.6V
STM32F103RB	YES, 2.0-3.6V
STM32F103RC	YES, 2.0-3.6V
STM32F103RD	YES, 2.0-3.6V
STM32F103RE	YES, 2.0-3.6V
STM32F103RF	YES, 2.0-3.6V
STM32F103RG	YES, 2.0-3.6V
STM32F103T4	YES, 2.0-3.6V
STM32F103T6	YES, 2.0-3.6V
STM32F103T8	YES, 2.0-3.6V
STM32F103TB	YES, 2.0-3.6V
STM32F103V8	YES, 2.0-3.6V
STM32F103VB	YES, 2.0-3.6V
STM32F103VC	YES, 2.0-3.6V
STM32F103VD	YES, 2.0-3.6V
STM32F103VE	YES, 2.0-3.6V
STM32F103VF	YES, 2.0-3.6V
STM32F103VG	YES, 2.0-3.6V
STM32F103ZC	YES, 2.0-3.6V
STM32F103ZD	YES, 2.0-3.6V
STM32F103ZE	YES, 2.0-3.6V
STM32F103ZF	YES, 2.0-3.6V
STM32F103ZG	YES, 2.0-3.6V
STM32F105R8	YES, 2.0-3.6V
STM32F105RB	YES, 2.0-3.6V
STM32F105RC	YES, 2.0-3.6V
STM32F105V8	YES, 2.0-3.6V
STM32F105VB	YES, 2.0-3.6V
STM32F105VC	YES, 2.0-3.6V
STM32F107RB	YES, 2.0-3.6V
STM32F107RC	YES, 2.0-3.6V
STM32F107VB	YES, 2.0-3.6V
STM32F107VC	YES, 2.0-3.6V
STM32F205RB	YES, 1.8-3.6V
STM32F205RC	YES, 1.8-3.6V
STM32F205RE	YES, 1.8-3.6V
STM32F205RF	YES, 1.8-3.6V
STM32F205RG	YES, 1.8-3.6V
STM32F205VB	YES, 1.8-3.6V
STM32F205VC	YES, 1.8-3.6V
STM32F205VE	YES, 1.8-3.6V
STM32F205VF	YES, 1.8-3.6V
STM32F205VG	YES, 1.8-3.6V
STM32F205ZC	YES, 1.8-3.6V
STM32F205ZE	YES, 1.8-3.6V
STM32F205ZF	YES, 1.8-3.6V
STM32F205ZG	YES, 1.8-3.6V
STM32F207IC	YES, 1.8-3.6V
STM32F207IE	YES, 1.8-3.6V

STM32F207IF	YES, 1.8-3.6V
STM32F207IG	YES, 1.8-3.6V
STM32F207VC	YES, 1.8-3.6V
STM32F207VE	YES, 1.8-3.6V
STM32F207VF	YES, 1.8-3.6V
STM32F207VG	YES, 1.8-3.6V
STM32F207ZC	YES, 1.8-3.6V
STM32F207ZE	YES, 1.8-3.6V
STM32F207ZF	YES, 1.8-3.6V
STM32F207ZG	YES, 1.8-3.6V
STM32F215RE	YES, 1.8-3.6V
STM32F215RG	YES, 1.8-3.6V
STM32F215VE	YES, 1.8-3.6V
STM32F215VG	YES, 1.8-3.6V
STM32F215ZE	YES, 1.8-3.6V
STM32F215ZG	YES, 1.8-3.6V
STM32F217IE	YES, 1.8-3.6V
STM32F217IG	YES, 1.8-3.6V
STM32F217VE	YES, 1.8-3.6V
STM32F217VG	YES, 1.8-3.6V
STM32F217ZE	YES, 1.8-3.6V
STM32F217ZG	YES, 1.8-3.6V
STM32F301C6	YES, 2.0-3.6V
STM32F301C8	YES, 2.0-3.6V
STM32F301K6	YES, 2.0-3.6V
STM32F301K8	YES, 2.0-3.6V
STM32F301R6	YES, 2.0-3.6V
STM32F301R8	YES, 2.0-3.6V
STM32F302C6	YES, 2.0-3.6V
STM32F302C8	YES, 2.0-3.6V
STM32F302CB	YES, 2.0-3.6V
STM32F302CC	YES, 2.0-3.6V
STM32F302K6	YES, 2.0-3.6V
STM32F302K8	YES, 2.0-3.6V
STM32F302R6	YES, 2.0-3.6V
STM32F302R8	YES, 2.0-3.6V
STM32F302RB	YES, 2.0-3.6V
STM32F302RC	YES, 2.0-3.6V
STM32F302RD	YES, 2.0-3.6V
STM32F302RE	YES, 2.0-3.6V
STM32F302VB	YES, 2.0-3.6V
STM32F302VC	YES, 2.0-3.6V
STM32F302VD	YES, 2.0-3.6V
STM32F302VE	YES, 2.0-3.6V
STM32F302ZD	YES, 2.0-3.6V
STM32F302ZE	YES, 2.0-3.6V
STM32F303C6	YES, 2.0-3.6V
STM32F303C8	YES, 2.0-3.6V
STM32F303CB	YES, 2.0-3.6V
STM32F303CC	YES, 2.0-3.6V
STM32F303K6	YES, 2.0-3.6V
STM32F303K8	YES, 2.0-3.6V
STM32F303R6	YES, 2.0-3.6V
STM32F303R8	YES, 2.0-3.6V
STM32F303RB	YES, 2.0-3.6V
STM32F303RC	YES, 2.0-3.6V
STM32F303RD	YES, 2.0-3.6V
STM32F303RE	YES, 2.0-3.6V
STM32F303VB	YES, 2.0-3.6V

STM32F303VC	YES, 2.0-3.6V
STM32F303VD	YES, 2.0-3.6V
STM32F303VE	YES, 2.0-3.6V
STM32F303ZD	YES, 2.0-3.6V
STM32F303ZE	YES, 2.0-3.6V
STM32F318C8	YES, 1.8-1.9V
STM32F318K8	YES, 1.8-1.9V
STM32F328C8	YES, 1.8-1.9V
STM32F334C4	YES, 2.0-3.6V
STM32F334C6	YES, 2.0-3.6V
STM32F334C8	YES, 2.0-3.6V
STM32F334K4	YES, 2.0-3.6V
STM32F334K6	YES, 2.0-3.6V
STM32F334K8	YES, 2.0-3.6V
STM32F334R6	YES, 2.0-3.6V
STM32F334R8	YES, 2.0-3.6V
STM32F358CC	YES, 1.8-1.9V
STM32F358RC	YES, 1.8-1.9V
STM32F358VC	YES, 1.8-1.9V
STM32F373C8	YES, 2.0-3.6V
STM32F373CB	YES, 2.0-3.6V
STM32F373CC	YES, 2.0-3.6V
STM32F373R8	YES, 2.0-3.6V
STM32F373RB	YES, 2.0-3.6V
STM32F373RC	YES, 2.0-3.6V
STM32F373V8	YES, 2.0-3.6V
STM32F373VB	YES, 2.0-3.6V
STM32F373VC	YES, 2.0-3.6V
STM32F378CC	YES, 1.8-1.9V
STM32F378RC	YES, 1.8-1.9V
STM32F378VC	YES, 1.8-1.9V
STM32F398VE	YES, 1.8-1.9V
STM32F401CB	YES, 1.8-3.6V
STM32F401CC	YES, 1.8-3.6V
STM32F401CD	YES, 1.8-3.6V
STM32F401CE	YES, 1.8-3.6V
STM32F401RB	YES, 1.8-3.6V
STM32F401RC	YES, 1.8-3.6V
STM32F401RD	YES, 1.8-3.6V
STM32F401RE	YES, 1.8-3.6V
STM32F401VB	YES, 1.8-3.6V
STM32F401VC	YES, 1.8-3.6V
STM32F401VD	YES, 1.8-3.6V
STM32F401VE	YES, 1.8-3.6V
STM32F405OE	YES, 1.8-3.6V
STM32F405OG	YES, 1.8-3.6V
STM32F405RG	YES, 1.8-3.6V
STM32F405VG	YES, 1.8-3.6V
STM32F405ZG	YES, 1.8-3.6V
STM32F407IE	YES, 1.8-3.6V
STM32F407IG	YES, 1.8-3.6V
STM32F407VE	YES, 1.8-3.6V
STM32F407VG	YES, 1.8-3.6V
STM32F407ZE	YES, 1.8-3.6V
STM32F407ZG	YES, 1.8-3.6V
STM32F410C8	YES, 1.8-3.6V
STM32F410CB	YES, 1.8-3.6V
STM32F410R8	YES, 1.8-3.6V
STM32F410RB	YES, 1.8-3.6V

STM32F410T8	YES, 1.8-3.6V
STM32F410TB	YES, 1.8-3.6V
STM32F411CC	YES, 1.8-3.6V
STM32F411CE	YES, 1.8-3.6V
STM32F411RC	YES, 1.8-3.6V
STM32F411RE	YES, 1.8-3.6V
STM32F411VC	YES, 1.8-3.6V
STM32F411VE	YES, 1.8-3.6V
STM32F412CE	YES, 1.8-3.6V
STM32F412CG	YES, 1.8-3.6V
STM32F412RE	YES, 1.8-3.6V
STM32F412RG	YES, 1.8-3.6V
STM32F412VE	YES, 1.8-3.6V
STM32F412VG	YES, 1.8-3.6V
STM32F412ZE	YES, 1.8-3.6V
STM32F412ZG	YES, 1.8-3.6V
STM32F413CG	YES, 1.8-3.6V
STM32F413CH	YES, 1.8-3.6V
STM32F413MG	YES, 1.8-3.6V
STM32F413MH	YES, 1.8-3.6V
STM32F413RG	YES, 1.8-3.6V
STM32F413RH	YES, 1.8-3.6V
STM32F413VG	YES, 1.8-3.6V
STM32F413VH	YES, 1.8-3.6V
STM32F413ZG	YES, 1.8-3.6V
STM32F413ZH	YES, 1.8-3.6V
STM32F415OG	YES, 1.8-3.6V
STM32F415RG	YES, 1.8-3.6V
STM32F415VG	YES, 1.8-3.6V
STM32F415ZG	YES, 1.8-3.6V
STM32F417IE	YES, 1.8-3.6V
STM32F417IG	YES, 1.8-3.6V
STM32F417VE	YES, 1.8-3.6V
STM32F417VG	YES, 1.8-3.6V
STM32F417ZE	YES, 1.8-3.6V
STM32F417ZG	YES, 1.8-3.6V
STM32F423CH	YES, 1.8-3.6V
STM32F423MH	YES, 1.8-3.6V
STM32F423RH	YES, 1.8-3.6V
STM32F423VH	YES, 1.8-3.6V
STM32F423ZH	YES, 1.8-3.6V
STM32F427IG	YES, 1.8-3.6V
STM32F427II	YES, 1.8-3.6V
STM32F427VG	YES, 1.8-3.6V
STM32F427VI	YES, 1.8-3.6V
STM32F427ZG	YES, 1.8-3.6V
STM32F427ZI	YES, 1.8-3.6V
STM32F429BI	YES, 1.8-3.6V
STM32F429IG	YES, 1.8-3.6V
STM32F429II	YES, 1.8-3.6V
STM32F429VG	YES, 1.8-3.6V
STM32F429VI	YES, 1.8-3.6V
STM32F429ZE	YES, 1.8-3.6V
STM32F429ZG	YES, 1.8-3.6V
STM32F429ZI	YES, 1.8-3.6V
STM32F437IG	YES, 1.8-3.6V
STM32F437II	YES, 1.8-3.6V
STM32F437VG	YES, 1.8-3.6V
STM32F437VI	YES, 1.8-3.6V

STM32F437ZG	YES, 1.8-3.6V
STM32F437ZI	YES, 1.8-3.6V
STM32F439BI	YES, 1.8-3.6V
STM32F439IG	YES, 1.8-3.6V
STM32F439II	YES, 1.8-3.6V
STM32F439VG	YES, 1.8-3.6V
STM32F439VI	YES, 1.8-3.6V
STM32F439ZG	YES, 1.8-3.6V
STM32F439ZI	YES, 1.8-3.6V
STM32F722IC	YES, 1.8-3.6V
STM32F722IE	YES, 1.8-3.6V
STM32F722RC	YES, 1.8-3.6V
STM32F722RE	YES, 1.8-3.6V
STM32F722VC	YES, 1.8-3.6V
STM32F722VE	YES, 1.8-3.6V
STM32F722ZC	YES, 1.8-3.6V
STM32F722ZE	YES, 1.8-3.6V
STM32F723IC	YES, 1.8-3.6V
STM32F723IE	YES, 1.8-3.6V
STM32F723VE	YES, 1.8-3.6V
STM32F723ZC	YES, 1.8-3.6V
STM32F723ZE	YES, 1.8-3.6V
STM32F732IE	YES, 1.8-3.6V
STM32F732RE	YES, 1.8-3.6V
STM32F732VE	YES, 1.8-3.6V
STM32F732ZE	YES, 1.8-3.6V
STM32F733IE	YES, 1.8-3.6V
STM32F733VE	YES, 1.8-3.6V
STM32F733ZE	YES, 1.8-3.6V
STM32F745IE	YES, 1.8-3.6V
STM32F745IG	YES, 1.8-3.6V
STM32F745VE	YES, 1.8-3.6V
STM32F745VG	YES, 1.8-3.6V
STM32F745ZE	YES, 1.8-3.6V
STM32F745ZG	YES, 1.8-3.6V
STM32F746BE	YES, 1.8-3.6V
STM32F746BG	YES, 1.8-3.6V
STM32F746IE	YES, 1.8-3.6V
STM32F746IG	YES, 1.8-3.6V
STM32F746NE	YES, 1.8-3.6V
STM32F746NG	YES, 1.8-3.6V
STM32F746VE	YES, 1.8-3.6V
STM32F746VG	YES, 1.8-3.6V
STM32F746ZE	YES, 1.8-3.6V
STM32F746ZG	YES, 1.8-3.6V
STM32F756BG	YES, 1.8-3.6V
STM32F756IG	YES, 1.8-3.6V
STM32F756NG	YES, 1.8-3.6V
STM32F756VG	YES, 1.8-3.6V
STM32F756ZG	YES, 1.8-3.6V
STM32F765BG	YES, 1.8-3.6V
STM32F765BI	YES, 1.8-3.6V
STM32F765IG	YES, 1.8-3.6V
STM32F765II	YES, 1.8-3.6V
STM32F765NG	YES, 1.8-3.6V
STM32F765NI	YES, 1.8-3.6V
STM32F765VG	YES, 1.8-3.6V
STM32F765VI	YES, 1.8-3.6V
STM32F765ZG	YES, 1.8-3.6V

STM32F765ZI	YES, 1.8-3.6V
STM32F767BG	YES, 1.8-3.6V
STM32F767BI	YES, 1.8-3.6V
STM32F767IG	YES, 1.8-3.6V
STM32F767II	YES, 1.8-3.6V
STM32F767NG	YES, 1.8-3.6V
STM32F767NI	YES, 1.8-3.6V
STM32F767VG	YES, 1.8-3.6V
STM32F767VI	YES, 1.8-3.6V
STM32F767ZG	YES, 1.8-3.6V
STM32F767ZI	YES, 1.8-3.6V
STM32F769AI	YES, 1.8-3.6V
STM32F769BG	YES, 1.8-3.6V
STM32F769BI	YES, 1.8-3.6V
STM32F769IG	YES, 1.8-3.6V
STM32F769II	YES, 1.8-3.6V
STM32F769NG	YES, 1.8-3.6V
STM32F769NI	YES, 1.8-3.6V
STM32F777BI	YES, 1.8-3.6V
STM32F777II	YES, 1.8-3.6V
STM32F777NI	YES, 1.8-3.6V
STM32F777VI	YES, 1.8-3.6V
STM32F777ZI	YES, 1.8-3.6V
STM32F779AI	YES, 1.8-3.6V
STM32F779BI	YES, 1.8-3.6V
STM32F779II	YES, 1.8-3.6V
STM32F779NI	YES, 1.8-3.6V
STM32G030C6	YES, 2.0-3.6V
STM32G030C8	YES, 2.0-3.6V
STM32G030F6	YES, 2.0-3.6V
STM32G030J6	YES, 2.0-3.6V
STM32G030K6	YES, 2.0-3.6V
STM32G030K8	YES, 2.0-3.6V
STM32G031C6	YES, 1.7-3.6V
STM32G031C8	YES, 1.7-3.6V
STM32G031F4	YES, 1.7-3.6V
STM32G031F6	YES, 1.7-3.6V
STM32G031F8	YES, 1.7-3.6V
STM32G031G4	YES, 1.7-3.6V
STM32G031G6	YES, 1.7-3.6V
STM32G031G8	YES, 1.7-3.6V
STM32G031J6	YES, 1.7-3.6V
STM32G031K6	YES, 1.7-3.6V
STM32G031K8	YES, 1.7-3.6V
STM32G031Y8	YES, 1.7-3.6V
STM32G041C8	YES, 1.7-3.6V
STM32G041J6	YES, 1.7-3.6V
STM32G070CB	YES, 2.0-3.6V
STM32G070KB	YES, 2.0-3.6V
STM32G070RB	YES, 2.0-3.6V
STM32G071C8	YES, 1.7-3.6V
STM32G071CB	YES, 1.7-3.6V
STM32G071EB	YES, 1.7-3.6V
STM32G071G8	YES, 1.7-3.6V
STM32G071GB	YES, 1.7-3.6V
STM32G071K8	YES, 1.7-3.6V
STM32G071KB	YES, 1.7-3.6V
STM32G071R8	YES, 1.7-3.6V
STM32G071RB	YES, 1.7-3.6V



STM32G081CB	YES, 1.7-3.6V
STM32G081EB	YES, 1.7-3.6V
STM32G081GB	YES, 1.7-3.6V
STM32G081KB	YES, 1.7-3.6V
STM32G081RB	YES, 1.7-3.6V
STM32G431C6	YES, 1.7-3.6V
STM32G431C8	YES, 1.7-3.6V
STM32G431CB	YES, 1.7-3.6V
STM32G431K6	YES, 1.7-3.6V
STM32G431K8	YES, 1.7-3.6V
STM32G431KB	YES, 1.7-3.6V
STM32G431M6	YES, 1.7-3.6V
STM32G431M8	YES, 1.7-3.6V
STM32G431MB	YES, 1.7-3.6V
STM32G431R6	YES, 1.7-3.6V
STM32G431R8	YES, 1.7-3.6V
STM32G431RB	YES, 1.7-3.6V
STM32G431V6	YES, 1.7-3.6V
STM32G431V8	YES, 1.7-3.6V
STM32G431VB	YES, 1.7-3.6V
STM32G473CE	YES, 1.7-3.6V
STM32G473QE	YES, 1.7-3.6V
STM32G473RE	YES, 1.7-3.6V
STM32G473VE	YES, 1.7-3.6V
STM32G474CE	YES, 1.7-3.6V
STM32G474ME	YES, 1.7-3.6V
STM32G474QE	YES, 1.7-3.6V
STM32G474RE	YES, 1.7-3.6V
STM32G474VE	YES, 1.7-3.6V
STM32L010C6	YES, 1.8-3.6V
STM32L010F4	YES, 1.8-3.6V
STM32L010K4	YES, 1.8-3.6V
STM32L010K8	YES, 1.8-3.6V
STM32L010R8	YES, 1.8-3.6V
STM32L010RB	YES, 1.8-3.6V
STM32L011D3	YES, 1.8-3.6V
STM32L011D4	YES, 1.8-3.6V
STM32L011E3	YES, 1.8-3.6V
STM32L011E4	YES, 1.8-3.6V
STM32L011F3	YES, 1.8-3.6V
STM32L011F4	YES, 1.8-3.6V
STM32L011G4	YES, 1.8-3.6V
STM32L011K3	YES, 1.8-3.6V
STM32L011K4	YES, 1.8-3.6V
STM32L021D4	YES, 1.8-3.6V
STM32L021F4	YES, 1.8-3.6V
STM32L021G4	YES, 1.8-3.6V
STM32L021K4	YES, 1.8-3.6V
STM32L031C4	YES, 1.8-3.6V
STM32L031C6	YES, 1.8-3.6V
STM32L031E4	YES, 1.8-3.6V
STM32L031E6	YES, 1.8-3.6V
STM32L031F4	YES, 1.8-3.6V
STM32L031F6	YES, 1.8-3.6V
STM32L031G4	YES, 1.8-3.6V
STM32L031G6	YES, 1.8-3.6V
STM32L031K4	YES, 1.8-3.6V
STM32L031K6	YES, 1.8-3.6V
STM32L041C6	YES, 1.8-3.6V

STM32L041F6	YES, 1.8-3.6V
STM32L041G6	YES, 1.8-3.6V
STM32L041K6	YES, 1.8-3.6V
STM32L051C6	YES, 1.8-3.6V
STM32L051C8	YES, 1.8-3.6V
STM32L051K6	YES, 1.8-3.6V
STM32L051K8	YES, 1.8-3.6V
STM32L051R6	YES, 1.8-3.6V
STM32L051R8	YES, 1.8-3.6V
STM32L051T6	YES, 1.8-3.6V
STM32L051T8	YES, 1.8-3.6V
STM32L052C6	YES, 1.8-3.6V
STM32L052C8	YES, 1.8-3.6V
STM32L052K6	YES, 1.8-3.6V
STM32L052K8	YES, 1.8-3.6V
STM32L052R6	YES, 1.8-3.6V
STM32L052R8	YES, 1.8-3.6V
STM32L052T6	YES, 1.8-3.6V
STM32L052T8	YES, 1.8-3.6V
STM32L053C6	YES, 1.8-3.6V
STM32L053C8	YES, 1.8-3.6V
STM32L053R6	YES, 1.8-3.6V
STM32L053R8	YES, 1.8-3.6V
STM32L062K8	YES, 1.8-3.6V
STM32L063C8	YES, 1.8-3.6V
STM32L063R8	YES, 1.8-3.6V
STM32L071C8	YES, 1.8-3.6V
STM32L071CB	YES, 1.8-3.6V
STM32L071CZ	YES, 1.8-3.6V
STM32L071K8	YES, 1.8-3.6V
STM32L071KB	YES, 1.8-3.6V
STM32L071KZ	YES, 1.8-3.6V
STM32L071RB	YES, 1.8-3.6V
STM32L071RZ	YES, 1.8-3.6V
STM32L071V8	YES, 1.8-3.6V
STM32L071VB	YES, 1.8-3.6V
STM32L071VZ	YES, 1.8-3.6V
STM32L072CB	YES, 1.8-3.6V
STM32L072KB	YES, 1.8-3.6V
STM32L072KZ	YES, 1.8-3.6V
STM32L072RB	YES, 1.8-3.6V
STM32L072RZ	YES, 1.8-3.6V
STM32L072V8	YES, 1.8-3.6V
STM32L072VB	YES, 1.8-3.6V
STM32L072VZ	YES, 1.8-3.6V
STM32L073CB	YES, 1.8-3.6V
STM32L073CZ	YES, 1.8-3.6V
STM32L073RB	YES, 1.8-3.6V
STM32L073RZ	YES, 1.8-3.6V
STM32L073V8	YES, 1.8-3.6V
STM32L073VB	YES, 1.8-3.6V
STM32L073VZ	YES, 1.8-3.6V
STM32L081CZ	YES, 1.8-3.6V
STM32L081KZ	YES, 1.8-3.6V
STM32L082KB	YES, 1.8-3.6V
STM32L082KZ	YES, 1.8-3.6V
STM32L083CB	YES, 1.8-3.6V
STM32L083CZ	YES, 1.8-3.6V
STM32L083RB	YES, 1.8-3.6V

STM32L083RZ	YES, 1.8-3.6V
STM32L083V8	YES, 1.8-3.6V
STM32L083VB	YES, 1.8-3.6V
STM32L083VZ	YES, 1.8-3.6V
STM32L100C6-A	YES, 1.8-3.6V
STM32L100R8-A	YES, 1.8-3.6V
STM32L100RB-A	YES, 1.8-3.6V
STM32L100RC	YES, 1.8-3.6V
STM32L151C6-A	YES, 1.8-3.6V
STM32L151C8-A	YES, 1.8-3.6V
STM32L151CB-A	YES, 1.8-3.6V
STM32L151CC	YES, 1.8-3.6V
STM32L151QC	YES, 1.8-3.6V
STM32L151QD	YES, 1.8-3.6V
STM32L151QE	YES, 1.8-3.6V
STM32L151R6-A	YES, 1.8-3.6V
STM32L151R8-A	YES, 1.8-3.6V
STM32L151RB-A	YES, 1.8-3.6V
STM32L151RC	YES, 1.8-3.6V
STM32L151RD	YES, 1.8-3.6V
STM32L151RE	YES, 1.8-3.6V
STM32L151UC	YES, 1.8-3.6V
STM32L151V8-A	YES, 1.8-3.6V
STM32L151VB-A	YES, 1.8-3.6V
STM32L151VC	YES, 1.8-3.6V
STM32L151VD	YES, 1.8-3.6V
STM32L151VE	YES, 1.8-3.6V
STM32L151ZC	YES, 1.8-3.6V
STM32L151ZD	YES, 1.8-3.6V
STM32L152C6-A	YES, 1.8-3.6V
STM32L152C8-A	YES, 1.8-3.6V
STM32L152CB-A	YES, 1.8-3.6V
STM32L152CC	YES, 1.8-3.6V
STM32L152QC	YES, 1.8-3.6V
STM32L152QD	YES, 1.8-3.6V
STM32L152QE	YES, 1.8-3.6V
STM32L152R6-A	YES, 1.8-3.6V
STM32L152R8-A	YES, 1.8-3.6V
STM32L152RC	YES, 1.8-3.6V
STM32L152RD	YES, 1.8-3.6V
STM32L152RE	YES, 1.8-3.6V
STM32L152V8-A	YES, 1.8-3.6V
STM32L152VB-A	YES, 1.8-3.6V
STM32L152VC	YES, 1.8-3.6V
STM32L152VD	YES, 1.8-3.6V
STM32L152VE	YES, 1.8-3.6V
STM32L152ZC	YES, 1.8-3.6V
STM32L152ZD	YES, 1.8-3.6V
STM32L152ZE	YES, 1.8-3.6V
STM32L162QD	YES, 1.8-3.6V
STM32L162RC	YES, 1.8-3.6V
STM32L162RD	YES, 1.8-3.6V
STM32L162RE	YES, 1.8-3.6V
STM32L162VC	YES, 1.8-3.6V
STM32L162VD	YES, 1.8-3.6V
STM32L162VE	YES, 1.8-3.6V
STM32L162ZD	YES, 1.8-3.6V
STM32L162ZE	YES, 1.8-3.6V
STM32L431CB	YES, 1.8-3.6V

STM32L431CC	YES, 1.8-3.6V
STM32L431KB	YES, 1.8-3.6V
STM32L431KC	YES, 1.8-3.6V
STM32L431RB	YES, 1.8-3.6V
STM32L431RC	YES, 1.8-3.6V
STM32L431VC	YES, 1.8-3.6V
STM32L432KB	YES, 1.8-3.6V
STM32L432KC	YES, 1.8-3.6V
STM32L433CB	YES, 1.8-3.6V
STM32L433CC	YES, 1.8-3.6V
STM32L433RB	YES, 1.8-3.6V
STM32L433RC	YES, 1.8-3.6V
STM32L433VC	YES, 1.8-3.6V
STM32L442KC	YES, 1.8-3.6V
STM32L443CC	YES, 1.8-3.6V
STM32L443RC	YES, 1.8-3.6V
STM32L443VC	YES, 1.8-3.6V
STM32L451CC	YES, 1.8-3.6V
STM32L451CE	YES, 1.8-3.6V
STM32L451RC	YES, 1.8-3.6V
STM32L451RE	YES, 1.8-3.6V
STM32L451VC	YES, 1.8-3.6V
STM32L451VE	YES, 1.8-3.6V
STM32L452CC	YES, 1.8-3.6V
STM32L452CE	YES, 1.8-3.6V
STM32L452RC	YES, 1.8-3.6V
STM32L452RE	YES, 1.8-3.6V
STM32L452VC	YES, 1.8-3.6V
STM32L452VE	YES, 1.8-3.6V
STM32L462CE	YES, 1.8-3.6V
STM32L462RE	YES, 1.8-3.6V
STM32L462VE	YES, 1.8-3.6V
STM32L471QE	YES, 1.8-3.6V
STM32L471QG	YES, 1.8-3.6V
STM32L471RE	YES, 1.8-3.6V
STM32L471RG	YES, 1.8-3.6V
STM32L471VE	YES, 1.8-3.6V
STM32L471VG	YES, 1.8-3.6V
STM32L471ZE	YES, 1.8-3.6V
STM32L471ZG	YES, 1.8-3.6V
STM32L475RC	YES, 1.8-3.6V
STM32L475RE	YES, 1.8-3.6V
STM32L475RG	YES, 1.8-3.6V
STM32L475VC	YES, 1.8-3.6V
STM32L475VE	YES, 1.8-3.6V
STM32L475VG	YES, 1.8-3.6V
STM32L476JE	YES, 1.8-3.6V
STM32L476JG	YES, 1.8-3.6V
STM32L476ME	YES, 1.8-3.6V
STM32L476MG	YES, 1.8-3.6V
STM32L476QE	YES, 1.8-3.6V
STM32L476QG	YES, 1.8-3.6V
STM32L476RC	YES, 1.8-3.6V
STM32L476RE	YES, 1.8-3.6V
STM32L476RG	YES, 1.8-3.6V
STM32L476VC	YES, 1.8-3.6V
STM32L476VE	YES, 1.8-3.6V
STM32L476VG	YES, 1.8-3.6V
STM32L476ZE	YES, 1.8-3.6V

STM32L476ZG	YES, 1.8-3.6V
STM32L486JG	YES, 1.8-3.6V
STM32L486QG	YES, 1.8-3.6V
STM32L486RG	YES, 1.8-3.6V
STM32L486VG	YES, 1.8-3.6V
STM32L486ZG	YES, 1.8-3.6V
STM32L496AE	YES, 1.8-3.6V
STM32L496AG	YES, 1.8-3.6V
STM32L496QE	YES, 1.8-3.6V
STM32L496QG	YES, 1.8-3.6V
STM32L496RE	YES, 1.8-3.6V
STM32L496RG	YES, 1.8-3.6V
STM32L496VE	YES, 1.8-3.6V
STM32L496VG	YES, 1.8-3.6V
STM32L496ZE	YES, 1.8-3.6V
STM32L496ZG	YES, 1.8-3.6V
STM32L4A6AG	YES, 1.8-3.6V
STM32L4A6QG	YES, 1.8-3.6V
STM32L4A6RG	YES, 1.8-3.6V
STM32L4A6VG	YES, 1.8-3.6V
STM32L4A6ZG	YES, 1.8-3.6V
<b>R5F1xx (RL78)</b>	
R5F1006A	YES, 1.8-5.5V
R5F1006C	YES, 1.8-5.5V
R5F1006D	YES, 1.8-5.5V
R5F1006E	YES, 1.8-5.5V
R5F1007A	YES, 1.8-5.5V
R5F1007C	YES, 1.8-5.5V
R5F1007D	YES, 1.8-5.5V
R5F1007E	YES, 1.8-5.5V
R5F1008A	YES, 1.8-5.5V
R5F1008C	YES, 1.8-5.5V
R5F1008D	YES, 1.8-5.5V
R5F1008E	YES, 1.8-5.5V
R5F100AA	YES, 1.8-5.5V
R5F100AC	YES, 1.8-5.5V
R5F100AD	YES, 1.8-5.5V
R5F100AE	YES, 1.8-5.5V
R5F100AF	YES, 1.8-5.5V
R5F100AG	YES, 1.8-5.5V
R5F100BA	YES, 1.8-5.5V
R5F100BC	YES, 1.8-5.5V
R5F100BD	YES, 1.8-5.5V
R5F100BE	YES, 1.8-5.5V
R5F100BF	YES, 1.8-5.5V
R5F100BG	YES, 1.8-5.5V
R5F100CA	YES, 1.8-5.5V
R5F100CC	YES, 1.8-5.5V
R5F100CD	YES, 1.8-5.5V
R5F100CE	YES, 1.8-5.5V
R5F100CF	YES, 1.8-5.5V
R5F100CG	YES, 1.8-5.5V
R5F100EA	YES, 1.8-5.5V
R5F100EC	YES, 1.8-5.5V
R5F100ED	YES, 1.8-5.5V
R5F100EE	YES, 1.8-5.5V
R5F100EF	YES, 1.8-5.5V
R5F100EG	YES, 1.8-5.5V
R5F100EH	YES, 1.8-5.5V

R5F100FA	YES, 1.8-5.5V
R5F100FC	YES, 1.8-5.5V
R5F100FD	YES, 1.8-5.5V
R5F100FE	YES, 1.8-5.5V
R5F100FF	YES, 1.8-5.5V
R5F100FG	YES, 1.8-5.5V
R5F100FH	YES, 1.8-5.5V
R5F100FJ	YES, 1.8-5.5V
R5F100FK	YES, 1.8-5.5V
R5F100FL	YES, 1.8-5.5V
R5F100GA	YES, 1.8-5.5V
R5F100GC	YES, 1.8-5.5V
R5F100GD	YES, 1.8-5.5V
R5F100GE	YES, 1.8-5.5V
R5F100GF	YES, 1.8-5.5V
R5F100GG	YES, 1.8-5.5V
R5F100GH	YES, 1.8-5.5V
R5F100GJ	YES, 1.8-5.5V
R5F100GK	YES, 1.8-5.5V
R5F100GL	YES, 1.8-5.5V
R5F100JC	YES, 1.8-5.5V
R5F100JD	YES, 1.8-5.5V
R5F100JE	YES, 1.8-5.5V
R5F100JF	YES, 1.8-5.5V
R5F100JG	YES, 1.8-5.5V
R5F100JH	YES, 1.8-5.5V
R5F100JJ	YES, 1.8-5.5V
R5F100JK	YES, 1.8-5.5V
R5F100JL	YES, 1.8-5.5V
R5F100LC	YES, 1.8-5.5V
R5F100LD	YES, 1.8-5.5V
R5F100LE	YES, 1.8-5.5V
R5F100LF	YES, 1.8-5.5V
R5F100LG	YES, 1.8-5.5V
R5F100LH	YES, 1.8-5.5V
R5F100LJ	YES, 1.8-5.5V
R5F100LK	YES, 1.8-5.5V
R5F100LL	YES, 1.8-5.5V
R5F100MF	YES, 1.8-5.5V
R5F100MG	YES, 1.8-5.5V
R5F100MH	YES, 1.8-5.5V
R5F100MJ	YES, 1.8-5.5V
R5F100MK	YES, 1.8-5.5V
R5F100ML	YES, 1.8-5.5V
R5F100PF	YES, 1.8-5.5V
R5F100PG	YES, 1.8-5.5V
R5F100PH	YES, 1.8-5.5V
R5F100PJ	YES, 1.8-5.5V
R5F100PK	YES, 1.8-5.5V
R5F100PL	YES, 1.8-5.5V
R5F100SH	YES, 1.8-5.5V
R5F100SJ	YES, 1.8-5.5V
R5F100SK	YES, 1.8-5.5V
R5F100SL	YES, 1.8-5.5V
R5F1016A	YES, 1.8-5.5V
R5F1016C	YES, 1.8-5.5V
R5F1016D	YES, 1.8-5.5V
R5F1016E	YES, 1.8-5.5V
R5F1017A	YES, 1.8-5.5V

R5F1017C	YES, 1.8-5.5V
R5F1017D	YES, 1.8-5.5V
R5F1017E	YES, 1.8-5.5V
R5F1018A	YES, 1.8-5.5V
R5F1018C	YES, 1.8-5.5V
R5F1018D	YES, 1.8-5.5V
R5F1018E	YES, 1.8-5.5V
R5F101AA	YES, 1.8-5.5V
R5F101AC	YES, 1.8-5.5V
R5F101AD	YES, 1.8-5.5V
R5F101AE	YES, 1.8-5.5V
R5F101AF	YES, 1.8-5.5V
R5F101AG	YES, 1.8-5.5V
R5F101BA	YES, 1.8-5.5V
R5F101BC	YES, 1.8-5.5V
R5F101BD	YES, 1.8-5.5V
R5F101BE	YES, 1.8-5.5V
R5F101BF	YES, 1.8-5.5V
R5F101BG	YES, 1.8-5.5V
R5F101CA	YES, 1.8-5.5V
R5F101CC	YES, 1.8-5.5V
R5F101CD	YES, 1.8-5.5V
R5F101CE	YES, 1.8-5.5V
R5F101CF	YES, 1.8-5.5V
R5F101CG	YES, 1.8-5.5V
R5F101EA	YES, 1.8-5.5V
R5F101EC	YES, 1.8-5.5V
R5F101ED	YES, 1.8-5.5V
R5F101EE	YES, 1.8-5.5V
R5F101EF	YES, 1.8-5.5V
R5F101EG	YES, 1.8-5.5V
R5F101EH	YES, 1.8-5.5V
R5F101FA	YES, 1.8-5.5V
R5F101FC	YES, 1.8-5.5V
R5F101FD	YES, 1.8-5.5V
R5F101FE	YES, 1.8-5.5V
R5F101FF	YES, 1.8-5.5V
R5F101FG	YES, 1.8-5.5V
R5F101FH	YES, 1.8-5.5V
R5F101FJ	YES, 1.8-5.5V
R5F101FK	YES, 1.8-5.5V
R5F101FL	YES, 1.8-5.5V
R5F101GA	YES, 1.8-5.5V
R5F101GC	YES, 1.8-5.5V
R5F101GD	YES, 1.8-5.5V
R5F101GE	YES, 1.8-5.5V
R5F101GF	YES, 1.8-5.5V
R5F101GG	YES, 1.8-5.5V
R5F101GH	YES, 1.8-5.5V
R5F101GJ	YES, 1.8-5.5V
R5F101GK	YES, 1.8-5.5V
R5F101GL	YES, 1.8-5.5V
R5F101JC	YES, 1.8-5.5V
R5F101JD	YES, 1.8-5.5V
R5F101JE	YES, 1.8-5.5V
R5F101JF	YES, 1.8-5.5V
R5F101JG	YES, 1.8-5.5V
R5F101JH	YES, 1.8-5.5V
R5F101JJ	YES, 1.8-5.5V

R5F101JK	YES, 1.8-5.5V
R5F101JL	YES, 1.8-5.5V
R5F101LC	YES, 1.8-5.5V
R5F101LD	YES, 1.8-5.5V
R5F101LE	YES, 1.8-5.5V
R5F101LF	YES, 1.8-5.5V
R5F101LG	YES, 1.8-5.5V
R5F101LH	YES, 1.8-5.5V
R5F101LJ	YES, 1.8-5.5V
R5F101LK	YES, 1.8-5.5V
R5F101LL	YES, 1.8-5.5V
R5F101MF	YES, 1.8-5.5V
R5F101MG	YES, 1.8-5.5V
R5F101MH	YES, 1.8-5.5V
R5F101MJ	YES, 1.8-5.5V
R5F101MK	YES, 1.8-5.5V
R5F101ML	YES, 1.8-5.5V
R5F101PF	YES, 1.8-5.5V
R5F101PG	YES, 1.8-5.5V
R5F101PH	YES, 1.8-5.5V
R5F101PJ	YES, 1.8-5.5V
R5F101PK	YES, 1.8-5.5V
R5F101PL	YES, 1.8-5.5V
R5F101SH	YES, 1.8-5.5V
R5F101SJ	YES, 1.8-5.5V
R5F101SK	YES, 1.8-5.5V
R5F101SL	YES, 1.8-5.5V
R5F10266	YES, 1.8-5.5V
R5F10267	YES, 1.8-5.5V
R5F10268	YES, 1.8-5.5V
R5F10269	YES, 1.8-5.5V
R5F1026A	YES, 1.8-5.5V
R5F10277	YES, 1.8-5.5V
R5F10278	YES, 1.8-5.5V
R5F10279	YES, 1.8-5.5V
R5F1027A	YES, 1.8-5.5V
R5F102A7	YES, 1.8-5.5V
R5F102A8	YES, 1.8-5.5V
R5F102A9	YES, 1.8-5.5V
R5F102AA	YES, 1.8-5.5V
R5F10366	YES, 1.8-5.5V
R5F10367	YES, 1.8-5.5V
R5F10368	YES, 1.8-5.5V
R5F10369	YES, 1.8-5.5V
R5F1036A	YES, 1.8-5.5V
R5F10377	YES, 1.8-5.5V
R5F10378	YES, 1.8-5.5V
R5F10379	YES, 1.8-5.5V
R5F1037A	YES, 1.8-5.5V
R5F103A7	YES, 1.8-5.5V
R5F103A8	YES, 1.8-5.5V
R5F103A9	YES, 1.8-5.5V
R5F103AA	YES, 1.8-5.5V
R5F104AA	YES, 1.8-5.5V
R5F104AC	YES, 1.8-5.5V
R5F104AD	YES, 1.8-5.5V
R5F104AE	YES, 1.8-5.5V
R5F104AF	YES, 1.8-5.5V
R5F104AG	YES, 1.8-5.5V



R5F104BA	YES, 1.8-5.5V
R5F104BC	YES, 1.8-5.5V
R5F104BD	YES, 1.8-5.5V
R5F104BE	YES, 1.8-5.5V
R5F104BF	YES, 1.8-5.5V
R5F104BG	YES, 1.8-5.5V
R5F104CA	YES, 1.8-5.5V
R5F104CC	YES, 1.8-5.5V
R5F104CD	YES, 1.8-5.5V
R5F104CE	YES, 1.8-5.5V
R5F104CF	YES, 1.8-5.5V
R5F104CG	YES, 1.8-5.5V
R5F104EA	YES, 1.8-5.5V
R5F104EC	YES, 1.8-5.5V
R5F104ED	YES, 1.8-5.5V
R5F104EE	YES, 1.8-5.5V
R5F104EF	YES, 1.8-5.5V
R5F104EG	YES, 1.8-5.5V
R5F104EH	YES, 1.8-5.5V
R5F104FA	YES, 1.8-5.5V
R5F104FC	YES, 1.8-5.5V
R5F104FD	YES, 1.8-5.5V
R5F104FE	YES, 1.8-5.5V
R5F104FF	YES, 1.8-5.5V
R5F104FG	YES, 1.8-5.5V
R5F104FH	YES, 1.8-5.5V
R5F104FJ	YES, 1.8-5.5V
R5F104GA	YES, 1.8-5.5V
R5F104GC	YES, 1.8-5.5V
R5F104GD	YES, 1.8-5.5V
R5F104GE	YES, 1.8-5.5V
R5F104GF	YES, 1.8-5.5V
R5F104GG	YES, 1.8-5.5V
R5F104GH	YES, 1.8-5.5V
R5F104GJ	YES, 1.8-5.5V
R5F104GK	YES, 1.8-5.5V
R5F104GL	YES, 1.8-5.5V
R5F104JC	YES, 1.8-5.5V
R5F104JD	YES, 1.8-5.5V
R5F104JE	YES, 1.8-5.5V
R5F104JF	YES, 1.8-5.5V
R5F104JG	YES, 1.8-5.5V
R5F104JH	YES, 1.8-5.5V
R5F104JJ	YES, 1.8-5.5V
R5F104LC	YES, 1.8-5.5V
R5F104LD	YES, 1.8-5.5V
R5F104LE	YES, 1.8-5.5V
R5F104LF	YES, 1.8-5.5V
R5F104LG	YES, 1.8-5.5V
R5F104LH	YES, 1.8-5.5V
R5F104LJ	YES, 1.8-5.5V
R5F104LK	YES, 1.8-5.5V
R5F104LL	YES, 1.8-5.5V
R5F104MF	YES, 1.8-5.5V
R5F104MG	YES, 1.8-5.5V
R5F104MH	YES, 1.8-5.5V
R5F104MJ	YES, 1.8-5.5V
R5F104MK	YES, 1.8-5.5V
R5F104ML	YES, 1.8-5.5V

R5F104PF	YES, 1.8-5.5V
R5F104PG	YES, 1.8-5.5V
R5F104PH	YES, 1.8-5.5V
R5F104PJ	YES, 1.8-5.5V
R5F104PK	YES, 1.8-5.5V
R5F104PL	YES, 1.8-5.5V
R5F10968	YES, 1.8-5.5V
R5F1096A	YES, 1.8-5.5V
R5F1096B	YES, 1.8-5.5V
R5F1096C	YES, 1.8-5.5V
R5F1096D	YES, 1.8-5.5V
R5F1096E	YES, 1.8-5.5V
R5F109AA	YES, 1.8-5.5V
R5F109AB	YES, 1.8-5.5V
R5F109AC	YES, 1.8-5.5V
R5F109AD	YES, 1.8-5.5V
R5F109AE	YES, 1.8-5.5V
R5F109BA	YES, 1.8-5.5V
R5F109BB	YES, 1.8-5.5V
R5F109BC	YES, 1.8-5.5V
R5F109BD	YES, 1.8-5.5V
R5F109BE	YES, 1.8-5.5V
R5F109GA	YES, 1.8-5.5V
R5F109GB	YES, 1.8-5.5V
R5F109GC	YES, 1.8-5.5V
R5F109GD	YES, 1.8-5.5V
R5F109GE	YES, 1.8-5.5V
R5F109LA	YES, 1.8-5.5V
R5F109LB	YES, 1.8-5.5V
R5F109LC	YES, 1.8-5.5V
R5F109LD	YES, 1.8-5.5V
R5F109LE	YES, 1.8-5.5V
R5F10PAD	YES, 2.7-5.5V
R5F10PAE	YES, 2.7-5.5V
R5F10PBD	YES, 2.7-5.5V
R5F10PBE	YES, 2.7-5.5V
R5F10PGD	YES, 2.7-5.5V
R5F10PGE	YES, 2.7-5.5V
R5F10PGF	YES, 2.7-5.5V
R5F10PGG	YES, 2.7-5.5V
R5F10PGH	YES, 2.7-5.5V
R5F10PGJ	YES, 2.7-5.5V
R5F10PLE	YES, 2.7-5.5V
R5F10PLF	YES, 2.7-5.5V
R5F10PLG	YES, 2.7-5.5V
R5F10PLH	YES, 2.7-5.5V
R5F10PLJ	YES, 2.7-5.5V
R5F10PME	YES, 2.7-5.5V
R5F10PMF	YES, 2.7-5.5V
R5F10PMG	YES, 2.7-5.5V
R5F10PMH	YES, 2.7-5.5V
R5F10PMJ	YES, 2.7-5.5V
R5F10PPE	YES, 2.7-5.5V
R5F10PPF	YES, 2.7-5.5V
R5F10PPG	YES, 2.7-5.5V
R5F10PPH	YES, 2.7-5.5V
R5F10WLA	YES, 1.8-5.5V
R5F10WLC	YES, 1.8-5.5V
R5F10WLD	YES, 1.8-5.5V

R5F10WLE	YES, 1.8-5.5V
R5F10WLF	YES, 1.8-5.5V
R5F10WLG	YES, 1.8-5.5V
R5F10WMA	YES, 1.8-5.5V
R5F10WMC	YES, 1.8-5.5V
R5F10WMD	YES, 1.8-5.5V
R5F10WME	YES, 1.8-5.5V
R5F10WMF	YES, 1.8-5.5V
R5F10WMG	YES, 1.8-5.5V
R5F10Y14	YES, 4.5-5.5V
R5F10Y16	YES, 4.5-5.5V
R5F10Y17	YES, 4.5-5.5V
R5F10Y44	YES, 4.5-5.5V
R5F10Y46	YES, 4.5-5.5V
R5F10Y47	YES, 4.5-5.5V
<b>R5F56x (RX600)</b>	
R5F564MF	YES, 2.7-3.6V
R5F564MG	YES, 2.7-3.6V
R5F564MJ	YES, 2.7-3.6V
R5F564ML	YES, 2.7-3.6V
<b>MSP430F1xx</b>	
MSP430F1101A	YES, 2.7-3.6V
MSP430F1111A	YES, 2.7-3.6V
MSP430F1121A	YES, 2.7-3.6V
MSP430F1122	YES, 2.7-3.6V
MSP430F1132	YES, 2.7-3.6V
MSP430F122	YES, 2.7-3.6V
MSP430F1222	YES, 2.7-3.6V
MSP430F123	YES, 2.7-3.6V
MSP430F1232	YES, 2.7-3.6V
MSP430F133	YES, 2.7-3.6V
MSP430F135	YES, 2.7-3.6V
MSP430F147	YES, 2.7-3.6V
MSP430F1471	YES, 2.7-3.6V
MSP430F148	YES, 2.7-3.6V
MSP430F1481	YES, 2.7-3.6V
MSP430F149	YES, 2.7-3.6V
MSP430F1491	YES, 2.7-3.6V
MSP430F155	YES, 2.7-3.6V
MSP430F156	YES, 2.7-3.6V
MSP430F157	YES, 2.7-3.6V
MSP430F1610	YES, 2.7-3.6V
MSP430F1611	YES, 2.7-3.6V
MSP430F1612	YES, 2.7-3.6V
MSP430F167	YES, 2.7-3.6V
MSP430F168	YES, 2.7-3.6V
MSP430F169	YES, 2.7-3.6V
<b>MSP430F2xx</b>	
MSP430F2001	YES, 2.3-3.6V
MSP430F2002	YES, 2.3-3.6V
MSP430F2003	YES, 2.3-3.6V
MSP430F2011	YES, 2.3-3.6V
MSP430F2012	YES, 2.3-3.6V
MSP430F2013	YES, 2.3-3.6V
MSP430F2101	YES, 2.3-3.6V
MSP430F2111	YES, 2.3-3.6V
MSP430F2112	YES, 2.3-3.6V
MSP430F2121	YES, 2.3-3.6V
MSP430F2122	YES, 2.3-3.6V

MSP430F2131	YES, 2.3-3.6V
MSP430F2132	YES, 2.3-3.6V
MSP430F2232	YES, 2.3-3.6V
MSP430F2234	YES, 2.3-3.6V
MSP430F2252	YES, 2.3-3.6V
MSP430F2254	YES, 2.3-3.6V
MSP430F2272	YES, 2.3-3.6V
MSP430F2274	YES, 2.3-3.6V
MSP430F233	YES, 2.3-3.6V
MSP430F2330	YES, 2.3-3.6V
MSP430F235	YES, 2.3-3.6V
MSP430F2350	YES, 2.3-3.6V
MSP430F2370	YES, 2.3-3.6V
MSP430F2410	YES, 2.3-3.6V
MSP430F2416	YES, 2.3-3.6V
MSP430F2417	YES, 2.3-3.6V
MSP430F2418	YES, 2.3-3.6V
MSP430F2419	YES, 2.3-3.6V
MSP430F247	YES, 2.3-3.6V
MSP430F2471	YES, 2.3-3.6V
MSP430F248	YES, 2.3-3.6V
MSP430F2481	YES, 2.3-3.6V
MSP430F249	YES, 2.3-3.6V
MSP430F2491	YES, 2.3-3.6V
MSP430F2616	YES, 2.3-3.6V
MSP430F2617	YES, 2.3-3.6V
MSP430F2618	YES, 2.3-3.6V
MSP430F2619	YES, 2.3-3.6V
<b>MSP430F4xx</b>	
MSP430F412	YES, 2.7-3.6V
MSP430F413	YES, 2.7-3.6V
MSP430F4132	YES, 2.7-3.6V
MSP430F415	YES, 2.7-3.6V
MSP430F4152	YES, 2.7-3.6V
MSP430F417	YES, 2.7-3.6V
MSP430F423	YES, 2.7-3.6V
MSP430F423A	YES, 2.7-3.6V
MSP430F425	YES, 2.7-3.6V
MSP430F4250	YES, 2.7-3.6V
MSP430F425A	YES, 2.7-3.6V
MSP430F4260	YES, 2.7-3.6V
MSP430F427	YES, 2.7-3.6V
MSP430F4270	YES, 2.7-3.6V
MSP430F427A	YES, 2.7-3.6V
MSP430F435	YES, 2.7-3.6V
MSP430F4351	YES, 2.7-3.6V
MSP430F436	YES, 2.7-3.6V
MSP430F4361	YES, 2.7-3.6V
MSP430F437	YES, 2.7-3.6V
MSP430F4371	YES, 2.7-3.6V
MSP430F447	YES, 2.7-3.6V
MSP430F448	YES, 2.7-3.6V
MSP430F4481	YES, 2.7-3.6V
MSP430F449	YES, 2.7-3.6V
MSP430F4491	YES, 2.7-3.6V
MSP430F4616	YES, 2.7-3.6V
MSP430F46161	YES, 2.7-3.6V
MSP430F4617	YES, 2.7-3.6V
MSP430F46171	YES, 2.7-3.6V

MSP430F4618	YES, 2.7-3.6V
MSP430F46181	YES, 2.7-3.6V
MSP430F4619	YES, 2.7-3.6V
MSP430F46191	YES, 2.7-3.6V
MSP430F47166	YES, 2.7-3.6V
MSP430F47167	YES, 2.7-3.6V
MSP430F47176	YES, 2.7-3.6V
MSP430F47177	YES, 2.7-3.6V
MSP430F47186	YES, 2.7-3.6V
MSP430F47187	YES, 2.7-3.6V
MSP430F47196	YES, 2.7-3.6V
MSP430F47197	YES, 2.7-3.6V
MSP430F4783	YES, 2.7-3.6V
MSP430F4784	YES, 2.7-3.6V
MSP430F4793	YES, 2.7-3.6V
MSP430F4794	YES, 2.7-3.6V
MSP430FE423	YES, 2.7-3.6V
MSP430FE4232	YES, 2.7-3.6V
MSP430FE423A	YES, 2.7-3.6V
MSP430FE4242	YES, 2.7-3.6V
MSP430FE425	YES, 2.7-3.6V
MSP430FE4252	YES, 2.7-3.6V
MSP430FE425A	YES, 2.7-3.6V
MSP430FE427	YES, 2.7-3.6V
MSP430FE4272	YES, 2.7-3.6V
MSP430FE427A	YES, 2.7-3.6V
MSP430FG4250	YES, 2.7-3.6V
MSP430FG4260	YES, 2.7-3.6V
MSP430FG4270	YES, 2.7-3.6V
MSP430FG437	YES, 2.7-3.6V
MSP430FG438	YES, 2.7-3.6V
MSP430FG439	YES, 2.7-3.6V
MSP430FG4616	YES, 2.7-3.6V
MSP430FG4617	YES, 2.7-3.6V
MSP430FG4618	YES, 2.7-3.6V
MSP430FG4619	YES, 2.7-3.6V
MSP430FG477	YES, 2.7-3.6V
MSP430FG478	YES, 2.7-3.6V
MSP430FG479	YES, 2.7-3.6V
MSP430FW423	YES, 2.7-3.6V
MSP430FW425	YES, 2.7-3.6V
MSP430FW427	YES, 2.7-3.6V
MSP430F5xx	
MSP430F5131	YES, 1.8-3.6V
MSP430F5132	YES, 1.8-3.6V
MSP430F5151	YES, 1.8-3.6V
MSP430F5152	YES, 1.8-3.6V
MSP430F5171	YES, 1.8-3.6V
MSP430F5172	YES, 1.8-3.6V
MSP430F5304	YES, 1.8-3.6V
MSP430F5308	YES, 1.8-3.6V
MSP430F5309	YES, 1.8-3.6V
MSP430F5310	YES, 1.8-3.6V
MSP430F5324	YES, 1.8-3.6V
MSP430F5325	YES, 1.8-3.6V
MSP430F5326	YES, 1.8-3.6V
MSP430F5327	YES, 1.8-3.6V
MSP430F5328	YES, 1.8-3.6V
MSP430F5329	YES, 1.8-3.6V

MSP430F5333	YES, 1.8-3.6V
MSP430F5335	YES, 1.8-3.6V
MSP430F5336	YES, 1.8-3.6V
MSP430F5338	YES, 1.8-3.6V
MSP430F5340	YES, 1.8-3.6V
MSP430F5341	YES, 1.8-3.6V
MSP430F5342	YES, 1.8-3.6V
MSP430F5358	YES, 1.8-3.6V
MSP430F5359	YES, 1.8-3.6V
MSP430F5418	YES, 1.8-3.6V
MSP430F5418A	YES, 1.8-3.6V
MSP430F5419	YES, 1.8-3.6V
MSP430F5419A	YES, 1.8-3.6V
MSP430F5435	YES, 1.8-3.6V
MSP430F5435A	YES, 1.8-3.6V
MSP430F5436	YES, 1.8-3.6V
MSP430F5436A	YES, 1.8-3.6V
MSP430F5437	YES, 1.8-3.6V
MSP430F5437A	YES, 1.8-3.6V
MSP430F5438	YES, 1.8-3.6V
MSP430F5438A	YES, 1.8-3.6V
MSP430F5500	YES, 1.8-3.6V
MSP430F5501	YES, 1.8-3.6V
MSP430F5502	YES, 1.8-3.6V
MSP430F5503	YES, 1.8-3.6V
MSP430F5504	YES, 1.8-3.6V
MSP430F5505	YES, 1.8-3.6V
MSP430F5506	YES, 1.8-3.6V
MSP430F5507	YES, 1.8-3.6V
MSP430F5508	YES, 1.8-3.6V
MSP430F5509	YES, 1.8-3.6V
MSP430F5510	YES, 1.8-3.6V
MSP430F5513	YES, 1.8-3.6V
MSP430F5514	YES, 1.8-3.6V
MSP430F5515	YES, 1.8-3.6V
MSP430F5517	YES, 1.8-3.6V
MSP430F5519	YES, 1.8-3.6V
MSP430F5521	YES, 1.8-3.6V
MSP430F5522	YES, 1.8-3.6V
MSP430F5524	YES, 1.8-3.6V
MSP430F5525	YES, 1.8-3.6V
MSP430F5526	YES, 1.8-3.6V
MSP430F5527	YES, 1.8-3.6V
MSP430F5528	YES, 1.8-3.6V
MSP430F5529	YES, 1.8-3.6V
MSP430F5630	YES, 1.8-3.6V
MSP430F5631	YES, 1.8-3.6V
MSP430F5632	YES, 1.8-3.6V
MSP430F5633	YES, 1.8-3.6V
MSP430F5634	YES, 1.8-3.6V
MSP430F5635	YES, 1.8-3.6V
MSP430F5636	YES, 1.8-3.6V
MSP430F5637	YES, 1.8-3.6V
MSP430F5638	YES, 1.8-3.6V
MSP430F5658	YES, 1.8-3.6V
MSP430F5659	YES, 1.8-3.6V
MSP430F6xxx	
MSP430F6433	YES, 1.8-3.6V
MSP430F6435	YES, 1.8-3.6V

MSP430F6436	YES, 1.8-3.6V
MSP430F6438	YES, 1.8-3.6V
MSP430F6458	YES, 1.8-3.6V
MSP430F6459	YES, 1.8-3.6V
MSP430F6630	YES, 1.8-3.6V
MSP430F6631	YES, 1.8-3.6V
MSP430F6632	YES, 1.8-3.6V
MSP430F6633	YES, 1.8-3.6V
MSP430F6634	YES, 1.8-3.6V
MSP430F6635	YES, 1.8-3.6V
MSP430F6636	YES, 1.8-3.6V
MSP430F6637	YES, 1.8-3.6V
MSP430F6638	YES, 1.8-3.6V
MSP430F6658	YES, 1.8-3.6V
MSP430F6659	YES, 1.8-3.6V
MSP430F6720	YES, 1.8-3.6V
MSP430F6720A	YES, 1.8-3.6V
MSP430F6721	YES, 1.8-3.6V
MSP430F6721A	YES, 1.8-3.6V
MSP430F6723	YES, 1.8-3.6V
MSP430F6723A	YES, 1.8-3.6V
MSP430F6724	YES, 1.8-3.6V
MSP430F6724A	YES, 1.8-3.6V
MSP430F6725	YES, 1.8-3.6V
MSP430F6725A	YES, 1.8-3.6V
MSP430F6726	YES, 1.8-3.6V
MSP430F6726A	YES, 1.8-3.6V
MSP430F6730	YES, 1.8-3.6V
MSP430F6730A	YES, 1.8-3.6V
MSP430F6731	YES, 1.8-3.6V
MSP430F6731A	YES, 1.8-3.6V
MSP430F6733	YES, 1.8-3.6V
MSP430F6733A	YES, 1.8-3.6V
MSP430F6734	YES, 1.8-3.6V
MSP430F6734A	YES, 1.8-3.6V
MSP430F6735	YES, 1.8-3.6V
MSP430F6735A	YES, 1.8-3.6V
MSP430F6736	YES, 1.8-3.6V
MSP430F6736A	YES, 1.8-3.6V
MSP430F67451	YES, 1.8-3.6V
MSP430F67451A	YES, 1.8-3.6V
MSP430F6745A	YES, 1.8-3.6V
MSP430F67461	YES, 1.8-3.6V
MSP430F67461A	YES, 1.8-3.6V
MSP430F6746A	YES, 1.8-3.6V
MSP430F67471	YES, 1.8-3.6V
MSP430F67471A	YES, 1.8-3.6V
MSP430F6747A	YES, 1.8-3.6V
MSP430F67481	YES, 1.8-3.6V
MSP430F67481A	YES, 1.8-3.6V
MSP430F6748A	YES, 1.8-3.6V
MSP430F67491	YES, 1.8-3.6V
MSP430F67491A	YES, 1.8-3.6V
MSP430F6749A	YES, 1.8-3.6V
MSP430F67651	YES, 1.8-3.6V
MSP430F67651A	YES, 1.8-3.6V
MSP430F6765A	YES, 1.8-3.6V
MSP430F67661	YES, 1.8-3.6V
MSP430F67661A	YES, 1.8-3.6V

MSP430F6766A	YES, 1.8-3.6V
MSP430F67671	YES, 1.8-3.6V
MSP430F67671A	YES, 1.8-3.6V
MSP430F6767A	YES, 1.8-3.6V
MSP430F67681	YES, 1.8-3.6V
MSP430F67681A	YES, 1.8-3.6V
MSP430F6768A	YES, 1.8-3.6V
MSP430F67691	YES, 1.8-3.6V
MSP430F67691A	YES, 1.8-3.6V
MSP430F6769A	YES, 1.8-3.6V
MSP430F67751	YES, 1.8-3.6V
MSP430F67751A	YES, 1.8-3.6V
MSP430F6775A	YES, 1.8-3.6V
MSP430F67761	YES, 1.8-3.6V
MSP430F67761A	YES, 1.8-3.6V
MSP430F6776A	YES, 1.8-3.6V
MSP430F67771	YES, 1.8-3.6V
MSP430F67771A	YES, 1.8-3.6V
MSP430F6777A	YES, 1.8-3.6V
MSP430F67781	YES, 1.8-3.6V
MSP430F67781A	YES, 1.8-3.6V
MSP430F6778A	YES, 1.8-3.6V
MSP430F67791	YES, 1.8-3.6V
MSP430F67791A	YES, 1.8-3.6V
MSP430F6779A	YES, 1.8-3.6V
<b>MSP430FR2xxx</b>	
MSP430FR2000	YES, 1.8-3.6V
MSP430FR2100	YES, 1.8-3.6V
MSP430FR2110	YES, 1.8-3.6V
MSP430FR2111	YES, 1.8-3.6V
<b>MSP430G2xxx</b>	
MSP430G2001	YES, 2.2-3.6V
MSP430G2101	YES, 2.2-3.6V
MSP430G2102	YES, 2.2-3.6V
MSP430G2111	YES, 2.2-3.6V
MSP430G2112	YES, 2.2-3.6V
MSP430G2113	YES, 2.2-3.6V
MSP430G2121	YES, 2.2-3.6V
MSP430G2131	YES, 2.2-3.6V
MSP430G2132	YES, 2.2-3.6V
MSP430G2152	YES, 2.2-3.6V
MSP430G2153	YES, 2.2-3.6V
MSP430G2201	YES, 2.2-3.6V
MSP430G2202	YES, 2.2-3.6V
MSP430G2203	YES, 2.2-3.6V
MSP430G2211	YES, 2.2-3.6V
MSP430G2212	YES, 2.2-3.6V
MSP430G2213	YES, 2.2-3.6V
MSP430G2221	YES, 2.2-3.6V
MSP430G2231	YES, 2.2-3.6V
MSP430G2232	YES, 2.2-3.6V
MSP430G2233	YES, 2.2-3.6V
MSP430G2252	YES, 2.2-3.6V
MSP430G2253	YES, 2.2-3.6V
MSP430G2302	YES, 2.2-3.6V
MSP430G2303	YES, 2.2-3.6V
MSP430G2312	YES, 2.2-3.6V
MSP430G2313	YES, 2.2-3.6V
MSP430G2332	YES, 2.2-3.6V



MSP430G2333	YES, 2.2-3.6V
MSP430G2352	YES, 2.2-3.6V
MSP430G2353	YES, 2.2-3.6V
MSP430G2402	YES, 2.2-3.6V
MSP430G2403	YES, 2.2-3.6V
MSP430G2412	YES, 2.2-3.6V
MSP430G2413	YES, 2.2-3.6V
MSP430G2432	YES, 2.2-3.6V
MSP430G2433	YES, 2.2-3.6V
MSP430G2444	YES, 2.2-3.6V
MSP430G2452	YES, 2.2-3.6V
MSP430G2453	YES, 2.2-3.6V
MSP430G2513	YES, 2.2-3.6V
MSP430G2533	YES, 2.2-3.6V
MSP430G2544	YES, 2.2-3.6V
MSP430G2553	YES, 2.2-3.6V
MSP430G2744	YES, 2.2-3.6V
MSP430I2xxx	
MSP430I2020	YES, 2.2-3.6V
MSP430I2021	YES, 2.2-3.6V
MSP430I2030	YES, 2.2-3.6V
MSP430I2031	YES, 2.2-3.6V
MSP430I2040	YES, 2.2-3.6V
MSP430I2041	YES, 2.2-3.6V
CC430xxxx	
CC430F5123	YES, 1.8-3.6V
CC430F5125	YES, 1.8-3.6V
CC430F5133	YES, 1.8-3.6V
CC430F5135	YES, 1.8-3.6V
CC430F5137	YES, 1.8-3.6V
CC430F5143	YES, 1.8-3.6V
CC430F5145	YES, 1.8-3.6V
CC430F5147	YES, 1.8-3.6V
CC430F6125	YES, 1.8-3.6V
CC430F6126	YES, 1.8-3.6V
CC430F6127	YES, 1.8-3.6V
CC430F6135	YES, 1.8-3.6V
CC430F6137	YES, 1.8-3.6V
CC430F6143	YES, 1.8-3.6V
CC430F6145	YES, 1.8-3.6V
CC430F6147	YES, 1.8-3.6V
CCxxx	
CC1110F16	YES, 2.0-3.6V
CC1110F32	YES, 2.0-3.6V
CC1110F8	YES, 2.0-3.6V
CC1111F16	YES, 2.0-3.6V
CC1111F32	YES, 2.0-3.6V
CC1111F8	YES, 2.0-3.6V
CC2430F128	YES, 2.0-3.6V
CC2430F32	YES, 2.0-3.6V
CC2430F64	YES, 2.0-3.6V
CC2431	YES, 2.0-3.6V
CC2510F16	YES, 2.0-3.6V
CC2510F32	YES, 2.0-3.6V
CC2510F8	YES, 2.0-3.6V
CC2511F16	YES, 2.0-3.6V
CC2511F32	YES, 2.0-3.6V
CC2511F8	YES, 2.0-3.6V
CC2530F128	YES, 2.0-3.6V

CC2530F256	YES, 2.0-3.6V
CC2530F32	YES, 2.0-3.6V
CC2530F64	YES, 2.0-3.6V
CC2531F256	YES, 2.0-3.6V
CC2533F32	YES, 2.0-3.6V
CC2533F64	YES, 2.0-3.6V
CC2533F96	YES, 2.0-3.6V
CC2540F128	YES, 2.0-3.6V
CC2540F256	YES, 2.0-3.6V
CC2541F128	YES, 2.0-3.6V
CC2541F256	YES, 2.0-3.6V
<b>EFM8</b>	
EFM8BB10F2	YES, 2.2-3.6V
EFM8BB10F4	YES, 2.2-3.6V
EFM8BB10F8	YES, 2.2-3.6V
EFM8BB21F16	YES, 2.2-3.6V
EFM8BB22F16	YES, 2.2-3.6V
EFM8BB31F16	YES, 2.2-3.6V
EFM8BB31F32	YES, 2.2-3.6V
EFM8BB31F64	YES, 2.2-3.6V
EFM8LB10F16	YES, 2.2-3.6V
EFM8LB11F16	YES, 2.2-3.6V
EFM8LB11F32	YES, 2.2-3.6V
EFM8LB12F32	YES, 2.2-3.6V
EFM8LB12F64	YES, 2.2-3.6V
EFM8SB10F2	YES, 1.8-3.6V
EFM8SB10F4	YES, 1.8-3.6V
EFM8SB10F8	YES, 1.8-3.6V
EFM8SB20F16	YES, 2.0-3.6V
EFM8SB20F32	YES, 2.0-3.6V
EFM8SB20F64	YES, 2.0-3.6V
EFM8UB10F16	YES, 2.2-3.6V
EFM8UB10F8	YES, 2.2-3.6V
EFM8UB11F16	YES, 2.2-3.6V
EFM8UB20F32	YES, 2.7-5.2V
EFM8UB20F64	YES, 2.7-5.2V
<b>C8051</b>	
C8051F300	YES, 2.7-3.6V
C8051F301	YES, 2.7-3.6V
C8051F302	YES, 2.7-3.6V
C8051F303	YES, 2.7-3.6V
C8051F304	YES, 2.7-3.6V
C8051F305	YES, 2.7-3.6V
C8051F310	YES, 2.7-3.6V
C8051F311	YES, 2.7-3.6V
C8051F312	YES, 2.7-3.6V
C8051F313	YES, 2.7-3.6V
C8051F314	YES, 2.7-3.6V
C8051F315	YES, 2.7-3.6V
C8051F316	YES, 2.7-3.6V
C8051F317	YES, 2.7-3.6V
C8051F320	YES, 2.7-3.6V
C8051F321	YES, 2.7-3.6V
C8051F326	YES, 2.7-3.6V
C8051F327	YES, 2.7-3.6V
C8051F330	YES, 2.7-3.6V
C8051F331	YES, 2.7-3.6V
C8051F332	YES, 2.7-3.6V
C8051F333	YES, 2.7-3.6V

C8051F334	YES, 2.7-3.6V
C8051F335	YES, 2.7-3.6V
C8051F336	YES, 2.7-3.6V
C8051F337	YES, 2.7-3.6V
C8051F338	YES, 2.7-3.6V
C8051F339	YES, 2.7-3.6V
C8051F340	YES, 2.7-5.2V
C8051F341	YES, 2.7-5.2V
C8051F342	YES, 2.7-5.2V
C8051F343	YES, 2.7-5.2V
C8051F344	YES, 2.7-5.2V
C8051F345	YES, 2.7-5.2V
C8051F346	YES, 2.7-5.2V
C8051F347	YES, 2.7-5.2V
C8051F348	YES, 2.7-5.2V
C8051F349	YES, 2.7-5.2V
C8051F34A	YES, 2.7-5.2V
C8051F34B	YES, 2.7-5.2V
C8051F34C	YES, 2.7-5.2V
C8051F34D	YES, 2.7-5.2V
C8051F350	YES, 2.7-3.6V
C8051F351	YES, 2.7-3.6V
C8051F352	YES, 2.7-3.6V
C8051F353	YES, 2.7-3.6V
C8051F360	YES, 2.7-3.6V
C8051F361	YES, 2.7-3.6V
C8051F362	YES, 2.7-3.6V
C8051F363	YES, 2.7-3.6V
C8051F364	YES, 2.7-3.6V
C8051F365	YES, 2.7-3.6V
C8051F366	YES, 2.7-3.6V
C8051F367	YES, 2.7-3.6V
C8051F368	YES, 2.7-3.6V
C8051F369	YES, 2.7-3.6V
C8051F370	YES, 1.8-3.6V
C8051F371	YES, 1.8-3.6V
C8051F374	YES, 1.8-3.6V
C8051F375	YES, 1.8-3.6V
C8051F380	YES, 2.7-5.2V
C8051F381	YES, 2.7-5.2V
C8051F382	YES, 2.7-5.2V
C8051F383	YES, 2.7-5.2V
C8051F384	YES, 2.7-5.2V
C8051F385	YES, 2.7-5.2V
C8051F386	YES, 2.7-5.2V
C8051F387	YES, 2.7-5.2V
C8051F388	YES, 2.7-5.2V
C8051F389	YES, 2.7-5.2V
C8051F38A	YES, 2.7-5.2V
C8051F38B	YES, 2.7-5.2V
C8051F38C	YES, 2.7-5.2V
C8051F390	YES, 1.8-3.6V
C8051F391	YES, 1.8-3.6V
C8051F392	YES, 1.8-3.6V
C8051F393	YES, 1.8-3.6V
C8051F394	YES, 1.8-3.6V
C8051F395	YES, 1.8-3.6V
C8051F396	YES, 1.8-3.6V
C8051F397	YES, 1.8-3.6V

C8051F398	YES, 1.8-3.6V
C8051F399	YES, 1.8-3.6V
C8051F410	YES, 2.4-5.2V
C8051F411	YES, 2.4-5.2V
C8051F412	YES, 2.4-5.2V
C8051F413	YES, 2.4-5.2V
C8051F501	YES, 1.8-5.2V
C8051F503	YES, 1.8-5.2V
C8051F505	YES, 1.8-5.2V
C8051F531	YES, 2.7-5.2V
C8051F585	YES, 1.8-5.2V
C8051F587	YES, 1.8-5.2V
C8051F850	YES, 2.2-3.6V
C8051F851	YES, 2.2-3.6V
C8051F852	YES, 2.2-3.6V
C8051F853	YES, 2.2-3.6V
C8051F854	YES, 2.2-3.6V
C8051F855	YES, 2.2-3.6V
C8051F860	YES, 2.2-3.6V
C8051F861	YES, 2.2-3.6V
C8051F862	YES, 2.2-3.6V
C8051F863	YES, 2.2-3.6V
C8051F864	YES, 2.2-3.6V
C8051F865	YES, 2.2-3.6V
C8051F901	YES, 1.8-3.6V
C8051F902	YES, 1.8-3.6V
C8051F911	YES, 1.8-3.6V
C8051F912	YES, 1.8-3.6V
C8051F920	YES, 1.8-3.6V
C8051F921	YES, 1.8-3.6V
C8051F930	YES, 1.8-3.6V
C8051F931	YES, 1.8-3.6V
C8051F960	YES, 1.8-3.8V
C8051F961	YES, 1.8-3.8V
C8051F962	YES, 1.8-3.8V
C8051F963	YES, 1.8-3.8V
C8051F964	YES, 1.8-3.8V
C8051F965	YES, 1.8-3.8V
C8051F966	YES, 1.8-3.8V
C8051F967	YES, 1.8-3.8V
C8051F968	YES, 1.8-3.8V
C8051F969	YES, 1.8-3.8V
<b>STM8</b>	
STM8AF5268	YES, 3.0-5.5V
STM8AF5269	YES, 3.0-5.5V
STM8AF5288	YES, 3.0-5.5V
STM8AF5289	YES, 3.0-5.5V
STM8AF528A	YES, 3.0-5.5V
STM8AF52A8	YES, 3.0-5.5V
STM8AF52A9	YES, 3.0-5.5V
STM8AF6213	YES, 3.0-5.5V
STM8AF6223	YES, 3.0-5.5V
STM8AF6226	YES, 3.0-5.5V
STM8AF6269	YES, 3.0-5.5V
STM8AF6286	YES, 3.0-5.5V
STM8AF6288	YES, 3.0-5.5V
STM8AF6289	YES, 3.0-5.5V
STM8AF628A	YES, 3.0-5.5V
STM8AF62A6	YES, 3.0-5.5V

STM8AF62A8	YES, 3.0-5.5V
STM8AF62A9	YES, 3.0-5.5V
STM8AF62AA	YES, 3.0-5.5V
STM8AL3136	YES, 1.8-3.6V
STM8AL3138	YES, 1.8-3.6V
STM8AL3146	YES, 1.8-3.6V
STM8AL3148	YES, 1.8-3.6V
STM8AL3166	YES, 1.8-3.6V
STM8AL3168	YES, 1.8-3.6V
STM8AL3188	YES, 1.8-3.6V
STM8AL318A	YES, 1.8-3.6V
STM8AL3L46	YES, 1.8-3.6V
STM8AL3L48	YES, 1.8-3.6V
STM8AL3L66	YES, 1.8-3.6V
STM8AL3L68	YES, 1.8-3.6V
STM8L051F3	YES, 1.8-3.6V
STM8L052C6	YES, 1.8-3.6V
STM8L052R8	YES, 1.8-3.6V
STM8L101F1	YES, 1.8-3.6V
STM8L101F2	YES, 1.8-3.6V
STM8L101F3	YES, 1.8-3.6V
STM8L101G2	YES, 1.8-3.6V
STM8L101G3	YES, 1.8-3.6V
STM8L101K3	YES, 1.8-3.6V
STM8L151C2	YES, 1.8-3.6V
STM8L151C3	YES, 1.8-3.6V
STM8L151C4	YES, 1.8-3.6V
STM8L151C6	YES, 1.8-3.6V
STM8L151C8	YES, 1.8-3.6V
STM8L151F2	YES, 1.8-3.6V
STM8L151F3	YES, 1.8-3.6V
STM8L151G2	YES, 1.8-3.6V
STM8L151G3	YES, 1.8-3.6V
STM8L151G4	YES, 1.8-3.6V
STM8L151G6	YES, 1.8-3.6V
STM8L151K2	YES, 1.8-3.6V
STM8L151K3	YES, 1.8-3.6V
STM8L151K4	YES, 1.8-3.6V
STM8L151K6	YES, 1.8-3.6V
STM8L151M8	YES, 1.8-3.6V
STM8L151R6	YES, 1.8-3.6V
STM8L151R8	YES, 1.8-3.6V
STM8L152C4	YES, 1.8-3.6V
STM8L152C6	YES, 1.8-3.6V
STM8L152C8	YES, 1.8-3.6V
STM8L152K4	YES, 1.8-3.6V
STM8L152K6	YES, 1.8-3.6V
STM8L152M8	YES, 1.8-3.6V
STM8L152R6	YES, 1.8-3.6V
STM8L152R8	YES, 1.8-3.6V
STM8L162M8	YES, 1.8-3.6V
STM8L162R8	YES, 1.8-3.6V
STM8S003F3	YES, 2.9-5.5V
STM8S003K3	YES, 2.9-5.5V
STM8S005C6	YES, 2.9-5.5V
STM8S005K6	YES, 2.9-5.5V
STM8S007C8	YES, 2.9-5.5V
STM8S103F2	YES, 2.9-5.5V
STM8S103F3	YES, 2.9-5.5V

STM8S103K3	YES, 2.9-5.5V
STM8S105C4	YES, 2.9-5.5V
STM8S105C6	YES, 2.9-5.5V
STM8S105K4	YES, 2.9-5.5V
STM8S105K6	YES, 2.9-5.5V
STM8S105S4	YES, 2.9-5.5V
STM8S105S6	YES, 2.9-5.5V
STM8S207C6	YES, 2.9-5.5V
STM8S207C8	YES, 2.9-5.5V
STM8S207CB	YES, 2.9-5.5V
STM8S207K6	YES, 2.9-5.5V
STM8S207K8	YES, 2.9-5.5V
STM8S207M8	YES, 2.9-5.5V
STM8S207MB	YES, 2.9-5.5V
STM8S207R6	YES, 2.9-5.5V
STM8S207R8	YES, 2.9-5.5V
STM8S207RB	YES, 2.9-5.5V
STM8S207S6	YES, 2.9-5.5V
STM8S207S8	YES, 2.9-5.5V
STM8S207SB	YES, 2.9-5.5V
STM8S208C6	YES, 2.9-5.5V
STM8S208C8	YES, 2.9-5.5V
STM8S208CB	YES, 2.9-5.5V
STM8S208MB	YES, 2.9-5.5V
STM8S208R8	YES, 2.9-5.5V
STM8S208RB	YES, 2.9-5.5V
STM8S208S6	YES, 2.9-5.5V
STM8S903F3	YES, 2.9-5.5V
STM8S903K3	YES, 2.9-5.5V
<b>HCS08</b>	
MC9S08AC16	YES, 2.7-5.5V
MC9S08AC32	YES, 2.7-5.5V
MC9S08AC48	YES, 2.7-5.5V
MC9S08AC60	YES, 2.7-5.5V
MC9S08AC8	YES, 2.7-5.5V
MC9S08FL16	YES, 4.5-5.5V
MC9S08FL8	YES, 4.5-5.5V
MC9S08JM16	YES, 2.7-5.5V
MC9S08JM32	YES, 2.7-5.5V
MC9S08JM60	YES, 2.7-5.5V
MC9S08JM8	YES, 2.7-5.5V
MC9S08PA16	YES, 2.7-5.5V
MC9S08PA32	YES, 2.7-5.5V
MC9S08PA4	YES, 2.7-5.5V
MC9S08PA60	YES, 2.7-5.5V
MC9S08PA8	YES, 2.7-5.5V
MC9S08PL16	YES, 2.7-5.5V
MC9S08PL32	YES, 2.7-5.5V
MC9S08PL4	YES, 2.7-5.5V
MC9S08PL60	YES, 2.7-5.5V
MC9S08PL8	YES, 2.7-5.5V
MC9S08PT16	YES, 2.7-5.5V
MC9S08PT32	YES, 2.7-5.5V
MC9S08PT60	YES, 2.7-5.5V
MC9S08PT8	YES, 2.7-5.5V
MC9S08QD2	YES, 2.7-5.5V
MC9S08QD4	YES, 2.7-5.5V
MC9S08SH16	YES, 2.7-5.5V
MC9S08SH32	YES, 2.7-5.5V

MC9S08SH4	YES, 2.7-5.5V
MC9S08SH8	YES, 2.7-5.5V
<b>PSoC</b>	
CY7C64215	YES, 4.5-5.5V
CY8C21123	YES, 3.0-5.5V
CY8C21223	YES, 3.0-5.5V
CY8C21234	YES, 3.0-5.5V
CY8C21323	YES, 3.0-5.5V
CY8C21334	YES, 3.0-5.5V
CY8C21434	YES, 3.0-5.5V
CY8C21534	YES, 3.0-5.5V
CY8C21634	YES, 3.0-5.5V
CY8C24123	YES, 3.0-5.5V
CY8C24223	YES, 3.0-5.5V
CY8C24423	YES, 3.0-5.5V
CY8C24794	YES, 3.0-5.5V
CY8C24894	YES, 3.0-5.5V
CY8C24994	YES, 3.0-5.5V
CY8C27143	YES, 3.0-5.5V
CY8C27243	YES, 3.0-5.5V
CY8C27443	YES, 3.0-5.5V
CY8C27543	YES, 3.0-5.5V
CY8C27643	YES, 3.0-5.5V
CY8C29466	YES, 3.0-5.5V
CY8C29566	YES, 3.0-5.5V
CY8C29666	YES, 3.0-5.5V
CY8C29866	YES, 3.0-5.5V
<b>1-Wire</b>	
DS1821	YES, 2.7-5.5V
DS1822	YES, 3.0-5.5V
DS1825	YES, 3.0-3.7V
DS18B20	YES, 3.0-5.5V
DS1971	YES, 2.8-5.2V
DS1972	YES, 2.8-5.2V
DS1973	YES, 2.8-5.2V
DS1982	YES, 2.8-5.5V
DS1985	YES, 2.8-5.5V
DS1992	YES, 2.8-5.5V
DS1993	YES, 2.8-5.5V
DS1995	YES, 2.8-5.5V
DS1996	YES, 2.8-5.5V
DS2406	YES, 2.8-5.5V
DS2430A	YES, 2.8-5.2V
DS2431	YES, 2.8-5.2V
DS24B33	YES, 2.8-5.2V
DS2502	YES, 2.8-5.5V
DS2505	YES, 2.8-5.5V
DS28E04-100	YES, 2.8-5.5V
DS28E05	YES, 1.7-3.6V
DS28EA00	YES, 3.0-5.5V
DS28EC20	YES, 3.3-5.0V
MAX31826	YES, 3.0-3.7V
<b>UNI/O EEPROM</b>	
11AA010	YES, 1.8-5.5V
11AA020	YES, 1.8-5.5V
11AA040	YES, 1.8-5.5V
11AA080	YES, 1.8-5.5V
11AA160	YES, 1.8-5.5V
11AA161	YES, 1.8-5.5V

11LC010	YES, 2.5-5.5V
11LC020	YES, 2.5-5.5V
11LC040	YES, 2.5-5.5V
11LC080	YES, 2.5-5.5V
11LC160	YES, 2.5-5.5V
11LC161	YES, 2.5-5.5V
<b>I2C EEPROM</b>	
24AA00	YES, 1.8-5.5V
24AA01	YES, 1.8-5.5V
24AA02	YES, 1.8-5.5V
24AA04	YES, 1.8-5.5V
24AA08	YES, 1.8-5.5V
24AA1025	YES, 1.8-5.5V
24AA128	YES, 1.8-5.5V
24AA16	YES, 1.8-5.5V
24AA256	YES, 1.8-5.5V
24AA32	YES, 1.8-5.5V
24AA512	YES, 1.8-5.5V
24AA515	YES, 1.8-5.5V
24AA64	YES, 1.8-5.5V
24C00	YES, 1.8-5.5V
24C01	YES, 1.8-5.5V
24C02	YES, 1.8-5.5V
24C04	YES, 1.8-5.5V
24C08	YES, 1.8-5.5V
24C1024	YES, 1.8-5.5V
24C128	YES, 1.8-5.5V
24C16	YES, 1.8-5.5V
24C256	YES, 1.8-5.5V
24C32	YES, 1.8-5.5V
24C64	YES, 1.8-5.5V
24FC1025	YES, 1.8-5.5V
24FC128	YES, 1.8-5.5V
24FC256	YES, 1.8-5.5V
24FC512	YES, 1.8-5.5V
24FC515	YES, 1.8-5.5V
24FC64	YES, 1.8-5.5V
24LC(S)21A	YES, 2.5-5.5V
24LC(S)22A	YES, 2.5-5.5V
24LC00	YES, 2.5-5.5V
24LC01	YES, 2.5-5.5V
24LC02	YES, 2.5-5.5V
24LC04	YES, 2.5-5.5V
24LC08	YES, 2.5-5.5V
24LC1025	YES, 2.5-5.5V
24LC128	YES, 2.5-5.5V
24LC16	YES, 2.5-5.5V
24LC256	YES, 2.5-5.5V
24LC32	YES, 2.5-5.5V
24LC512	YES, 2.5-5.5V
24LC515	YES, 2.5-5.5V
24LC64	YES, 2.5-5.5V
34C02	YES, 1.8-5.5V
85C72	YES, 1.8-5.5V
85C82	YES, 1.8-5.5V
85C92	YES, 1.8-5.5V
AT24C01D	YES, 1.8-3.6V
AT24C02D	YES, 1.8-3.6V
AT24C04D	YES, 1.8-3.6V



AT24C08D	YES, 1.8-3.6V
AT24C16D	YES, 1.8-3.6V
AT24C32D	YES, 1.8-5.5V
AT24C32E	YES, 1.8-3.6V
AT24C64D	YES, 1.8-5.5V
BR24T256	YES, 1.8-5.5V
CAT24C02	YES, 1.8-5.5V
CAT24C04	YES, 1.8-5.5V
CAT24C08	YES, 1.8-5.5V
CAT24C16	YES, 1.8-5.5V
M24128	YES, 1.8-5.5V
M24256	YES, 1.8-5.5V
M24512	YES, 1.8-5.5V
M24C01	YES, 1.8-5.5V
M24C02	YES, 1.8-5.5V
M24C04	YES, 1.8-5.5V
M24C08	YES, 1.8-5.5V
M24C16	YES, 1.8-5.5V
M24C32	YES, 1.8-5.5V
M24C64	YES, 1.8-5.5V
M24M01	YES, 1.8-5.5V
M24M02	YES, 1.8-5.5V
<b>SPI EEPROM</b>	
25AA010	YES, 1.8-5.5V
25AA020	YES, 1.8-5.5V
25AA080	YES, 1.8-5.5V
25AA1024	YES, 1.8-5.5V
25AA128	YES, 1.8-5.5V
25AA160	YES, 1.8-5.5V
25AA256	YES, 1.8-5.5V
25AA320	YES, 1.8-5.5V
25AA40	YES, 1.8-5.5V
25AA512	YES, 1.8-5.5V
25AA640	YES, 1.8-5.5V
25LC010	YES, 2.5-5.5V
25LC020	YES, 2.5-5.5V
25LC040	YES, 2.5-5.5V
25LC080	YES, 2.5-5.5V
25LC1024	YES, 2.5-5.5V
25LC128	YES, 2.5-5.5V
25LC160	YES, 2.5-5.5V
25LC256	YES, 2.5-5.5V
25LC320	YES, 2.5-5.5V
25LC512	YES, 2.5-5.5V
25LC640	YES, 2.5-5.5V
AT25010	YES, 2.7-5.5V
AT25020	YES, 2.7-5.5V
AT25040	YES, 2.7-5.5V
AT25080	YES, 2.7-5.5V
AT25128	YES, 2.7-5.5V
AT25160	YES, 2.7-5.5V
AT25256	YES, 2.7-5.5V
AT25320	YES, 2.7-5.5V
AT25512	YES, 1.8-5.5V
AT25640	YES, 2.7-5.5V
CAT25256	YES
CAT25256-NO-ID	YES, 1.8-5.5V
CAT25256-WITH-ID	YES, 1.8-5.5V
M95010	YES, 1.8-5.5V

M95020	YES, 1.8-5.5V
M95040	YES, 1.8-5.5V
M95080	YES, 1.8-5.5V
M95080-DR	YES, 1.8-5.5V
M95128	YES, 1.8-5.5V
M95160	YES, 1.8-5.5V
M95256	YES, 1.8-5.5V
M95320	YES, 1.8-5.5V
M95512	YES, 1.8-5.5V
M95640	YES, 1.8-5.5V
M95M01	YES, 1.8-5.5V
M95M02-DR	YES, 1.8-5.5V
MR25H256A	YES, 2.7-3.6V
X25128	YES, 2.5-5.5V
<b>SPI FLASH EPROM</b>	
A25L80P	YES, 2.7-3.6V
A25LQ32A	YES, 2.7-3.6V
AT25DF041A	YES, 2.3-3.6V
AT25DF081	YES, 1.7-1.9V
AT25DF081A	YES, 2.7-3.6V
AT25DF321	YES, 2.7-3.6V
AT25DF641	YES, 2.7-3.6V
AT25F1024	YES, 2.7-3.6V
AT25F2048	YES, 2.7-3.6V
AT25F4096	YES, 2.7-3.6V
AT25F512	YES, 2.7-3.6V
AT25F512A	YES, 2.7-3.6V
AT25FS010	YES, 2.7-3.6V
AT25FS040	YES, 2.7-3.6V
AT25SF041	YES, 2.5-3.6V
AT25SF081	YES, 2.5-3.6V
AT25SF161	YES, 2.5-3.6V
AT25SF641B	YES, 2.7-3.6V
AT25SL321	YES, 1.8-2.0V
AT26DF041	YES, 2.7-3.6V
AT26DF081A	YES, 2.7-3.6V
AT26DF161	YES, 2.7-3.6V
AT26DF161A	YES, 2.7-3.6V
AT26DF321	YES, 2.7-3.6V
AT26F004	YES, 2.7-3.6V
AT45DB011B	YES, 2.7-3.6V
AT45DB011D	YES
AT45DB011D-256	YES, 2.5-3.6V
AT45DB011D-264	YES, 2.5-3.6V
AT45DB021B	YES, 2.7-3.6V
AT45DB021D	YES
AT45DB021D-256	YES, 2.5-3.6V
AT45DB021D-264	YES, 2.5-3.6V
AT45DB021E	YES
AT45DB021E-256	YES, 1.8-3.6V
AT45DB021E-264	YES, 1.8-3.6V
AT45DB041B	YES, 2.7-3.6V
AT45DB041D	YES
AT45DB041D-256	YES, 2.5-3.6V
AT45DB041D-264	YES, 2.5-3.6V
AT45DB041E	YES
AT45DB041E-256	YES, 1.8-3.6V
AT45DB041E-264	YES, 1.8-3.6V
AT45DB081B	YES, 2.7-3.6V

AT45DB081D	YES
AT45DB081D-256	YES, 2.5-3.6V
AT45DB081D-264	YES, 2.5-3.6V
AT45DB081E	YES
AT45DB081E-256	YES, 1.8-3.6V
AT45DB081E-264	YES, 1.8-3.6V
AT45DB161B	YES, 2.7-3.6V
AT45DB161D	YES
AT45DB161D-512	YES, 2.5-3.6V
AT45DB161D-528	YES, 2.5-3.6V
AT45DB161E	YES
AT45DB161E-512	YES, 2.3-3.6V
AT45DB161E-528	YES, 2.3-3.6V
AT45DB321B	YES, 2.7-3.6V
AT45DB321D	YES
AT45DB321D-512	YES, 2.5-3.6V
AT45DB321D-528	YES, 2.5-3.6V
AT45DB321E	YES
AT45DB321E-512	YES, 2.3-3.6V
AT45DB321E-528	YES, 2.3-3.6V
AT45DB641E	YES
AT45DB641E-256	YES, 1.8-3.6V
AT45DB641E-264	YES, 1.8-3.6V
AT45DB642D	YES
AT45DB642D-1024	YES, 2.5-3.6V
AT45DB642D-1056	YES, 2.5-3.6V
EN25F16	YES, 2.7-3.6V
EN25F40	YES, 2.7-3.6V
EN25QH128A	YES, 2.7-3.6V
EN25QH16A	YES, 2.7-3.6V
EN25S16	YES, 1.8-1.9V
EN25S64	YES, 1.8-1.9V
F25L004A	YES, 2.7-3.6V
GD25Q127C	YES, 2.7-3.6V
GD25Q16C	YES, 2.7-3.6V
GD25Q32C	YES, 2.7-3.6V
GD25Q64C	YES, 2.7-3.6V
IS25LP016D	YES, 2.3-3.6V
IS25LP032D	YES, 2.3-3.6V
IS25LP064	YES, 2.3-3.6V
IS25LP064A	YES, 2.3-3.6V
IS25LP128	YES, 2.3-3.6V
IS25LQ010B	YES, 2.3-3.6V
IS25LQ016B	YES, 2.3-3.6V
IS25LQ020B	YES, 2.3-3.6V
IS25LQ025B	YES, 2.3-3.6V
IS25LQ032B	YES, 2.3-3.6V
IS25LQ040B	YES, 2.3-3.6V
IS25LQ080B	YES, 2.3-3.6V
IS25LQ512B	YES, 2.3-3.6V
IS25WP032	YES, 1.8-1.9V
IS25WP064	YES, 1.8-1.9V
IS25WP128	YES, 1.8-1.9V
IS25WQ020	YES, 1.8-1.9V
IS25WQ040	YES, 1.8-1.9V
LE25U40C	YES, 2.3-3.6V
M25P05	YES, 2.7-3.6V
M25P10	YES, 2.7-3.6V
M25P10_2.3V	YES, 2.3-3.6V

M25P128	YES, 2.7-3.6V
M25P16	YES, 2.7-3.6V
M25P20	YES, 2.7-3.6V
M25P32	YES, 2.7-3.6V
M25P40	YES, 2.7-3.6V
M25P40_2.3V	YES, 2.3-3.6V
M25P64	YES, 2.7-3.6V
M25P80	YES, 2.7-3.6V
M25PE10	YES, 2.7-3.6V
M25PE20	YES, 2.7-3.6V
M25PE40	YES, 2.7-3.6V
M25PE80	YES, 2.7-3.6V
M25PX16	YES, 2.3-3.6V
M25PX32	YES, 2.7-3.6V
M25PX80	YES, 2.3-3.6V
M45PE10	YES, 2.7-3.6V
M45PE20	YES, 2.7-3.6V
M45PE40	YES, 2.7-3.6V
M45PE80	YES, 2.7-3.6V
MT25QL128	YES, 2.7-3.6V
MT25QL256A	YES, 2.7-3.6V
MT25QL512A	YES, 2.7-3.6V
MT25QU01GBBB	YES, 1.8-2.0V
MT25QU128	YES, 1.8-2.0V
MT25QU512A	YES, 1.8-2.0V
MX25L1006E	YES, 2.7-3.6V
MX25L12835F	YES, 2.7-3.6V
MX25L12845E	YES, 2.7-3.6V
MX25L1606E	YES, 2.7-3.6V
MX25L1633E	YES, 2.7-3.6V
MX25L1635D	YES, 2.7-3.6V
MX25L2006E	YES, 2.7-3.6V
MX25L25635F	YES, 2.7-3.6V
MX25L25645G	YES, 2.7-3.6V 5)
MX25L3206E	YES, 2.7-3.6V
MX25L4005	YES, 2.7-3.6V
MX25L4006E	YES, 2.7-3.6V
MX25L51245G	YES, 2.7-3.6V 5)
MX25L512E	YES, 2.7-3.6V
MX25L6405	YES, 2.7-3.6V
MX25L6406E	YES, 2.7-3.6V
MX25L6435E	YES, 2.7-3.6V
MX25L6445E	YES, 2.7-3.6V
MX25L6473F	YES, 2.7-3.6V
MX25L8005	YES, 2.7-3.6V
MX25L8006E	YES, 2.7-3.6V
MX25U12835F	YES, 1.8-2.0V
MX25U1635E	YES, 1.8-2.0V
MX25U3235E	YES, 1.8-2.0V
MX25U3235F	YES, 1.8-2.0V
MX25V1635F	YES, 2.3-3.6V
MX25V2033F	YES, 2.3-3.6V
MX25V4006E	YES, 2.3-3.6V
MX25V4035F	YES, 2.3-3.6V
MX25V8006E	YES, 2.3-3.6V
MX66L1G45G	YES, 2.7-3.6V 5)
N25Q008A11E	YES, 1.8-2.0V
N25Q00AA11G	YES, 1.8-2.0V
N25Q00AA13G	YES, 2.7-3.6V

N25Q016A11E	YES, 1.8-2.0V
N25Q032A11E	YES, 1.8-2.0V
N25Q032A13E	YES, 2.7-3.6V
N25Q064A11E	YES, 1.8-2.0V
N25Q064A13E	YES, 2.7-3.6V
N25Q128A11E	YES, 1.8-2.0V
N25Q128A13E	YES, 2.7-3.6V
N25Q256A11E	YES, 1.8-2.0V
N25Q256A13E	YES, 2.7-3.6V
N25Q512A13G	YES, 2.7-3.6V
PM25LV010A	YES, 2.7-3.6V
PM25LV016B	YES, 2.7-3.6V
PM25LV020	YES, 2.7-3.6V
PM25LV040	YES, 2.7-3.6V
PM25LV080B	YES, 2.7-3.6V
PM25LV512A	YES, 2.7-3.6V
S25FL064L	YES, 2.7-3.6V
S25FL116K	YES, 2.7-3.6V
S25FL128P	YES
S25FL128P-256kB	YES, 2.7-3.6V
S25FL128P-64kB	YES, 2.7-3.6V
S25FL128S-256kB	YES, 2.7-3.6V
S25FL128S-64kB	YES, 2.7-3.6V
S25FL132K	YES, 2.7-3.6V
S25FL164K	YES, 2.7-3.6V
S25FL208K	YES, 2.7-3.6V
S25FL256S-256kB	YES, 2.7-3.6V
S25FL256S-64kB	YES, 2.7-3.6V
S25FL512S-256kB	YES, 2.7-3.6V
S25FS064S	YES, 1.8-2.0V 5)
SST25LF020A	YES, 3.0-3.6V
SST25LF040A	YES, 3.0-3.6V
SST25PF040C	YES, 2.3-3.6V
SST25VF010	YES, 2.7-3.6V
SST25VF010A	YES, 2.7-3.6V
SST25VF016B	YES, 2.7-3.6V
SST25VF020	YES, 2.7-3.6V
SST25VF032B	YES, 2.7-3.6V
SST25VF040	YES, 2.7-3.6V
SST25VF040B	YES, 2.7-3.6V
SST25VF064C	YES, 2.7-3.6V
SST25VF080B	YES, 2.7-3.6V
SST25VF512	YES, 2.7-3.6V
SST25VF512A	YES, 2.7-3.6V
SST25WF040B	YES, 1.8-1.9V
SST26VF016B	YES, 2.7-3.6V
SST26VF032B	YES, 2.7-3.6V
SST26VF064B	YES, 2.7-3.6V
SST26WF040B	YES, 1.8-1.9V
SST26WF064C	YES, 1.8-1.9V
W25Q128BV	YES, 2.7-3.6V
W25Q128FV	YES, 2.7-3.6V
W25Q128JV	YES, 2.7-3.6V
W25Q128JW	YES, 1.8-1.9V
W25Q16BL	YES, 2.3-3.6V
W25Q16DV	YES, 2.7-3.6V
W25Q16FW	YES, 1.8-1.9V
W25Q16JV	YES, 2.7-3.6V
W25Q256FV	YES, 2.7-3.6V

W25Q256JW	YES, 1.8-1.9V
W25Q32BV	YES, 2.7-3.6V
W25Q32FV	YES, 2.7-3.6V
W25Q32FW	YES, 1.8-1.9V
W25Q32JV	YES, 2.7-3.6V
W25Q40CL	YES, 2.3-3.6V
W25Q64BV	YES, 2.7-3.6V
W25Q64CV	YES, 2.7-3.6V
W25Q64FV	YES, 2.7-3.6V
W25Q64FW	YES, 1.8-1.9V
W25Q64JV	YES, 2.7-3.6V
W25Q80BV	YES, 2.7-3.6V
W25X16A	YES, 2.7-3.6V
W25X20	YES, 2.7-3.6V
W25X40	YES, 2.7-3.6V
W25X80	YES, 2.7-3.6V
<b>MicroWire EEPROM</b>	
93AA46A	YES, 1.8-5.5V
93AA46B	YES, 1.8-5.5V
93AA46C	YES
93AA46C-16	YES, 1.8-5.5V
93AA46C-8	YES, 1.8-5.5V
93AA56A	YES, 1.8-5.5V
93AA56B	YES, 1.8-5.5V
93AA56C	YES
93AA56C-16	YES, 1.8-5.5V
93AA56C-8	YES, 1.8-5.5V
93AA66A	YES, 1.8-5.5V
93AA66B	YES, 1.8-5.5V
93AA66C	YES
93AA66C-16	YES, 1.8-5.5V
93AA66C-8	YES, 1.8-5.5V
93AA76A	YES, 1.8-5.5V
93AA76B	YES, 1.8-5.5V
93AA76C	YES
93AA76C-16	YES, 1.8-5.5V
93AA76C-8	YES, 1.8-5.5V
93AA86A	YES, 1.8-5.5V
93AA86B	YES, 2.7-5.5V
93AA86C	YES
93AA86C-16	YES, 1.8-5.5V
93AA86C-8	YES, 1.8-5.5V
93C06	YES, 4.5-5.5V
93C46	YES
93C46-16	YES, 1.8-5.5V
93C46-8	YES, 1.8-5.5V
93C46A	YES, 2.7-5.5V
93C46B	YES, 2.5-5.5V
93C46C	YES
93C46C-16	YES, 1.8-5.5V
93C46C-8	YES, 1.8-5.5V
93C56	YES
93C56-16	YES, 1.8-5.5V
93C56-8	YES, 1.8-5.5V
93C56A	YES, 1.8-5.5V
93C56B	YES, 1.8-5.5V
93C56C	YES
93C56C-16	YES, 1.8-5.5V
93C56C-8	YES, 1.8-5.5V

93C66	YES
93C66-16	YES, 1.8-5.5V
93C66-8	YES, 1.8-5.5V
93C66A	YES, 1.8-5.5V
93C66B	YES, 1.8-5.5V
93C66C	YES
93C66C-16	YES, 1.8-5.5V
93C66C-8	YES, 1.8-5.5V
93C76	YES
93C76-16	YES, 1.8-5.5V
93C76-8	YES, 1.8-5.5V
93C76A	YES, 1.8-5.5V
93C76B	YES, 1.8-5.5V
93C76C	YES
93C76C-16	YES, 1.8-5.5V
93C76C-8	YES, 1.8-5.5V
93C86	YES
93C86-16	YES, 1.8-5.5V
93C86-8	YES, 1.8-5.5V
93C86A	YES, 2.7-5.5V
93C86B	YES, 2.7-5.5V
93C86C	YES
93C86C-16	YES, 1.8-5.5V
93C86C-8	YES, 1.8-5.5V
93LC46A	YES, 2.5-5.5V
93LC46B	YES, 2.5-5.5V
93LC46C	YES
93LC46C-16	YES, 2.5-5.5V
93LC46C-8	YES, 2.5-5.5V
93LC56A	YES, 2.5-5.5V
93LC56B	YES, 2.5-5.5V
93LC56C	YES
93LC56C-16	YES, 2.5-5.5V
93LC56C-8	YES, 2.5-5.5V
93LC66A	YES, 2.5-5.5V
93LC66B	YES, 2.5-5.5V
93LC66C	YES
93LC66C-16	YES, 2.5-5.5V
93LC66C-8	YES, 2.5-5.5V
93LC76A	YES, 2.5-5.5V
93LC76B	YES, 2.5-5.5V
93LC76C	YES
93LC76C-16	YES, 2.5-5.5V
93LC76C-8	YES, 2.5-5.5V
93LC86A	YES, 2.5-5.5V
93LC86B	YES, 2.5-5.5V
93LC86C	YES
93LC86C-16	YES, 2.5-5.5V
93LC86C-8	YES, 2.5-5.5V
BR93H56	YES, 2.5-5.5V
BR93H66	YES, 2.5-5.5V
BR93H76	YES, 2.5-5.5V
BR93H86	YES, 2.5-5.5V
M93S46	YES, 1.8-5.5V
M93S56	YES, 1.8-5.5V
M93S66	YES, 1.8-5.5V
HCSxxx	
HCS300	YES, 2.0-5.5V
HCS301	YES, 3.5-5.5V