


- Försänkare
- Kärkiupottimet
- Countersink
- Svasatore
- Forsenkere
- Forsænkere



G136



- 1.1 1.2 1.3 1.4 1.5 4.1 4.2 4.3 5.1 5.2 5.3 6.1 6.2 6.3
- 1.6 2.1 2.2 2.3 3.1 3.2 3.3 3.4 6.4 7.1 7.2 7.3 7.4 8.1 8.2

max d mm	min d mm	l ₁ mm	d ₂ Øh ₉ mm	z	e-Code	max d mm	min d mm	l ₁ mm	d ₂ Øh ₉ mm	z	e-Code
4.3	1.3	40	4	3	G1364.3	12.4	2.8	56	8	3	G13612.4
5.0	1.5	40	4	3	G1365.0	13.4	2.9	56	8	3	G13613.4
5.3	1.5	40	4	3	G1365.3	15.0	3.2	60	10	3	G13615.0
5.8	1.5	45	5	3	G1365.8	16.5	3.2	60	10	3	G13616.5
6.0	1.5	45	5	3	G1366.0	19.0	3.5	63	10	3	G13619.0
6.3	1.5	45	5	3	G1366.3	20.5	3.5	63	10	3	G13620.5
7.0	1.8	50	6	3	G1367.0	23.0	3.8	67	10	3	G13623.0
7.3	1.8	50	6	3	G1367.3	25.0	3.8	67	10	3	G13625.0
8.0	2.0	50	6	3	G1368.0	26.0	3.8	67	10	3	G13626.0
8.3	2.0	50	6	3	G1368.3	28.0	4.0	71	12	3	G13628.0
9.4	2.2	50	6	3	G1369.4	30.0	4.2	71	12	3	G13630.0
10.0	2.5	50	6	3	G13610.0	31.0	4.2	71	12	3	G13631.0
10.4	2.5	50	6	3	G13610.4						
11.5	2.8	56	8	3	G13611.5						