



Model	Rated Voltage	Operating voltage	Rated Current	Rated Speed	Starting Voltage	Stall current	Terminal Resistance	End play of Shaft	Weight(approx)
	V	V	mA	rpm	V	mA	Ω(approx)	mm	g
QX7	1.3	0.9-1.6	75Max	600±1000	0.75Max	140Max	10.6	0.1-0.2	4
QX7	3	2.0-3.6	80Max	8000±1000	1.4Max	140Max	22.0	0.1-0.2	4

► Dimensions of vibrator and holder can be tailor-made according to the customer's needs