



PE converter
PE-VK-5.1
 Part number: 7451

FESTO



Data sheet

Feature	Value
Authorisation	CCC
CE mark (see declaration of conformity)	to EU directive low-voltage devices
Measured variable	Relative pressure
Measurement method	Pneu./elect. pressure transducer
Operating pressure	0 ... 0.25 bar
Operating medium	Compressed air in accordance with ISO8573-1:2010 [7:-:-]
Note on operating and pilot medium	Lubricated operation not possible
Medium temperature	-10 ... 50 °C
Ambient temperature	-10 ... 50 °C
Switching element function	Changeover switch
Switch-on point	0.0005 bar
Switch-off point	0.0001 bar
Max. switching output voltage AC	250 V
Max. switching output voltage DC	250 V
Electrical connection	Cable 4-core
Mounting type	Optional on mounting frame 1n with through hole
Assembly position	Any
Pneumatic connection	M5
Product weight	250 g
Protection class	IP62