



HSS-Grommets Halogen free material TPE-SEBS, TPE-SEBS V0, IP-class IP65, HSS-M100 and HSS-M120

IP-class is IP54, country of manufacture Finland, FI, CE-marked.

CODE	D	D1	D2	H	B	box quantity / colour
HSS- M9	18mm	9mm	2-6mm	9mm	1-3,5mm	2500 pcs light grey RAL 7035
HSS-M9 V0	18mm	9mm	2-6mm	9mm	1-3,5mm	2500 pcs natural white
HSS-M12	22mm	12mm	3-5mm	11mm	1,5-4,5mm	2000 pcs light grey RAL 7035
HSS-M12 V0	22mm	12mm	3-5mm	11mm	1,5-4,5mm	2000 pcs natural white
HSS-M16	23,5mm	16mm	5-10mm	11mm	1,5-4,5mm	1500 pcs light grey RAL 7035
HSS-M16 V0	23,5mm	16mm	5-10mm	11mm	1,5-4,5mm	1500 pcs natural white
HSS-M20	27,5mm	20mm	7-12mm	11mm	1,5-4,5mm	1000 pcs light grey RAL 7035
HSS-M20 V0	27,5mm	20mm	7-12mm	11mm	1,5-4,5mm	1000 pcs natural white
HSS-PG16	32,5mm	23mm	10-14mm	11mm	1,5-4,5mm	500 pcs light grey RAL 7035
HSS-PG16 V0	32,5mm	23mm	10-14mm	11mm	1,5-4,5mm	500 pcs natural white
HSS-M25	32,5mm	25mm	8-15mm	11mm	1,5-4,5mm	500 pcs light grey RAL 7035
HSS-M25 V0	32,5mm	25mm	8-15mm	11mm	1,5-4,5mm	500 pcs natural white
HSS-M32	44mm	32mm	14-20mm	15mm	1,5-4,5mm	500 pcs light grey RAL 7035
HSS-M32 V0	44mm	32mm	14-20mm	15mm	1,5-4,5mm	500 pcs natural white
HSS-M40	53mm	40mm	20-28mm	15mm	1,5-4,5mm	250 pcs light grey RAL 7035
HSS-M40 V0	53mm	40mm	20-28mm	15mm	1,5-4,5mm	250 pcs natural white
HSS-M50	65mm	50mm	8-27-35mm	21mm	1,5-5,5mm	150 pcs light grey RAL 7035
HSS-M50 V0	65mm	50mm	8-27-35mm	21mm	1,5-5,6mm	150 pcs natural white
HSS-M60	71mm	60mm	15-34-45mm	21mm	1,5-5,5mm	100 pcs light grey RAL 7035
HSS-M60 V0	71mm	60mm	15-34-45mm	21mm	1,5-5,5mm	100 pcs natural white
HSS-M80	93mm	80mm	22-39-60mm	25mm	1,5-5,5mm	100 pcs light grey RAL 7035
HSS-M80 V0	93mm	80mm	22-39-60mm	25mm	1,5-5,5mm	100 pcs natural white
HSS-M100	122mm	100mm	52-68-85mm	20mm	1,5-5,5mm	50 pcs light grey RAL 7035
HSS-M100 V0	122mm	100mm	52-68-85mm	20mm	1,5-5,5mm	50 pcs natural white
HSS-M120	142mm	120mm	69-95-100mm	26mm	1,5-6,0mm	20 pcs light grey RAL 7035
HSS-M120 V0	142mm	120mm	69-95-100mm	26mm	1,5-6,0mm	20 pcs natural white