


CAD FILE:



Technical Data

Material:

Contact material: Brass

Plating: Gold Flash

Insulator material: Black polyester UL94V-0

Standard: PA6T+30%G.F

Electrical:

Current rating: 3Amps/contact max.

Contact resistance: $\leq 20m\Omega$ /contact



Insulation resistance: $\geq 1000M\Omega$ at V=100V

Withstanding voltage: 550V AC/minute

Mechanical:

Soldering temperature: +260°C, 4s max

UNSPECIFIED TOLERANCE: ± 0.20



$$A = 2.54 * \frac{nP}{2} + 0.40 \pm 0.35$$

$$B = 2.54 * \frac{nP}{2} - 2.54 \pm 0.20$$

Pin Number=2~80

APPROVALS		DATE	DEALON 德之隆® ELECTRONICS CO.,LTD		
DRAWN	G.M.Chen	2015/7/17	TITLE:	CONNECTOR	
CHECKED			PART NO.	DW254S-22-XX-85	
APPROVALS			UNIT: mm	SCALE: 1:1	SHEET 1 OF 1
TOLERANCES ARE		30~PL: ± 0.30	ANGLE	DRAWING NO.	PROJ:
		10~30 ± 0.20			
		5~10 ± 0.15	$\pm 2'$		
		~ 5 ± 0.10			

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
	A		NEW			