

ERV1/4"-VU-L50/8-V29A-1SIL

ERV1/4"-VU-L50/8-V29A-1SIL

Item number: 48728035

Quantity: 1 pcs.

Order code: FLS-CBMZZ0150N1000DZN01HRZZ0025UZZZZZZZZZZNZZ
KAVCC00501ZZ

Overview: ERV1/4"-VU-L50/8-V29A-1SIL
Float Switch Type FLS-ME
Material: Stainless steel 316Ti (EN 1.4571)
Pressure: 15.0 bar
Temperature range: -10°C up to 80°C
Fluid density: 1000 kg/m³
Electrical connection: Cable silicone 1 m
Process connection: Mounting thread upwards 1/4"BSP
Switch function 1: Change-over (SPDT) 25 mm
Switch rating: max. AC 50V; 5VA; 0.25A / DC 75V; 2,5W; 0.15A
Float: Stainless steel 316Ti V29A; Float outer diameter: 29 mm
Number of floats: 1 pc
Guide tube: OD 8 mm
Insertion length (L): 50 mm
Float stop: Welded peg

Float can't be mounted through the connection nozzle

Details: ERV1/4"-VU-L50/8-V29A-1SIL
Float Switch Type FLS-ME
Material: Stainless steel 316Ti (EN 1.4571)
Pressure: 15.0 bar
Temperature range: -10°C up to 80°C
Fluid density: 1000 kg/m³
Electrical connection: Cable silicone 1 m
Process connection: Mounting thread upwards 1/4"BSP
Switch function 1: Change-over (SPDT) 25 mm
Switch rating: max. AC 50V; 5VA; 0.25A / DC 75V; 2,5W; 0.15A
Float: Stainless steel 316Ti V29A; Float outer diameter: 29 mm
Number of floats: 1 pc
Guide tube: OD 8 mm
Insertion length (L): 50 mm
Float stop: Welded peg

Float can't be mounted through the connection nozzle