

AC FAN

JAMICON®

92X92X25 mm

JA0925-0N Series



- **Motor** : Two-pole shaded pole induction motor
- **Frame** : Aluminum Alloy, Painted black
- **Impeller** : Retardant thermoplastic in black color, rated UL94V-0
- **Speed Range** : ±10%
- **Impedance protected**

SPECIFICATIONS

Model	Bearing	Nominal Voltage (V)	Frequency (Hz)	Air Flow (CFM)	Static Pressure (inchH ₂ O)	Speed (R.P.M.)	Nominal Current (Amp)	Input Power (Watt)	Noise (dBA)	Weight (g)	
JA0925H1B0N	Dual Ball	110 - 120	50	23.24	0.054	1600	0.11	10	20.3	205	
			60	28.59	0.075	2000		8	24.9		
JA0925H1S0N	Sleeve		50	19.7	0.041	1400		10	15.1		
			60	23.19	0.053	1700		8	21.9		
JA0925H2B0N	Dual Ball		220 - 240	50	21.37	0.046	1500	0.05	10		16.3
				60	25.78	0.059	1800		8		24.7
JA0925H2S0N	Sleeve	50		18.71	0.037	1400	10		16.3		
		60		22.56	0.049	1700	8		20.7		

Specifications subject to change without notice

