



## 34XR-A Digital Multimeter

True RMS digital multimeter with temperature and backlight for contractors and field service technicians.

- Frequency to 40 MHz, temperature to 1832 °F, capacitance to 4000  $\mu$ F
- Input warning tone when test leads are in wrong jack
- 1000 V/750 V DC/AC
- 10 Amps AC/DC, fully safety fused
- Resistance to 40 M $\Omega$
- Continuity beeper
- Min/Max, Data Hold and Range Lock
- Auto power off to save battery life
- Separate door for easy battery and fuse access
- Magne-Grip™ Holster with magnetic hanging strap
- Three-year warranty



34XR-A

### No hassle warranty

*No waiting.*

*No shipping  
charges.*



Our commitment to high-quality products and customer service is demonstrated by our industry exclusive "No Hassle" warranty. In the unlikely event that an Amprobe Test Tool requires warranty service, any of our local dealers are authorized to replace it, on the spot.

(note: \$500 MSLP limit)



## 34XR-A Digital Multimeter

## Data Sheet

### General Specifications

<b>Autoranging</b>	
<b>Display</b>	3-3/4 digit LCD, 3999 counts with 41-segment analog bar graph
<b>Display Update Rate</b>	2/sec, nominal
<b>Power Battery</b>	9 V NEDA 1604, JIS 006P, IEC 6F22
<b>Battery Life</b>	200 hrs typical (alkaline) frequent use of backlight will decrease battery life
<b>Operating Temperature</b>	0 °C to 45 °C at < 70 % R.H.;
<b>Storage Temperature</b>	-20 °C to 60 °C, 0 to 80 % R.H. with battery removed from meter
<b>Dimensions</b>	196mm x 92mm x 60mm (7.75" x 3.55" x 2.4")
<b>Weight</b>	400 gr (1 lb) without holster, including battery

### Specifications

Function	Range	Accuracy
<b>DC Voltage</b>		
<b>Ranges</b>	400 mV, 4 V, 40 V, 400 V, 1000 V	± (0.5 % rdg + 1 dgt)
<b>Resolution</b>	100 µV	
<b>AC Voltage (45 Hz to 2 kHz) True RMS</b>		
<b>Ranges</b>	400 mV, 4 V, 40 V, 400 V, 750 V	
<b>Accuracy</b>	400 mV range, 45 to 100 Hz:	± (1.2 % rdg + 8 dgts)
	750 V range: 45 to 1 kHz:	± (2.0 % rdg + 8 dgts)
	All other ranges, 45 to 500 Hz:	± (1.2 % rdg + 8 dgts)
	All other ranges, 500 to 2 kHz:	± (2.0 % rdg + 8 dgts)
<b>Resolution</b>	100 µV	
AC coupled True RMS specified from 5 % to 100 % of range		
<b>DC Current</b>		
<b>Ranges</b>	400 µA, 4 mA, 40 mA, 300 mA, 10 A	
<b>Accuracy</b>	400 µA to 300 mA ranges:	± (1.0 % rdg + 1 dgt)
	10 A range:	± (2.0 % rdg + 3 dgts)
<b>Resolution</b>	0.1 µA	
<b>AC Current (45 Hz to 1 kHz) True RMS</b>		
<b>Ranges</b>	400 µA, 4 mA, 40 mA, 300 mA, 10 A	
<b>Accuracy</b>	400 µA to 300 mA ranges:	± (1.5 % rdg + 8 dgts)
	10 A range:	± (2.5 % rdg + 10 dgts)
<b>Resolution</b>	0.1 µA	
<b>Resistance</b>		
<b>Ranges</b>	400 Ω, 4 kΩ, 40 kΩ, 400 kΩ, 4 MΩ, 40 MΩ	
<b>Accuracy</b>	400, 4 k, 40 k, 400 k, 4 MΩ ranges:	± (1.0 % rdg + 4 dgts)
	40 MΩ range:	± (2.0 % rdg + 5 dgts)
<b>Resolution</b>	100 mΩ	
<b>Capacitance</b>		
<b>Ranges</b>	4 µF, 40 µF, 400 µF, 4000 µF	
<b>Accuracy</b>	4 µF range:	± (5.0 % rdg + 10 dgts)
	40 µF, 400 µF ranges:	± (5.0 % rdg + 5 dgts)
	4000 µF range:	± (5.0 % rdg + 15 dgts)
<b>Resolution</b>	1 nF	

**Specifications, cont.**

Function	Range	Accuracy
<b>Temperature</b>		
Ranges	-20 °C to 1000 °C, -4 °F to 1832 °F	
Accuracy	-20 °C to 10 °C:	± (2.0 % rdg + 4 °C)
	10 °C to 200 °C:	± (1.0 % rdg + 3 °C)
	200 °C to 1000 °C:	± (3.0 % rdg + 2 °C)
	-4 °F to 50 °F:	± (2.0 % rdg + 8 °F)
	50 °F to 400 °F:	± (1.0 % rdg + 6 °F)
	400 °F to 1832 °F:	± (3.0 % rdg + 4 °F)
Resolution	1 °C, 1 °F	
<b>Frequency</b>		
Ranges	4 kHz, 40 kHz, 400 kHz, 4 MHz, 40MHz	
Resolution	1 Hz	
<b>Duty Cycle</b>		
Ranges	0 to 90 %	
Accuracy	5 V logic:	± (2.0 % rdg + 5 dgts)
Frequency Range	40 Hz to 20 kHz	
<b>Continuity</b>		
Audible Indication	< 35 Ω	
<b>Diode Test</b>		
Test Current	1.2 mA (approximate)	
Open Circuit Volts	3.0 V DC typical	
<b>Overload Protection</b>		
AC/DC Voltage	All ranges 1000 V DC or 750 V AC RMS	
AC/DC Current	μA/mA input: 0.315 A /1000 V fast-blow ceramic (6.3 x 32 mm)	
	10 A input: 10 A /1000 V fast-blow ceramic 10 x 38 mm	
	(10 A for 4 minutes maximum followed by a 12 minute cooling period)	

## 34XR-A Digital Multimeter

## Data Sheet



### Included Accessories

Test leads with threaded alligator clips (TL36A), 9 V battery (installed), Magne-Grip™ Holster with magnetic hanging strap, Temperature adapter (TA-1), Type K thermocouple probe (TP255A), spare fuse, users manual

### Optional Accessories

VC221B	Padded Vinyl Carry Case
DL248D	Deluxe Test Lead Kit
DC205C	Heavy Duty Case
HV231-10A	High Voltage Probe
TP254A	High Temperature Probe

### Amprobe® Test Tools

website: [www.Amprobe.com](http://www.Amprobe.com)  
email: [info@amprobe.com](mailto:info@amprobe.com)  
Everett, WA 98203  
Tel: 877-AMPROBE

### Amprobe® Test Tools Europe

In den Engematten 14  
79286 Glottertal, Germany  
Tel.: +49 (0) 7684 8009 - 0