



JKL LAMP PART NUMBER	COLOR LCD HIGH OUTPUT WHITE 6720°k RGB	STARTING CIRCUIT VOLTAGE VS (Vrms) @ 0°C	OPERATING LAMP VOLTAGE VL (Vrms)	OPERATING LAMP CURRENT IL (mAmps)	BRIGHTNESS (CANDELA/m <sup>2</sup> )	*RATED LIFE (HRS) AVERAGE
BF3228-21B	x = .315 y = .295	1190	475	5 ± 1	28,000 ± 10%	40,000

\* RATED LIFE IS DEFINED AS THE POINT AT WHICH THE INTENSITY BECOMES 50% OF THE INITIAL RATING.

			<b>METRIC</b> DIMENSIONS ARE IN MILLIMETERS TOLERANCE UNLESS OTHERWISE SPECIFIED 1 PL +/- 0 2 PL +/- 0 ANGLE +/- 0			<b>JKL COMPONENTS CORPORATION</b>								
						TITLE <b>MINIATURE COLD CATHODE FLUORESCENT LAMP</b>								
<b>B</b> ELECTRICAL RATING CHANGES <b>A</b> BRIGHTNESS RATING CHANGES RELEASED			DRAWN BY L. WENGSTROM			APPVD BY DATE J.K. 8/5/04			SIZE <b>A</b>		FSCM NO. <b>55335</b>		DRAWING NO. <b>BF3228-21B</b>	
REV. NO. DESCRIPTION/ECO NUMBER APPVD DATE			<b>- CAD DRAWING -</b> MANUAL REVISIONS NOT PERMITTED			SCALE <b>NONE</b>		RELEASED DATE 12/95		REVISION DATE 8/5/04		REV. NO. <b>B</b> SHEET 1 OF 1		

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[JKL Components:](#)

[BF3228-21B](#)