





DUAL-IN-LINE SLOTTED HEADERS

Solder Tail and Wrapost Open Frame

Series 160, 162, 163



- Series 160, 162, and 163 DIL Headers are equipped with slotted heads to accept wires or component leads.
- Series 160 terminations are pluggable 0,46 dia. solder tails MM #0282, See page 183 for details. Series 162 and 163 terminations are two or three level wrapposts MM #1106. See page 195 for details.
- Insulators are high temperature thermoplastic.



Total number of pins				Quantity per tube	<div style="border: 1px solid black; border-radius: 50%; padding: 5px; display: inline-block;"> <i>For Electrical, Mechanical & Environmental Data, See pg. 4</i> </div> <div style="border: 1px solid black; border-radius: 50%; padding: 5px; display: inline-block; margin-left: 20px;"> Ordering Information </div> <div style="border: 1px solid black; border-radius: 50%; padding: 5px; display: inline-block; margin-left: 20px;"> <i>XX=Plating Code See Below</i> </div>		
	A	B	C		Solder Tail	2 Level Wrappost L = 9,4	3 Level Wrappost L = 12,95
10	12,6	5,08	7,6	41	160-XX-210-00-001000	162-10-210-00-001000	163-10-210-00-001000
4	5,0	7,62	10,1	102	160-XX-304-00-001000	162-10-304-00-001000	163-10-304-00-001000
6	7,6	7,62	10,1	67	160-XX-306-00-001000	162-10-306-00-001000	163-10-306-00-001000
8	10,1	7,62	10,1	50	160-XX-308-00-001000	162-10-308-00-001000	163-10-308-00-001000
10	12,6	7,62	10,1	40	160-XX-310-00-001000	162-10-310-00-001000	163-10-310-00-001000
14	17,7	7,62	10,1	28	160-XX-314-00-001000	162-10-314-00-001000	163-10-314-00-001000
16	20,3	7,62	10,1	25	160-XX-316-00-001000	162-10-316-00-001000	163-10-316-00-001000
18	22,8	7,62	10,1	22	160-XX-318-00-001000	162-10-318-00-001000	163-10-318-00-001000
20	25,3	7,62	10,1	20	160-XX-320-00-001000	162-10-320-00-001000	163-10-320-00-001000
22	27,8	7,62	10,1	18	160-XX-322-00-001000	162-10-322-00-001000	163-10-322-00-001000
24	30,4	7,62	10,1	16	160-XX-324-00-001000	162-10-324-00-001000	163-10-324-00-001000
28	35,5	7,62	10,1	14	160-XX-328-00-001000	162-10-328-00-001000	163-10-328-00-001000
20	25,4	10,16	12,7	20	160-XX-420-00-001000	162-10-420-00-001000	163-10-420-00-001000
22	27,8	10,16	12,7	18	160-XX-422-00-001000	162-10-422-00-001000	163-10-422-00-001000
24	30,4	10,16	12,7	16	160-XX-424-00-001000	162-10-424-00-001000	163-10-424-00-001000
28	35,5	10,16	12,7	14	160-XX-428-00-001000	162-10-428-00-001000	163-10-428-00-001000
32	40,6	10,16	12,7	12	160-XX-432-00-001000	162-10-432-00-001000	163-10-432-00-001000
24	30,4	15,24	17,7	16	160-XX-624-00-001000	162-10-624-00-001000	163-10-624-00-001000
28	35,5	15,24	17,7	14	160-XX-628-00-001000	162-10-628-00-001000	163-10-628-00-001000
32	40,6	15,24	17,7	12	160-XX-632-00-001000	162-10-632-00-001000	163-10-632-00-001000
36	45,7	15,24	17,7	11	160-XX-636-00-001000	162-10-636-00-001000	163-10-636-00-001000
40	50,8	15,24	17,7	10	160-XX-640-00-001000	162-10-640-00-001000	163-10-640-00-001000
42	53,3	15,24	17,7	9	160-XX-642-00-001000	162-10-642-00-001000	163-10-642-00-001000
48	60,9	15,24	17,7	8	160-XX-648-00-001000	162-10-648-00-001000	163-10-648-00-001000
50	63,5	15,24	17,7	8	160-XX-650-00-001000	162-10-650-00-001000	163-10-650-00-001000
52	66,0	15,24	17,7	7	160-XX-652-00-001000	162-10-652-00-001000	163-10-652-00-001000
50	63,5	22,86	25,3	8	160-XX-950-00-001000	162-10-950-00-001000	163-10-950-00-001000
52	66,0	22,86	25,3	7	160-XX-952-00-001000	162-10-952-00-001000	163-10-952-00-001000
64	81,2	22,86	25,3	6	160-XX-964-00-001000	162-10-964-00-001000	163-10-964-00-001000

For RoHS compliance select ◇ plating code.

SPECIFY PLATING CODE XX=

10 ◇

90

40 ◇

Pin Plating

0,25µm Au

5,08µm Sn/Pb

5,08µm Sn

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Mill-Max:

[163-10-964-00-001000](#) [163-10-952-00-001000](#) [163-10-950-00-001000](#) [163-10-652-00-001000](#) [163-10-650-00-001000](#) [163-10-648-00-001000](#) [163-10-642-00-001000](#) [163-10-640-00-001000](#) [163-10-636-00-001000](#) [163-10-632-00-001000](#) [163-10-628-00-001000](#) [163-10-624-00-001000](#) [163-10-432-00-001000](#) [163-10-428-00-001000](#) [163-10-424-00-001000](#) [163-10-422-00-001000](#) [163-10-420-00-001000](#) [163-10-328-00-001000](#) [163-10-324-00-001000](#) [163-10-322-00-001000](#) [163-10-320-00-001000](#) [163-10-318-00-001000](#) [163-10-316-00-001000](#) [163-10-314-00-001000](#) [163-10-310-00-001000](#) [163-10-308-00-001000](#) [163-10-306-00-001000](#) [163-10-304-00-001000](#) [163-10-210-00-001000](#)

[162-10-964-00-001000](#) [162-10-952-00-001000](#) [162-10-950-00-001000](#) [162-10-652-00-001000](#) [162-10-650-00-001000](#) [162-10-648-00-001000](#) [162-10-642-00-001000](#) [162-10-640-00-001000](#) [162-10-636-00-001000](#) [162-10-632-00-001000](#) [162-10-628-00-001000](#) [162-10-624-00-001000](#) [162-10-432-00-001000](#) [162-10-428-00-001000](#) [162-10-424-00-001000](#) [162-10-422-00-001000](#) [162-10-420-00-001000](#) [162-10-328-00-001000](#) [162-10-324-00-001000](#) [162-10-322-00-001000](#) [162-10-320-00-001000](#) [162-10-318-00-001000](#) [162-10-316-00-001000](#) [162-10-314-00-001000](#) [162-10-310-00-001000](#) [162-10-308-00-001000](#) [162-10-306-00-001000](#) [162-10-304-00-001000](#) [162-10-210-00-001000](#)

[160-90-964-00-001000](#) [160-90-952-00-001000](#) [160-90-950-00-001000](#) [160-90-652-00-001000](#) [160-90-650-00-001000](#) [160-90-648-00-001000](#) [160-90-642-00-001000](#) [160-90-640-00-001000](#) [160-90-636-00-001000](#) [160-90-632-00-001000](#) [160-90-628-00-001000](#) [160-90-624-00-001000](#) [160-90-432-00-001000](#) [160-90-428-00-001000](#) [160-90-424-00-001000](#) [160-90-422-00-001000](#) [160-90-420-00-001000](#) [160-90-328-00-001000](#) [160-90-324-00-001000](#) [160-90-322-00-001000](#) [160-90-320-00-001000](#) [160-90-318-00-001000](#) [160-90-316-00-001000](#) [160-90-314-00-001000](#) [160-90-310-00-001000](#) [160-90-308-00-001000](#) [160-90-306-00-001000](#) [160-90-304-00-001000](#) [160-90-210-00-001000](#)

[160-10-964-00-001000](#) [160-10-952-00-001000](#) [160-10-950-00-001000](#) [160-10-652-00-001000](#) [160-10-650-00-001000](#) [160-10-648-00-001000](#) [160-10-642-00-001000](#) [160-10-640-00-001000](#) [160-10-636-00-001000](#) [160-10-632-00-001000](#) [160-10-628-00-001000](#) [160-10-432-00-001000](#) [160-10-428-00-001000](#)