



## MTP5S-E6-C Cable Tie Mount

### MTP5S-E6-C

The multiple tie plate in natural color supports five bundles and is used with miniature, intermediate, and standard cable ties. It uses #6 (M3) screws and is made of nylon 6.6, which increases mechanical strength, heat and wear resistance, and stiffness. It is designed for indoor environments and comes in packages of 100.

### Specifications

Application	Low Profile Multiple Tie Plates Used to Secure Closely Spaced Wire Bundles
Product Type	Cable Tie Mount
Color	Natural
Flammability Rating	UL94V-2
Environment	Indoor
Material	Nylon 6.6
Maximum Operating Temperature (°C)	85
Maximum Operating Temperature (°F)	185
Minimum Loop Tensile Strength (N)	222
Minimum Loop Tensile Strength (lb)	50
Minimum Operating Temperature (°C)	-60
Minimum Operating Temperature (°F)	-76
Mount Method	Screw
Mounting Hole Thread Size	#6
Overall Height (In.)	0.125
Overall Height (mm)	3.18
Overall Length (In.)	6.75
Overall Length (mm)	171.4
Overall Width (In.)	0.5
Overall Width (mm)	12.7
Standards Met	cULus 62275 Type 2,21 (E136577), CE Compliant, RoHS Compliant
For Use With	Miniature, Intermediate, Standard Cross-Section Ties

**Packaging Detail**

UPC	07498358443
Std. Pkg. Qty.	100
Std. Pkg. Volume (cf)	0.0705
Std. Ctn. Qty.	1000
Std. Ctn. Volume (cf)	0.7051