

MLCC > Normal Type

CL10C331JB8NNN#

Mass Production
General
Standard
2T
Normal
125°C
RoHS

REACH
?

"#" indicates a package code.


List of part numbers with package codes

CL10C331JB8NNNC, CL10C331JB8NNND, CL10C331JB8NNNL

※ If the packaging code is Z or R, the horizontal package type (HMC) is applied to reduce the acoustic noise.

Size


Size Code	0603 (1608)	inch(mm)
L Size	1.60±0.10mm	
W Size	0.80±0.10mm	
T Size	0.80±0.10mm	



Characteristics

Temperature Characteristic	C0G(-55 ~ +125)
Capacitance	330.0pF
Tolerance	±5%
Rated Voltage	50.0Vdc
Status	Mass Production

Graph



Frequency Characteristics
Network Analyzer



Any data in this page are subject to change, modify or discontinue without notice.
 This page includes the typical data for design reference only.
 If there is any question regarding the data, please contact our sales personnel or application engineers.